

Wiha Torque Screwdrivers



A Convincing Concept

The exact torque!

- Made to EN ISO 6798, BS EN 26789, ASME B107.14M standards for repeated fastening of sensitive and expensive components in assembly, or in final inspections and quality assurance applications.
- the **TorqueFix®** model and low cost **EasyTorque®** model with a fixed torque value,
- the **TorqueVario®-S** with an integrated window scale that displays the torque value numerically. The TorqueVario®-S torque screwdriver is also available in an ESD safe version and VDE 1000V Electric safe version

TorqueFix® Factory Preset



- TorqueFix® Torque Screwdriver with a Fixed Torque Value pre-set by Wiha.
- ±6%, Traceable to national standards (*model 0.15 Nm = ±10%)

Part No.	Nm	⊙	↔
28501015	0.15*	4	112
28501050	0.5	4	112
28501060	0.6	4	112
28501090	0.9	4	112
28501110	1.1	4	119
28501200	2.0	4	119
28501250	2.5	4	119
28501300	3.0	4	126
28501380	3.8	4	126
28501550	5.5	4	132
28501720	7.2	4	132

NOTE- Special requirement torque settings on request.

TorqueVario®-S: Adjustable with Scale



- TorqueVario®-S Torque Screwdriver with Torque Value can be set via Window Scale
- Supplied with torque setter
- ±6%, traceable to national standards (*model 0.1-0.6 Nm = ±10%)

Part No.	Nm	⊙	↔
28521060	0.1-0.6*	4	127
28521100	0.4-1.0	4	127
28521200	0.8-2.0	4	131
28521500	1.0-5.0	4	138
28521800	2.0-8.0	4	142

EasyTorque Preset Torque Screwdriver



- Uses the same interchangeable blade system as the TorqueFix series.
- Comfortable handle for good power transfer. Lightweight design, torque value printed on tool.
- Internal mechanism slips when torque value has been attained. Opening torque not mechanically limited in anti-clockwise direction. Release accuracy ± 10%
- Ideal for screw-fastening indexable inserts to a prescribed torque.

Part No.	Nm	⊙	↔
30342-6	0.5	4	103
30343-3	0.6	4	103
30344-0	0.9	4	103
30345-7	1.1	4	103
30346-4	1.2	4	103
30347-1	1.4	4	103
30348-8	2.0	4	103
30349-5	2.5	4	103
30350-1	3.0	4	103
30351-8	3.8	4	103

Interchangeable Blades



- Torque 1/4" Universal Bits Holder for Torque Screwdrivers

Part No.	⊙	⬮	↔
27526-6	1/4"	4	155



- Torque Adaptor Blade suitable for 1/4" square drive sockets

Part No.	⊙	⬮	↔
26229-7	1/4"	4	155



- Torque Phillips Interchangeable Blade for Torque Screwdrivers

Part No.	⊕	⬮	↔	↔
26197-9	PH0	4	175	42
26058-3	PH1	4	175	42
27079-7	PH2	4	175	42



- Torque TORX® Interchangeable Blade for Torque Screwdrivers

Part No.	⊗	⬮	↔	↔
28595006	T6	4	175	42
28595007	T7	4	175	42
28595008	T8	4	175	42
28695010	T10	4	175	42

NOTE: Many more interchangeable blades available to order, please enquire.

Wiha Torque Vario Set



- Set of 13 pieces, with universal bit holder, 10 bits (PH1, PH2, PZ1, PZ2, T10, T15, T20, T25, 2.5 flat, 3.0 flat), Torque Vario 1.0 - 5.0Nm and torque setter

Part No.	Description
268 930	Torque Vario Set 1.0 - 5.0Nm

Torqueleader Quickset Screwdrivers



These versatile precision torque screwdrivers have micrometer adjustment of torque and are available in three torque ranges. Adaptors to convert from male to female hex or female to male hex are also available.

Part No.	Range	OAL mm	Colour	T-Bar	Fitting
NOR 016000	20-120 cNm	160	black	-	Male
NOR 016040	20-120 cNm	69	black	-	F/Hex
NOR 016100	1-6 N.m	222	red	✓	Male
NOR 016500	1-6 N.m	184	red	✓	F/Hex
NOR 016300	4-9 N.m	222	green	✓	Male
NOR 016700	4-9 N.m	184	green	✓	F/Hex

Torqueleader Preset Screwdrivers



Ideal for production applications, these torque limiting screwdrivers are designed to be set with the use of Torque Leader Calibration Analyser. Other models available in different colours to assist with identification in multiple tool applications, please enquire.

Part No.	Range	OAL mm	Colour	Fitting
NOR 015140	2-135 cNm	143	red	Male
NOR 015240	2-135 cNm	111	red	F/Hex
NOR 015540	6-406 cNm	159	red	Male
NOR 015640	6-406 cNm	127	red	F/Hex
NOR 015900	1-13.60 Nm	168	black	Male
NOR 015920	1-13.60 Nm	137	black	F/Hex

Torque Wrenches

Coaxial Torque Spanner



Torque spanner for 8mm AF nuts preset to 1N.m, specifically for use with coaxial connectors.

Part No.	Description	OAL
CHD 0801	Coax Torque Spanner	131mm

Norbar Torque Wrenches



Part No.	Torque Range	Length	Sq. Dr.
13001	1-5 N.m	170mm	1/4"
13002	10-50 lbf.in	170mm	1/4"



Part No.	Torque Range	Length	Sq. Dr.
11034	1-20 N.m / 10-180 lbf.in	215mm	3/8"
11037	1-20 N.m / 10-180 lbf.in	215mm	1/4"
11087	4-20 N.m / 40-180 lbf.in	220mm	3/8"
11123	4-20 N.m / 40-180 lbf.in	220mm	1/4"
11125	4-20 N.m / 40-180 lbf.in	215mm	3/8"



Part No.	Description
13042	
13043	
13044	
13045	
13046	
13047	
13049	
13050	

GearWrench Torque Wrench



Part No.	Description
85050	Torque Wrench 1/4" Drive - 30 - 200in/lbs
85051	Torque Wrench 3/8" Drive - 25 - 250in/lbs
85052	Torque Wrench 3/8" Drive - 10 - 100ft/lbs
85053	Torque Wrench 1/2" Drive - 10 - 150ft/lbs
85054	Torque Wrench 1/2" Drive - 20 - 250ft/lbs
85055	Torque Wrench 3/4" Drive - 100 - 600ft/lbs



Electronic torque wrenches with buzzer and indication for target torque settings and LCD screen with backlight.

Part No.	Description
KD 85071	Torque W. 1/2" Dr - 34-399 Nm / 25-250 lbf.ft
KD 85070	Torque W. 3/8" Dr - 15-134 Nm / 10-110 lbf.ft