



datasheet for MLN 100/2,5  
 article number: 934063103



<b>product description:</b>	<b>order number: 934 063-103</b>
<b>description:</b>	Measuring lead, at either end 4 mm diameter plug with caged spring and 4 mm diameter socket for tower construction. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.
<b>typ:</b>	MLN 100/2.5 gelb/yellow
<b>system:</b>	4mm system
<b>order number:</b>	934 063-103
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>norm</b>	IEC 61010
<b>pin dimensions</b>	4 mm
<b>type of contact:</b>	pin (spring loaded)
<b>cable type:</b>	LEH-XY
<b>cable specification:</b>	highly flexible lead
<b>wire stranding:</b>	320 x 0.10 mm
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b> <a href="#">Please consider derating curve!</a>	32 A
<b>contact resistance:</b>	12 mOhm
<b>cable length:</b>	100 cm
<b>conductor size:</b>	2.5 mm <sup>2</sup>
<b>cable material:</b>	PVC
<b>cable color:</b>	yellow
<b>material</b>	
<b>contact material:</b>	contact pin: brass contact spring: copper - beryllium
<b>contact surface material:</b>	nickel
<b>housing material:</b>	PA
<b>environmental conditions:</b>	

<b>temperature range:</b>	-15 °C to +70 °C
<b>flammable class:</b>	
<b>housing (basic material):</b>	UL 94 V - 2
<b>drawing</b>	<p>The drawing shows a technical representation of a component. It includes a top view and a side view. The top view shows a rectangular component with a diameter of 7.5 and a height of 15. The side view shows a component with a diameter of 0.4 and a length of L. The side view also shows a section with a diameter of 0.4 and a length of 38, and another section with a diameter of 0.4 and a length of 20.5.</p>