





SIZE	Part Number	Jack Screw Thread	Packing
25	8655MH2501LF	UNC 4-40	bulk : Qty 60
	8655MH2511LF		individual set 50 sets/carton
	8655MH2502LF	M3	bulk : Qty 60
	8655MH2512LF		individual set 50 sets/carton

NOTE:RoHS INFORMATIONS

-The LF product meets European union Directives and other country regulations as described in GS-22-009

-The product is not intended to be exposed to a manufaturing solder process

-Packaging spec:see GS-14-920



NOTES : for every sizes




Material and finish : Zinc die-cast
nickel plated
Cable strain relief : Zinc die-cast
Jackscrew : Brass, nickel plated
UNC 4-40 or M3 (see tables)
Temperature range : -55°C to +125 °C
Attenuation factor : >40 dB between 10 MHz

Other size details : see on next pages.



TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	dr	A Parrenin	2009/05/20	projection		mm		size	A3	scale	3:2
linear	X.	± /		eng	A Parrenin	2014/06/09					ecn no	ELX-B-17874-1		
	0.X	± /		chr	A Parrenin	2014/06/09								
	0.XX	± /	appr	Gert Dreesbeke	2014/06/09	product family		-	rel level	Released				
	0.XXX	± /				title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS		dwg no	C-8655-1685C		rev	C	
	0.XXXX	± /												
angular	0°	± / ° A	surface		302	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 1 of 4		



SIZE	Part Number	Jack Screw Thread	Packing
09	8655MH0901LF	UNC 4-40	bulk : Qty 80
	8655MH0911LF		individual set 50 sets/carton
	8655MH0902LF	M3	bulk : Qty 80
	8655MH0912LF		individual set 50 sets/carton





SIZE	Part Number	Jack Screw Thread	Packing
15	8655MH1501LF	UNC 4-40	bulk : Qty 80
	8655MH1511LF		individual set 50 sets/carton
	8655MH1502LF	M3	bulk : Qty 80
	8655MH1512LF		individual set 50 sets/carton





TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	dr	A Parrenin	2009/05/20	projection		mm	size	A3	scale	3:2		
linear	X.	± /		ISO 406	eng	A Parrenin				2014/06/09	ecn no	ELX-B-17874-1			
	0.X	± /		ISO 1101	chr	A Parrenin				2014/06/09					
	0.XX	± /	surface	-	appr	Gert Dreesbeke	2014/06/09	product family	-	rel level			Released		
	0.XXX	± /													
	0.XXXX	± /													
angular	0°	± / ° A	302			title		STRAIGHT METAL HOODS WITH 2 METAL CLAMPS		dwg no		C-8655-1685C		rev	C
				www.fci.com		cat. no.		-		Product - Customer Drw				sheet 2 of 4	

SIZE	Part Number	Jack Screw Thread	Packing
37	8655MH3701LF	UNC 4-40	bulk : Qty 40
	8655MH3711LF		individual set 50 sets/carton
	8655MH3702LF	M3	bulk : Qty 40
	8655MH3712LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS


SIZE	Part Number	Jack Screw Thread	Packing
50	8655MH5001LF	UNC 4-40	bulk : Qty 40
	8655MH5011LF		individual set 50 sets/carton
	8655MH5002LF	M3	bulk : Qty 40
	8655MH5012LF		individual set 50 sets/carton



TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	dr	A Parrenin	2009/05/20	projection	mm	size	A3	scale	3:2				
linear	X.	±/		ISO 406	eng	A Parrenin			2014/06/09	ecn no	ELX-B-17874-1					
	0.X	±/	ISO 1101	chr	A Parrenin	2014/06/09	product family	-			rel level	Released				
	0.XX	±/	surface	appr	Gert Droesbeke	2014/06/09		FCi	title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS			dwg no	C-8655-1685C	rev	C
	0.XXX	±/		www.fci.com	cat. no.	-										
	0.XXXX	±/														
angular	0°	±/° A	302													


CABLING INSTRUCTIONS

1- Strip the cable and solder or crimp the wires




SCALE 3:2

2-Put the connector into a half hood and tighten the jacket with a metal clamp




SCALE 3:2

3-To get the electrical continuity between the cable outer conductor and the hood tighten the outer conductor with the other metal clamp as shown



SCALE 3:2

4-Mount the jackscrews,the other half hood and tighten with 2 screws



TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	dr	A Parrenin	2009/05/20	projection	mm	size	A3	scale	1:1
linear	X.	± /		ISO 406	eng	A Parrenin			2014/06/09	ecp no	ELX-B-17874-1	
	0.X	± /	ISO 1101	chr	A Parrenin	2014/06/09	rel level	Released				
	0.XX	± /	surface	appr	Gert Dreesbeke	2014/06/09		STRAIGHT METAL HOODS			rev	
	0.XXX	± /		WITH 2 METAL CLAMPS				C-8655-1685C	C			
	0.XXXX	± /		www.fci.com			Product - Customer Drw			sheet 4 of 4		
angular	0°	± / ° A	302									