

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

3-349-026-03
2/8.99

METRAHit® 22/23/24/25/26


- Precision multimeter (V, dB, Ω , F, Hz, °C/°F)
- Resolution: 10 μ V, 10 m Ω
- Integrated quartz movement for MIN-MAX recording with reference to real-time
- Signal generator functions

METRAHit® 23/24/25/26

- Current measurement (10 A), direct or with current transformer: Display value is based on a transformation ratio of 1000:1 or 10,000:1
- METRAHit® 23S: 16 A measuring range

METRAHit® 22M/26M

- Large, 128 kB measurement data memory
- Quartz movement for data logging with reference to real-time
- Can be operated with accessory power pack



Signal generator function

QUALITY MANAGEMENT SYSTEM



DQS Certified per
DIN EN ISO 9001 Reg. No. 1262



DKD Calibration Certificate



Applications

The 22S through 26M multimeters are rugged and reliable, hand-held or system instruments for maintenance, initial start-up, training and R&D in industry, for government authorities, in the test lab, in manufacturing and quality assurance, as well as at universities.

Features

TRMS Value for Distorted Waveshapes with METRAHit® 25S and 26S/M

The utilized measuring method allows for TRMS measurements independent of waveshape.

METRAHit® 25S: TRMS AC to 1 kHz

METRAHit® 26S/M: TRMS AC and (AC+DC) to 20 kHz.

Pulse and Pulse Run Generator

This function allows for the testing of circuits and transmission paths by reading out individual pulses or pulse bursts with an amplitude of 3 V and a frequency ranging from 1 to 1000 Hz to the measurement input sockets.

Additional Functions

Continuity testing with acoustic signal, voltage for diode continuity, event counting (number and duration of events), stopwatch, data compare and long-range capacitance measurement. The integrated temperature measurement function allows for the connection of platinum sensors.

Automatic Blocking System (ABS) *

The automatic blocking system prevents incorrect connection of the measuring cables, as well as incorrect selection of the measured quantity. The potential for danger to the user, the instrument and the system is thus substantially reduced, and in many cases entirely eliminated.

Overload Protection

Overload protection safeguards the instrument in the voltage range. Overranging is indicated with an acoustic signal. The FUSE display indicates that the fuse for the active current measuring range has blown.

Automatic / Manual Measuring Range Selection

Measured quantities are selected with the rotary switch. The measuring range is automatically matched to the measurement value. The AUTO/MAN key allows for manual selection as well.

Display of Negative Values at the Analog Scale

Both negative and positive values are displayed for zero-frequency quantities at the analog scale, so that measured quantity fluctuations around the zero point can be observed.

Automatic Storage of Measurement Values *

The digitally displayed measurement value can be saved with the "DATA" function. A patented process assures that the actual measurement value is stored instead of a random value, even for rapidly changing measured quantities. The stored measurement value appears at the digital display.

* Patented

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Storage of MIN-MAX Values

In addition to display of current values, the minimum or the maximum value can be continuously updated and stored to memory.

Sampling Rate

The sampling rate defines the interval at which the respective measurement value is transmitted to the interface, or to measurement value memory.

Depending upon the measured quantity, sampling rates can be adjusted in steps of 1, 2 and 5 from 0.05 s to 10 s.

Continuity Testing

Testing for short-circuits and interruptions is possible with continuity testing. In addition to the display function, an acoustic signal can be activated which sounds if the adjustable limit value is violated.

Battery Saving Circuit

The instrument is switched off automatically if the measurement value remains constant for approx. 10 minutes, and if none of the keys or switches have been activated during this period. Automatic shut-down can be disabled.

Protective Cover for Aggressive Environments

A soft rubber cover with as tilt stand protects the instrument from impacts and drops. The rubber material assures a solid stance, even if the instrument has been placed on top of a vibrating surface.

Infrared Transmission of Measurement Data

Measurement data can be transmitted to a standard serial port at a PC via the infrared interface which is provided as standard equipment, and the optional METRAHit®SI232 adapter (for S versions) or the optional METRAHit®BD232 adapter (for M versions). Up to six instruments can transmit measurement data to the PC online (up to 10 instruments off-line).

Calibration

The multimeters are shipped with a DKD calibration certificate. In addition to standard quantities, our DKD calibration lab is also accredited for high value resistance of up to 30 GΩ/1000 V.

The instruments can be re-calibrated at our DKD calibration lab after the customer defined calibration interval has expired (manufacturer recommendation: 1 year).

Additional Functions, METRAHit®22M/26M

Memory Mode

The instrument is equipped with a quartz-movement-synchronized measurement value memory (128 kB), with a capacity for 13,000 to 60,000 measurement values depending upon configuration. Data are stored to temporary memory, or are transmitted directly to a PC. The system acquires measurement values with reference to real-time, which allows for use as a real-time data logger.

At high speed sampling frequencies (≤ 1 kHz) the instrument functions as a high speed recorder, and with slow sampling (... 10 min) as a dot matrix printer. Long-term recording is supported by the sleep mode:

For sampling periods of > 20 s, the electronics are switched on for 10 s after each measuring cycle, and are switched off for the remainder of the sampling period. Battery service life is thus extended to a maximum of 6000 hours (8 to 9 months).

Sampling rates can be adjusted from 1 ms to 10 minutes in steps of 1, 2 and 5 depending upon the measured quantity. In addition, measurement values can be stored to memory by pressing a key.

The contents of the memory can be read out with the help of a PC which has been connected to the multimeter via the METRAHit®BD232 IR adapter, and METRAWin®10/METRAHit® analysis software.

Features List

METRAHit® Function	22S	22M	23S	24S	25S	26S	26M
Current – A_{max}	not applicable		... 16 A	... 10 A/max. 16 A/30 s			
Band Width V_{AC}	... 1 kHz			... 20 kHz			
Rectification	arithmetic mean value				TRMS _{AC}	TRMS _{AC, AC+DC}	
Pulse Generator	•	•	•	•	•	•	•
MIN-MAX / Data Hold	•	•	•	•	•	•	•
Continuity, Diode	•	•	•	•	•	•	•
Fuse, 1000 V	not applicable		1.6 A	1.6 A and 16 A			
Power Current Transformer	—	—	•	—	—	—	—
Clip-On Transformer Factor	•	•	•	•	•	•	•
128 kByte Memory	—	•	—	—	—	—	•
Quartz Movement	•	•	•	•	•	•	•
Protective Rubber Cover	—	•	•	•	•	•	•

Applicable Regulations and Standards

IEC 61010-1 DIN EN 61010 Part 1 VDE 0411-1	Safety requirements for electrical equipment for measurement, control and laboratory use
DIN 43751	Digital measuring instruments
DIN EN 50081 Part 1	Generic standard for interference emission, residential, business and light industry
DIN EN 50082 Part 1	Generic standard for interference immunity, residential, business and light industry
VDI/VDE 3540	Reliability of measuring, control and regulating devices
DIN EN 60529 DIN VDE 0470 Part 1	Test instruments and test procedures – Protection provided by enclosures (IP code)

Standard Equipment

- Multimeter
- Cover for aggressive environments (except METRAHit®22S)
- KS17-2 cable set
- Batteries
- Operating instructions
- DKD calibration certificate

Guarantee

- 3 years material and workmanship
- 1 year for calibration

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Characteristic Values

Meas. Function	Measuring Range	Resolution at Upper Range Limit		Input Impedance		Intrinsic Deviation at max. Resolution under Reference Conditions		Overload Capacity ⁴⁾		Meas. Function
		30000 ¹⁾	3000 ¹⁾	—	∞	±(... % of rdg. + ... d)	±(... % of rdg. + ... d)	Value	Duration	
V ¹⁰⁾	300 mV	10 µV	100 µV	> 20 MΩ	5 MΩ // < 50 pF	0.05 + 3 ⁷⁾	0.5 + 30	1050 V DC AC eff sine	cont.	V
	3 V	100 µV	1 mV	11 MΩ	5 MΩ // < 50 pF	0.05 + 3	0.2 + 30			
	30 V	1 mV	10 mV	10 MΩ	5 MΩ // < 50 pF	0.05 + 3	0.2 + 30			
	300 V	10 mV	100 mV	10 MΩ	5 MΩ // < 50 pF	0.05 + 3	0.2 + 30			
	1000 V	100 mV	1 V	10 MΩ	5 MΩ // < 50 pF	0.05 + 3	0.2 + 30			
dB	see table on next page			—	same as for V ∞	—	± 0.1 dB ¹¹⁾			dB
				approx. Voltage Drop at Upper R. Limit						
				—	∞	—	∞ ⁵⁾			
A ¹⁰⁾	300 µA	10 nA	100 nA	160 mV	160 mV	0.1 + 5	0.5 + 30	0.36 A	cont.	A
	3 mA	100 nA	1 µA	160 mV	160 mV	0.1 + 5	0.5 + 30			
	30 mA	1 µA	10 µA	200 mV	200 mV	0.05 + 5	0.5 + 30			
	300 mA	10 µA	100 µA	300 mV	300 mV	0.5 + 5	0.5 + 30	10 A ⁶⁾	cont.	
	3 A	100 µA	1 mA	110 mV	110 mV	0.5 + 5	0.75 + 30			
	10 A	1 mA	10 mA	350 mV	350 mV	0.5 + 5	0.75 + 30			
Ω	300 Ω	10 mΩ		Open-Circuit Voltage	Meas. Current at Upper R. Limit	±(... % of rdg. + ... d)		500 V DC AC eff sine	5 min.	Ω
	3 kΩ	100 mΩ		0.6 V	max. 250 µA	0.1 + 5 ⁷⁾				
	30 kΩ	1 Ω		0.6 V	max. 45 µA	0.1 + 5 ⁷⁾				
	300 kΩ	10 Ω		0.6 V	max. 4.5 µA	0.1 + 5				
	3 MΩ	100 Ω		0.6 V	max. 1.5 µA	0.1 + 5				
	30 MΩ	1 kΩ		0.6 V	max. 150 nA	0.1 + 5				
Ω ¹¹⁾	300 Ω		0.1 Ω	max. 3 V	max. 1.2 mA	0.2 + 5				Ω ¹¹⁾
→ ¹¹⁾	3 V ¹²⁾		1 mV	max. 3 V	max. 1.2 mA	0.2 + 5				→ ¹¹⁾
→	3 V ¹²⁾	100 µV		max. 3 V	max. 1.2 mA	0.2 + 3				→
				Discharge Resist.	U _{0 max}	±(... % of rdg. + ... d)				
F	3 nF		1 pF	10 MΩ	3 V	1 + 6 ⁷⁾		500 V DC AC eff sine	5 min.	F
	30 nF		10 pF	10 MΩ	3 V	1 + 6 ⁷⁾				
	300 nF		100 pF	1 MΩ	3 V	1 + 6				
	3 µF		1 nF	100 kΩ	3 V	1 + 6				
	30 µF		10 nF	11 kΩ	3 V	1 + 6				
	300 µF		100 nF	2 kΩ	3 V	5 + 6				
	3000 µF		1 µF	2 kΩ	3 V	5 + 6				
	30000 µF		1 µF	2 kΩ	3 V	5 + 60				
				f _{min} ³⁾		±(... % of rdg. + ... d)	max. measuring voltage			
Hz	300.00 Hz	0.01 Hz		1 Hz		0.1 + 1 ⁸⁾	1000 V	1000 V	cont.	Hz
	3.0000 kHz	0.1 Hz		1 Hz		0.1 + 1 ⁸⁾	1000 V			
	100.00 kHz	10 Hz		1 Hz		0.1 + 1 ⁸⁾	< 30 kHz: 300 V > 30 kHz: 30 V			
🕒	100 min ²⁾	10 ms				±15 d				🕒
						±(... % of rdg. + ... d)				
°C/°F	Pt 100/ Pt 1000	-200.0 ... +100.0 °C	0.1 °C			0.5 K + 3 ⁹⁾		500 V DC/AC eff sine	5 min.	°C/°F
		+100.0 ... +850.0 °C				0.5 + 3 ⁹⁾				

- 1) Display: 4¾ place, a different resolution and sampling rate can be selected for the storage and transmission of measurement values in the rAtE menu.
- 2) Stopwatch, format: mm:ss:h where m = minutes, s = seconds and h = hundredths of a second, max.: 99:59:5
- 3) Smallest measurable frequency for sinusoidal measurement signals symmetric to the zero point
- 4) At 0° to + 40° C
- 5) Values of less than 100 digits are suppressed.
- 6) 15 (20) ... 45 ... 65 Hz ... 20 (1) kHz sine, see page 4 for influences.
- 7) 12 A – 5 min., 16 A – 30 s
- 8) ZERO appears at display when "zero balancing" function is activated.
- 9) Range: 300 mV ∞: U_E = 50 mV_{eff/rms} ... 300 mV_{eff/rms}
 3 V ∞: U_E = 0.3 V_{eff/rms} ... 3 V_{eff/rms}
 30 V ∞: U_E = 3 V_{eff/rms} ... 30 V_{eff/rms}
 300 V ∞: U_E = 30 V_{eff/rms} ... 300 V_{eff/rms}
 1000 V ∞: U_E = 300 V_{eff/rms} ... 1000 V_{eff/rms}
- 10) Plus sensor error
- 10) METRAHit® 26S/M and 25S: TRMS measurement
- 11) Indicated error values apply as of a displayed value of 10% of the measuring range.
- 12) Display up to max. 1.8 V, otherwise „OL“ is shown on the display

Key: rdg. = reading, R = measuring range, d = digit(s)

Measuring Function	Measuring Range	22S/M	23S	24S	25S ¹⁰⁾	26S/M ¹⁰⁾
A	300 µA	—	•	•	•	•
	3 mA	—	•	•	•	•
	30 mA	—	•	•	•	•
	300 mA	—	•	•	•	•
	3 A	—	•	•	•	•
A ~ ∞	10 A	—	16 A ¹²⁾	•	•	•
	mA/A	—	•	•	•	•
A ~ ∞	mV/A	•	—	—	—	—

¹²⁾ Without 16 A fuse

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

dB Ranges

Measuring Ranges	Display Range for Reference Voltage $U_{REF} = 0.775 V$	Resolution
300mV \sim	- 48 dB ... - 8 dB	0.01 dB
3 V \sim	- 28 dB ... + 12dB	0.01 dB
30 V \sim	- 8 dB ... + 32 dB	0.01 dB
300 V \sim	+ 2 dB ... + 52 dB	0.01 dB
1000 V \sim	+ 22 dB ... + 63 dB	0.01 dB
	Display (dB) = $20 \lg U_x (V) / U_{REF}$	

Real-Time Clock

Accuracy ± 1 min. per month
Temp. Influence 50 ppm per K

Influencing Quantities and Influence Errors

Influencing Quantity	Influence Range	Measured Quantity / Measuring Range ¹⁾	Influence Error (...% + ... d) / 10 K
Temperature	0 °C ... +21 °C and +25 °C ... +40 °C	V \equiv	0.2 + 10
		V \sim	0.4 + 10
		300 μ A ... 30 mA \equiv + $\overline{\equiv}$	0.5 + 10
		300 mA \equiv + $\overline{\equiv}$	0.5 + 10
		3 A / 10 A \equiv + $\overline{\equiv}$	0.75 + 10
		300 Ω ... 300 k Ω	0.2 + 10
		3 M Ω	0.2 + 10
		30 M Ω	1 + 10
		3 nF ... 300 μ F	0.5 + 10
		Hz	0.5 + 10
°C (Pt100)	0.5 + 10		

METRAHit®26S/M: TRMS AC and (AC+DC) 15 Hz to 20 kHz
METRAHit®25S: TRMS AC 15 Hz to 1 kHz
METRAHit®22/23/24: mean value rectification, AC 20 Hz to 1 kHz

Influencing Quantity	Influence Range (max. resolution)	Frequency	Intrinsic Error ²⁾ $\pm (... \% \text{ of rdg.} + ... \text{ d})$
Frequency V_{AC}	300,000 mV	> 15 Hz ... 45 Hz	2.5 + 40 (> 300 d)
		> 65 Hz ... 1 kHz	1.0 + 30 (> 300 d)
		> 1 kHz ... 20 kHz	3.0 + 50 (> 300 d)
	3,00000 V 30,0000 V 300,000 V	> 15 Hz ... 45 Hz	2.2 + 40 (> 300 d)
		> 65 Hz ... 1 kHz	0.7 + 30 (> 300 d)
		> 1 kHz ... 20 kHz	2.2 + 50 (> 300 d)
1000,0 V	> 15 Hz ... 45 Hz	2.2 + 40 (> 300 d)	
	> 65 Hz ... 1 kHz	1.2 + 30 (> 300 d)	
	> 1 kHz ... 10 kHz	10 + 50 (> 300 d)	

Influencing Quantity	Influence Range (max. resolution)	Frequency	Intrinsic Error ²⁾ $\pm (... \% \text{ of rdg.} + ... \text{ d})$
Frequency I_{AC}	300.00 μ A ...	> 15 Hz ... 45 Hz	1 + 30
		> 65 Hz ... 1 kHz	
	3,0000 A 10,000 A	> 15 Hz ... 45 Hz	1 + 30
		> 65 Hz ... 1 kHz	3 + 30

1) With zero balancing
2) Indicated error values apply as of a displayed value of 10% of the measuring range.

Influencing Quantity	Influence Range	Measured Quantity / Measuring Range	Influence Error ²⁾
crest factor CF	1 ... 3	V \sim , A \sim	$\pm 1\%$ of rdg.
	> 3 ... 5		$\pm 3\%$ of rdg.
Measured Quantity Waveshape ³⁾	<p>The allowable crest factor CF for the periodic quantity to be measured depends upon the displayed value:</p>		

Influencing Quantity	Influence Range	Measured Quantity / Measuring Range ¹⁾	Influence Error
Relative Humidity	75% 3 days instrument off	V, A, Ω F, Hz °C	1 x intrinsic error

Influencing Qty.	Influence Range	Measuring Range	Damping
Common-Mode Interference Voltage	influencing quantity max. 1000 V \sim 50 Hz, 60 Hz sine	V \equiv	> 90 dB
		300 mV ... 30 V \sim	> 60 dB
		300 V \sim 1000 V \sim	> 60 dB
Series-Mode Interference Voltage	influencing quantity V \sim , nominal measuring range value, max. 1000 V \sim , 50 Hz, 60 Hz sine	V \equiv ⁴⁾	> 40 dB
		influencing quantity max. 1000 V \equiv	> 60 dB

1) With zero balancing
2) Except for sinusoidal waveshapes
3) METRAHit®26S/M and 25S only
4) For METRAHit®22/23/24: except for mV range

Reference Conditions

Ambient Temperature +23 °C \pm 2 K
Relative Humidity 45 ... 55%
Measured Qty. Frequency 45 ... 65 Hz
Measured Qty. Waveshape sine
Battery Voltage 3 V \pm 0.1 V
Power Pack Voltage 4.5 V \pm 0.2 V

Response Time (after manual range selection)

Measured Quantity / Measuring Range	Digital Display Response Time	Measured Quantity Jump Function
V \equiv , V \sim , A \equiv , A \sim	1.5 s	from 0 to 80% of the measuring range upper limit
300 Ω ... 3 M Ω	2 s	from ∞ to 50% of the measuring range upper limit
30 M Ω	5 s	
Continuity	< 50 ms	
\rightarrow	1.5 s	from 0 to 50% of the measuring range upper limit
3 nF ... 300 μ F	max. 2 s	
3 000 μ F	max. 7 s	
30 000 μ F	max. 14 s	
> 10 Hz	max. 1.5 s	
°C	max. 3 s	

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Power Supply

Battery	2 ea. 1.5 V mignon cells alkaline-manganese cells per IEC LR6 zinc-carbon battery per IEC R6
Service Life	alkaline-manganese cells: approx. 100 hr.
Battery Test	" \rightarrow " symbol is displayed automatically when battery voltage drops to below approx. 2.3 V, or if voltage from the power pack is less than approx. 3 V.

Display

LC display field (65 mm x 30 mm) with analog and digital display of unit of measure, type of current and various special functions.

Analog

Display	LCD scale with pointer
Scale Length	55 mm for V $\overline{=}$ and A $\overline{=}$, 47 mm for all other ranges
Scaling	\mp 5 ... 0 ... \pm 30 with 35 graduations for $\overline{=}$, 0 ... 30 with 30 graduations for all other ranges
Polarity Display	with automatic reversal
Overload Display	triangle is displayed (13)
Measuring Rate	20 measurements per second

Digital

Display / Char. Height	7 segment characters / 12 mm
Places	4 $\frac{3}{4}$ places \cong 31,000 steps
Overload Display	"OL" is displayed
Polarity Display	"-" sign is displayed when plus pole is connected to " \perp "
Measuring Rate	2 measurements per second

Display Refresh

V (DC, AC+DC), V AC, A, Ω , \rightarrow , EVENTS AC+DC, °C (Pt100/1000)	2 times per second
Hz, EVENTS AC	1 time per second

Data Interface

Data Transmission	via optical, infrared interface through the housing
-------------------	--

With Accessory Interface Adapter

Type	RS232C, serial, per DIN 19241
Baud Rate	METRAHit®SI232: 8192 baud, METRAHit®BD232: 9600 baud

Fuses for METRAHit® 23/24/25/26

Fuses for Ranges to 300 mA	FF (UR) 1.6 A/1000 V AC/DC, 6.3 mm x 32 mm, 10 kA breaking capacity at 1000 V with resistive load, protects all current ranges up to 300 mA in combination with power diodes
to 10 A	FF (UR) 16 A/1000 V AC/DC, 10 mm x 38 mm, 30 kA breaking capacity at 1000 V AC/DC with resistive load, protects 3 A and 10 A ranges

Electrical Safety

Protection Class	II per IEC 61010-1/EN 61010-1/ VDE 0411-1	
Overvoltage Category	II	III
Operating Voltage	1000 V	600 V
Contamination Level	2	2
Test Voltage	5.55 kV \sim per IEC 61010-1/EN 61010-1/ VDE 0411-1	

Electromagnetic Compatibility (EMC)

Interference Emission	EN 50081-1:1992 EN 55022:1987 class B
Interference Immunity	EN 50082-1:1992 IEC 801-2:1991 8 kV atmospheric discharge IEC 801-3:1984 3 V/m IEC 801-4:1988 0.5 kV

Ambient Conditions

Operating Temperature Range	-20° C ... +50° C
Storage Temperature Range	-25° C ... +70° C (without batteries)
Relative Humidity	max. 75%, no condensation allowed
Climatic Category	3z/-20/50/75% in compliance with VDI/VDE 3540
Elevation	to 2000 m
Deployment	indoor use only

Mechanical Design

Protection	instrument: IP 50, connector sockets: IP 20
Dimensions	84 mm x 195 mm x 35 mm
Weight	approx. 350 gr. with batteries

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Accessories

F836 Ever-Ready Case

for multimeter (without protective rubber cover) and accessories



F829 Carrying Pouch

for multimeter (with or without GH18 protective rubber cover) and accessories



METRAHit®BD232 Interface Adapter

METRAHit®22/23/24/25/26 multimeters can be adjusted, and their parameters can be configured, with the help of the METRAHit®BD232 bidirectional adapter, and measurement data can be transmitted to a PC. The adapter has no memory of its own, but can be used to read out data from the memory at the METRAHit®22M/26M. It supports all measuring functions and data formats for the METRAHit®20 series, and is included in the user-friendly BD-Pack 1.

METRAHit®SI232 Memory Adapter (for METRAHit®22/23/24/25/26S)

The METRAHit®SI232 memory adapter can be plugged in to hand-held multimeters and allows for on-site storage of measurement data without a PC, as well as subsequent uploading to a PC. Data are synchronized with an integrated clock. The date format is limited to a maximum of 30,000 digits during storage.

Memory:

128 kB (equal to about 100,000 measurement values, can be increased by a factor of 10 to 20 if data compression is used)


Adjustable Sampling Rate:

50 ms to 1 min.

METRAwin®10/METRAHit® Software

METRAwin®10/METRAHit® software (compatible with WINDOWS as of version 3.11) is used to process and display measurement data at a PC. Sampling can be performed manually with an adjustable sampling interval, or in a signal-dependent fashion (with adjustable signal hysteresis). Storage of data in ASCII format can be controlled with two trigger thresholds per measuring channel, or with the system clock.

Y(t) Recorder




Acquired measurement values from a maximum of four freely selectable channels are displayed at the monitor as a line graph with horizontal time axis and are measured with two pointers.

The amplitudes and time axes of stored signals can be zoomed or compressed. The time scale can be displayed


either in absolute time, or in relative measuring time.

High Speed Y(t) Recorder



Rapid changes to measurement values can be recorded with METRAHit®22M/26M and 29S instruments at sampling rates of 1 kHz and 2 kHz respectively.

XY Recorder



Acquired data from two to four freely selectable channels are displayed at the monitor as an XY graph and are measured with the cursor. All scales are freely adjustable, as is the case with all display formats.

Multimeter



Transmitted measurement values from a maximum of four freely selectable channels are displayed at the monitor in the online mode either in digital format with additional analog scale, or as an analog pointer instrument with additional digital display.

Table

Acquired measurement data from up to 10 channels are displayed at the monitor numerically in easy to read tabular form.

Mathematics Functions

High performance mathematics functions are capable of analyzing, linking and displaying measurement data either online or off-line.

Sampling (online)

Sampling can be performed either manually (with the mouse), automatically with an adjustable interval (50 ms to 60 min) or signal-dependent with adjustable signal hysteresis (0 to 500 digits). Data can be controlled with time and window triggers and can be stored to memory as multiple data files.

Measurement Data Processing

High performance calculator and linearization functions allow for further processing of measurement data. For example, mA signals from sensors or transducers can be displayed directly as pressure values, active power and many other quantities.

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Order Information

Designation	Type	Article Number
All multimeters include the KS17-2 measurement cable, operating instructions, DKD calibration certificate and the GH18 protective rubber cover (except for METRAHit® 22S)		
Analog-digital multimeter with signal generator for training and plant operations (current measurement with accessory current clip only)	METRAHit22S	M222A
Same as METRAHit22S but with 128 kByte memory	METRAHit22M	M222B
Analog-digital multimeter with signal generator for energy technology applications with 16 A current range (without 16 A fuse)	METRAHit23S	M223A
Universal analog-digital multimeter with signal generator	METRAHit24S	M224A
TRMS _{AC} analog-digital multimeter with signal generator, V _{AC} to 1 kHz	METRAHit25S	M225A
TRMS _{AC, AC+DC} analog-digital multimeter with signal generator, V _{AC} 15 Hz to 20 kHz	METRAHit26S	M226A
Same as METRAHit26S but with 128 kByte memory	METRAHit26M	M226B
Hardware Accessories		
Mains power pack, 230 V~/4.5 V, 600 mA for METRAHit®22M/26M	NA4/500	Z218A
Protective rubber cover with strap	GH18 ²⁾	GTZ 3212 000 R0001
Voltage measuring probe for electrical power installations of up to 1000 V	KS30	GTZ 3204 000 R0001
High-voltage probe, 3 kV/3 V	HV3	GTZ 3431 011 R0001
High-voltage probe, 30 kV/30 V (for direct voltage only)	HV30	GTZ 3431 001 R0001
Pt100 temperature sensor for surface and immersion measurements, -40 ... +600 °C	Z3409	GTZ 3409 000 R0001
Pt1000 temperature sensor for measurements in gases and liquids, -50 ... +220 °C	TF220	Z102A
Pt100 oven sensor, -50 ... +550 °C	TF550	GTZ 3408 000 R0001
10 adhesive Pt100 temperature sensors, -50 ... +550 °C	TS-Chipset	GTZ 3406 000 R0001
Carrying pouch	F829	GTZ 3301 000 R0003
Ever-ready case	F836	GTZ 3302 000 R0001
Ever-ready case for 2 METRAHit®S with METRAHit®SI232 and accessories	F840	GTZ 3302 001 R0001
Hard case (with room for 1 METRAHit® including GH18, 1 KS17-2 and 1 clip-on current transformer/sensor)	HC20	Z113A
Fuse link (10 ea.)	FF(UR) 1.6A/1000V AC/DC	Z109C
Fuse link (10 ea.)	FF(UR) 16A/1000V AC/DC	Z109B

¹⁾ For METRAHit®23/24/25/26

²⁾ For METRAHit®22S/M

³⁾ For METRAHit®22M/26M, especially recommended

^{D)} Data sheet available

Accessory Clip-On Current Transformers and Sensors		
Electric-Set consisting of: F829 carrying pouch, WZ11A clip-on current transformer (15 ... 180 A~, 1 mA/1 A~) and measurement cable	Electric-Set	GTZ 3236 000 R0001
WZ11A and B clip-on current transformers and sensors ^{D)}		
Clip-on transformers 1 ... 200 A~, 1000:1, 48...65...400 Hz	WZ11A ¹⁾	Z208A
Clip-on current sensor, adjustable, 0.5 ... 20 A~, 1 mV/mA and 5 ... 200 A~, 1 mV/A, 48...65...500 Hz	WZ11B ²⁾	Z208B
WZ12A ... D clip-on current transformers and sensors ^{D)} frequency range: 45...65 ...500 Hz, jaw opening: 15 mm max. cable diameter		
Clip-on current transformer 15 A ... 180 A, 1000:1	WZ12A ¹⁾	Z219A
Clip-on current sensor 10 mA ... 100 A, 0.1 mV/mA	WZ12B ²⁾	Z219B
Clip-on current sensor, adjustable 1 mA ... 15 A, 1 mV/mA and 1 A ... 150 A, 1 mV/A	WZ12C ²⁾	Z219C
Clip-on current transformer 30 mA ... 150 A, 1000:1	WZ12D ¹⁾	Z219D
Clip-on current transformer 4 ... 500 A~, 1 mA~/A~ with cable and protective circuit jaw opening: 30 mm max. cable dia.	Z3511 ¹⁾	GTZ 3511 000 R0001
Clip-on current transformer 0.5 ... 1000 A~, 1 mA~/A~ with cable and protective circuit jaw opening: 54 mm max. cable dia.	Z3512 ¹⁾	GTZ 3512 000 R0001
Clip-on current transformer 1 ... 2000 A~, 1 mA~/A~ with cable and protective circuit jaw opening: 64 mm max. cable dia.	Z3514 ¹⁾	GTZ 3514 000 R0001
Clip-on current sensor, active, with battery (service life: 30 hr.) measuring range: AC 20 A measuring range: DC 30 A frequency range: DC ... 20 kHz output: 10 mV/A jaw opening: 19 mm max. cable dia.	Z201A ²⁾	Z201A
Clip-on current sensor, active, with battery (service life: 50 hr.) measuring ranges: AC 20 A/200 A measuring ranges: DC 30 A/300 A frequency range: DC ... 10 kHz output: 10 mV/A or 1 mV/A jaw opening: 19 mm max. cable dia.	Z202A ²⁾	Z202A
Clip-on current sensor, active, with battery (service life: 50 hr.) measuring ranges: AC 200 A/1000 A measuring ranges: DC 300 A/1000 A frequency range: DC ... 10 kHz output: 1 mV/A jaw opening: 32 mm max. cable dia.	Z203A ²⁾	Z203A
AmpFLEX flexible current sensor ^{D)} 30/300 A, 3 V 300/3000 A, 3 V 1000 A, 1 V 1/10 kA, 1 V	AF033A ¹⁾ AF33A ¹⁾ AF11A ¹⁾ AF101A ¹⁾	Z207A Z207B Z207D Z207C

For additional information concerning accessories see our catalog: *Measuring Instruments and Testers*.

An overview of additional multimeters from the METRAHit® series is included in the brochure: *METRAHit® and METRAWin®*.

METRAHit® 22 ... 26S/M

Analog-Digital Multimeters with Signal Generator

Software Accessories		
1-channel pack consisting of: METRAHit®BD232 bidirectional interface adapter, cable, METRAwin®10/METRAHit® software and installation instructions	BD-Pack 1 ³⁾	Z215A
1-channel memory pack consisting of: METRAHit®SI232 memory adapter, cable, METRAwin®10/METRAHit® software and installation instructions	1-CH. Pack ¹⁾	GTZ 3231 020 R0001
4-channel memory pack consisting of: 4 METRAHit®SI232 memory adapters, cable, METRAwin®10/METRAHit® software and installation instructions	4-CH. Pack ¹⁾	GTZ 3234 020 R0001
Memory adapter for METRAHit®S	SI232 ^{D)}	GTZ 3242 020 R0001
Bidirectional interface adapter	BD232 ³⁾	GTZ 3242 100 R0001
1-channel pack including cable, METRAwin®10/METRAHit® software and installation instructions	Z3231	GTZ 3231 000 R0001
RS232 interface cable, 2 m long, (included with Z3231)	Z3241	GTZ 3241 000 R0001
METRAwin®10/METRAHit® software update and installation instructions	Z3240	GTZ 3240 000 R0001

Printed in Germany • Subject to change without notice

GOSSEN-METRAWATT GMBH
Thomas-Mann-Str. 16-20
90471 Nuremberg, Germany
Phone +49 911 8602-0
Fax +49 911 8602-669
e-mail: info@gmc-instruments.com
<http://www.gmc-instruments.com>

GOSSEN
METRAWATT
CAMILLE BAUER