

10

9

8

7

6

5


4

3

2

1


### 3 POLE ZENSKA / FEMALE



WIDOK OD STRONY DRUTOW  
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	BRAZOWY	BN
3	NIEBIESKI	BU
4	CZARNY	BK


### 4 POLE ZENSKA / FEMALE



WIDOK OD STRONY DRUTOW  
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	BRAZOWY	BN
2	BIALY	WH
3	NIEBIESKI	BU
4	CZARNY	BK

### 5 POLE ZENSKA / FEMALE




WIDOK OD STRONY DRUTOW  
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	BRAZOWY	BN
2	BIALY	WH
3	NIEBIESKI	BU
4	CZARNY	BK
5	SZARY	GY


#### Tablica tolerancji dlugosci Table of length tolerances

Powyzej Over	Do-wlacznie Up to and including	Tolerancja (+) Tolerance
0	600	±10mm
600	1000	+30/-10mm
1000	5000	±25mm
5000	20000	±30mm
20000	>	±50mm

MOLEX PN	WOODHEAD PN	L(mm)
1200795022	W04000E03M003	300
1200798001	W04000E03M050	5000
1200798009	W05000E03M050	5000



WIDOK OD STRONY CZOLA  
FRONT SIDE VIEW



3 = 3-pol	006: L = 0,6 m
4 = 4-pol	020: L = 2 m
5 = 5-pol	040: L = 4 m
	050: L = 5 m
	060: L = 6 m
	100: L = 10 m

#### UWAGI:

1. DLUGOSCI CIECIA I SPECYFIKACJE  
NABIJANIA WG LISTY CIECIA.

#### NOTES:

1. CUTTING LENGTH AND CRIMPING  
SPECIFICATION IN CUTTING LIST.

ORIGINAL RELEASE EC NO: DRWN:MSUSKA CHKD: APPR:	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION	
			mm	INCH	DRAWN BY MSUSKA	DATE 2009/03/09	TITLE FE-ST-PVC-XM-ULTRA LOCK			
			4 PLACES		CHECKED BY	DATE	APPROVED BY MWOLSZCZAK			
			3 PLACES		APPROVED BY DATE		MOLEX MOLEX INCORPORATED		SHEET NO. 1 OF 1	
		2 PLACES		MATERIAL NO. SEE TABLE		DOCUMENT NO. W0X000E03MXXX				
		1 PLACE		ANGULAR						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9

8

7

6

5

4

3

2

1