

D2.5/8.SFT.2L

ABB contact for United
States of America



General Information

Extended Product Type:	D2.5/8.SFT.2L
Product ID:	1SNA290091R2600
EAN:	3472592900919
Catalog Description:	D2.5/8.SFT.2L Spring Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with test socket - Grey
Long Description:	D2.5/8.SFT.2L Spring Terminal Blocks - Fuse - Grey,2.5mm ² RatedCrossSection, 8mm Spacing TH 35-7.5, TH 35-15 Rail

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Spring Terminal Blocks

Ordering

EAN:	3472592900919
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85361010

Dimensions

Product Net Width:	8.0 mm
Product Net Height:	80.0 mm
Product Net Depth:	45.5 mm
Product Net Weight:	14.00 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	176 mm
Package Level 1 Height:	75 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.70000 kg
Package Level 1 EAN:	3472592900919
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	6.800 kg
Package Level 3 Units:	10800 piece
Product Packing Type:	Box

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q4

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity-Main Circuit	Spring Clamp / Flexible 1x 26 ... 12 AWG

UL/CSA: Spring Clamp / Rigid 1x 26 ... 12 AWG
Flammability According to UL94: V0

Additional Information

Ambient Temperature: -5 ... +40 °C
Color: Grey
Connecting Capacity-Main Circuit: Spring Clamp / Flexible 1x 0.12 ... 2.5 mm²
Spring Clamp / Rigid 1x 0.12 ... 4 mm²
Spring Clamp / With Insulated Ferrule 1x 0.5 ... 1.5 mm²
Connection Type: Spring
Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function: Fuse
Gauge Type: A2
IIT Publishing Status: Level 0 - Information enabled
Insulation Material: Polyamide
Mounting on DIN Rail: TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels: 1
Pollution Degree: 3
Product Main Type: D2.5/8.SF.2L
Product Name: Terminal block
Rated Cross-Section: 2.5 mm²
Rated Current (I_n): Main Circuit 6.3 A
Rated Impulse Withstand Voltage (U_{imp}): 8000 V
Rated Voltage (U_r): 630 V
Recommended Screw Driver: 3.5 mm
Spacing: 8 mm
Sub-Function: for 5x20 and 5x25 Fuses
Wire Stripping Length: 9.5 mm

Certificates and Declarations (Document Number)

cUL Certificate: 1SND162000A0204
Declaration of Conformity - CE: 1SND225020C1005
GOST Certificate: 1SND161005A1104
RoHS Information: 1SND230488F0201

Classifications

ETIM 4.0: EC000899 - Fuse terminal block
ETIM 5.0: EC000899 - Fuse terminal block
Object Classification Code: X



