

Labels that stick,
for professional results

ID PAL™
LABELING TOOL



Finally, an affordable label printer designed for the tool box. Not just the office.

ID PAL™ is an affordable, handheld label printer designed for industrial labeling applications. It's the perfect tool for creating small labels used in:

- ▶ Maintenance and engineering
- ▶ Electrical data communications
- ▶ Field service and installation
- ▶ Storerooms and tool cribs
- ▶ Construction
- ▶ Laboratories

At this price, now you can afford to equip everyone on your team with their own labeling tool.

▶ Long-lasting labels that stick...and stay stuck!

High performance Brady ribbons and tapes means that ID PAL labels stick longer. Printed surface resists scratches, smears and fading.

▶ Rugged construction

Weighs only 1.2 lbs. Fits securely in your hand. Designed to withstand harsh environments and rough handling – even a four-foot drop onto concrete!

▶ Extremely easy to use


Anyone can pick it up and start creating labels immediately. Exposed edge makes peeling the label from the liner a snap.

▶ Saves time and money

Six AA-size batteries print up to 3,500 one-inch labels. Less tape waste means two times more labels per cartridge than other labelmakers.



Ask your distributor for a free demo, or learn more by visiting our website at www.bradyidpal.com



ID PAL label



Competitor label

Other Features

- ▶ Quick "drop-in" cartridge loading
- ▶ Multiple line printing
- ▶ 10 preset lengths for wire marking
- ▶ 5 font sizes: (7, 10, 14, 20 & 28 pt)
- ▶ Common electrical and datacomm symbols
- ▶ Built-in industrial cutter
- ▶ Automatic shut-off
- ▶ 6 month warranty (extended to 12 months with user registration)

Specifications

Print method:	Thermal transfer (non smearing)
Weight:	1.2 lbs. (0.55 kg) with batteries and tape cartridge included
Dimensions (L x W x H):	9.0 x 4.5 x 2.5 inches (228.6 x 114.3 x 63.5 mm)
Power source:	6 AA-size batteries or AC with optional adapter
Operating temperature:	40° - 120° F (4° - 49° C)
Agency Approvals:	Printer: FCC Class A approved Tapes: UL and CSA approved

Choose from Three Label Formats



Printer and Accessories

Catalog Number	Description
IDPAL	ID PAL label printer (includes PAL-750-439 label cartridge)
IDPAL-AC	AC adapter
IDPAL-IG	Impact guards
IDPAL-HC	Hard-sided carry case

Label Cartridge Selection Chart

Application*	Material/Color	Label Width/Catalog Numbers			Roll Length	*Application Key
		3/8" / 9mm	1/2" / 12mm	3/4" / 19mm		
	Polyester B430/Black on Clear	PAL-375-430*	PAL-500-430*	PAL-750-430*	21' / 6.4m	*Application Key Wire/Cable/ Curved Surface Textured Surface Highly Textured Surface
	Polyester B423/Black on White	PAL-375-423*	PAL-500-423*	PAL-750-423*	21' / 6.4m	
	Vinyl B439/Black on White	PAL-375-439*	PAL-500-439*	PAL-750-439*	21' / 6.4m	
	Vinyl B439/ Black on Yellow	PAL-375-439YL	PAL-500-439YL	PAL-750-439YL	21' / 6.4m	
	Nylon Cloth B499/Black on White	PAL-375-499*	PAL-500-499*	PAL-750-499*	19' / 5.8m	

www.bradyidpal.com



Need to create larger labels on the go? Check out the ID PAL's big brother – the HandiMark™ Portable Label Maker.

- ▶ Prints on tape up to 2" wide! (Max. text height: 1.7")
- ▶ 7 ribbon colors and 15 vinyl tape colors
- ▶ Reflective, repositionable, and tamper resistant tapes also available
- ▶ Multiple lines and multiple fonts on a single label
- ▶ Wide variety of text formatting features
- ▶ Vertical text, mirror, repeat and batch printing
- ▶ Serial numbering and bar code generation
- ▶ 113 built in safety symbols and industrial pictograms
- ▶ 10,000 character file memory
- ▶ 12 operating languages (including French and Spanish)
- ▶ PC connection (MarkWare™ facility identification software supported)

Catalog Number	Description
42001	HandiMark portable label maker
20709	HandiMark and MarkWare facility ID software

BRADY
 2221 West Camden Road
 P.O.Box 2999
 Milwaukee, WI 53201-2999
 Tel. 1-800-635-7557
 Fax 1-800-445-7556
 www.bradyidpal.com