


Product Datasheet


Double Level Terminal Blocks, 2.5sq.mm

Screw Clamp Double Level Terminal Blocks, 20A, 600V, 22-12 AWG, 0.5-2.5 sq.mm








878-7471



Dimensions in mm



Product Specifications:

Specifications	2.5mm ²
Technical Date	Rated voltage / Rated current / Wire size
UL	600V / 20A / AWG 22-12
CSA	600V / 20A / AWG 22-12
IEC	800V / 24A / 0.5-2.5mm ²
Insulating impulse voltage withstand/pollution degree	8KV / 3
Torque (in -lbs)	5
Clamping Screw (M)	M2.6
Insulation stripping length (mm)	8~10 mm
Net weight per piece	13 g
Material / Available Color (Standard Color: Beige)	 Red Orange Beige Blue Grey White Black
Rail Dimensions	T / W / H (mm)
For TS35x7.5 	5 x 69 x 63.5
For TS35x15 	5 x 69 x 71
Accessories	Cat. No.
End Bracket 	8787553
	8787556
Cross 	8787572
Marking Tags 	8787590