


PCB terminal block - PTSM 0,5/ 4-2,5-V SMD WH R44 - 1814728

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



PCB terminal block, Nominal current: 6 A, Nom. voltage: 250 V, Pitch: 2.5 mm, Number of positions: 4, Connection method: Spring-cage conn., Mounting: SMD/THT/THR, Conductor/PCB connection direction: 90 °

Key commercial data

| | |
|------------------------|--|
| Packing unit | 1 PCE |
| Minimum order quantity | 400 PCE |
| GTIN |  4 046356 760478 |
| Custom tariff number | 85369010 |
| Country of origin | GERMANY |

Technical data

Dimensions

| | |
|-------------|--------|
| Length | 5 mm |
| Height | 9 mm |
| Pitch | 2.5 mm |
| Dimension a | 7.5 mm |
| Pin spacing | 2.5 mm |

General

| | |
|----------------------------------|-------------------|
| Range of articles | PTSM 0,5/..-V-SMD |
| Insulating material group | I |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated surge voltage (II/2) | 2.5 kV |
| Rated voltage (III/3) | 63 V |
| Rated voltage (III/2) | 250 V |
| Rated voltage (II/2) | 320 V |
| Connection in acc. with standard | EN-VDE |

PCB terminal block - PTSM 0,5/ 4-2,5-V SMD WH R44 - 1814728

Technical data

General

| | |
|---|---------------------|
| Nominal current I_N | 6 A |
| Nominal cross section | 0.5 mm ² |
| Maximum load current | 6 A |
| Insulating material | PA |
| Oberfläche Lötpin | Sn |
| Inflammability class according to UL 94 | V0 |
| Stripping length | 6 mm |
| Number of positions | 4 |

Connection data

| | |
|--|----------------------|
| Conductor cross section solid min. | 0.14 mm ² |
| Conductor cross section solid max. | 0.5 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 0.5 mm ² |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm ² |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 0.5 mm ² |
| Conductor cross section AWG/kcmil min. | 26 |
| Conductor cross section AWG/kcmil max | 20 |
| Minimum AWG according to UL/CUL | 26 |
| Maximum AWG according to UL/CUL | 20 |

Classifications

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002643 |
| ETIM 5.0 | EC002637 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 11 | 39121432 |
| UNSPSC 12.01 | 39121432 |
| UNSPSC 13.2 | 39121432 |
| UNSPSC 6.01 | 30211801 |
| UNSPSC 7.0901 | 39121432 |

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141109 |
| eCl@ss 4.1 | 27141109 |

PCB terminal block - PTSM 0,5/ 4-2,5-V SMD WH R44 - 1814728

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.0 | 27141190 |
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27261101 |
| eCl@ss 7.0 | 27440401 |

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>