



PSZFON

HEAD **Flat Head** TYPE **Open End** SECTION **Round** SURFACE **Linear Knurls**

M	l	g	DESCRIPTION	d _h	d _k	k	d	BULK PACK		SMALL PACK		KG /1,000
								ARTICLE	BOX QTY	ARTICLE	BOX QTY	
mm		mm		mm	mm	mm	mm					kg
M3	10.0	0.5 - 3.0	PSZFON-0330	5.0	6.8	0.8	4.9	33218	10,000	33217	500	0.9
M4	10.3	0.3 - 3.0 3.0 - 4.0	PSZFON-0430	6.0	8.8	1.0	5.9	33220	10,000	33219	500	1.3
	11.8									33222	10,000	
M5	12.3	0.3 - 3.0 3.0 - 4.0	PSZFON-0530	7.0	9.8	1.0	6.9	33224	8,000	33223	500	1.8
	15.3									33485	5,000	
M6	14.8	0.5 - 3.0 3.0 - 4.5	PSZFON-0630	9.0	11.8	1.5	8.9	33213	4,000	33225	500	4.0
	16.3									33228	4,000	
M8	16.3	0.5 - 3.0 3.0 - 5.5	PSZFON-0830	11.0	14.8	1.5	10.9	33230	2,000	33229	250	5.7
	18.8									33232	2,000	
M10	17.3	0.5 - 3.0 3.0 - 6.0	PSZFON-1030	12.0	15.8	2.0	11.9	33234	1,500	33233	250	7.0
	22.3									33236	1,500	
M12	23.3	1.0 - 4.0	PSZFON-1240	16.0	21.8	2.0	15.9	33238	800	33237	200	16.8



PSZFCN

HEAD **Flat Head** TYPE **Closed End** SECTION **Round** SURFACE **Linear Knurls**

M	l	g	DESCRIPTION	d _h	d _k	k	d	BULK PACK		SMALL PACK		KG /1,000
								ARTICLE	BOX QTY	ARTICLE	BOX QTY	
mm		mm		mm	mm	mm	mm					kg
M4	15.3	0.3 - 3.0	PSZFCN-0430	6.0	8.8	1.0	5.9	33312	5,000	33311	500	2.1
M5	17.8	0.3 - 3.0	PSZFCN-0530	7.0	9.8	1.0	6.9	32917	5,000	33055	500	2.9
M6	20.3	0.5 - 3.0	PSZFCN-0630	9.0	11.8	1.5	8.9	32918	2,000	32835	500	5.8
M8	24.8	0.5 - 3.0	PSZFCN-0830	11.0	14.8	1.5	10.9	32919	1,500	32836	250	9.8

M=Thread Size; l=Nominal Body Length; g=Grip Range (Min - Max); d_h=Hole Size; d_k=Nominal Head Diameter; k=Nominal Head Thickness; d=Nominal Barrel Diameter