

650 W - 2 Speed Percussion Drill

D21721K / D21720K / D21720*



Very compact and lightweight to enhance user comfort
Two speed gearbox for increased torque and more versatility
Variable speed control with forward and reverse mode to suit different materials
Dust sealed switch for added durability

Standard Equipment: Keyless Chuck, kitbox, multi position side-handle, depth stop

Chuck Capacity	1.5-13 mm
Power Input	650 Watts
Power Output	325W Watts
Max Torque	30/12 Nm
No Load Speed	0-1100 / 0-2600 rpm
Blows per Minute	0-19000 / 0-44200 bpm
Max. Drilling Capacity [Wood]	40/25 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	16 mm
Spindle Thread	1/2" x20 U.N.F.
Weight	2.1 kg
Length x Height	330 x 199 mm

*Available with heavy duty carrying case as K version and with keyed chuck as D21720



770 W - 2 Speed Percussion Drill

D21805 / D21805K / D21805KS*



Two speed gearbox for increased torque
Improved drilling performance due to new motor wind
Improved ergonomics with new polymer gear case
New gear design to give improved life

Standard Equipment: Keyed chuck, Chuck key, Multi-position side handle, Depth stop

Chuck Capacity	1.5-13 mm
Power Input	770 Watts
Power Output	425 Watts
Max Torque	40/20 Nm
No Load Speed	0-1100 / 0-2700 rpm
Blows per Minute	0-18700 / 0-45900 bpm
Max. Drilling Capacity [Wood]	35 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	2.3 kg
Length x Height	352 x 199 mm

*Available with heavy duty carrying case as K version and with keyless chuck as S version



950 W - 2 Speed Percussion Drill

DWD522KS



Improved drilling performance from powerful new motor gives improved performance in heavy duty applications
Innovative mode selection collar allows intuitive control for optimal performance
Two speed gearbox for increased versatility
Mechanical clutch increases user control and protection

Standard Equipment: multi-position side handle, depth stop, Heavy Duty Carrying Case.

Chuck Capacity	1.5-13 mm
Power Input	950 Watts
Power Output	415 Watts
Max Torque	40/20 Nm
No Load Speed	0-1250 0-3500 rpm
Blows per Minute	0-56000 bpm
Max. Drilling Capacity [Wood]	40 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	2.8 kg
Length x Height	370 x 210 mm



1100 W - 2 Speed Pistol Percussion Drill

DWD524KS



Improved drilling performance from powerful new motor gives improved performance in heavy duty applications
Innovative mode selection collar allows intuitive control for optimal performance
Two speed gearbox for increased versatility
Mechanical clutch increases user control and protection

Standard Equipment: multi-position side handle, depth stop, Heavy Duty Carrying Case.

Chuck Capacity	1.5-13 mm
Power Input	1100 Watts
Power Output	540 Watts
Max Torque	40/20 Nm
No Load Speed	0-1200 0-3500 rpm
Blows per Minute	0-5600 bpm
Max. Drilling Capacity [Wood]	40 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	2.8 kg
Length x Height	370 x 210 mm



EXTREME MASONRY DRILL BITS



Extreme DEWALT Masonry Drill Bits offer class-leading percussion drilling performance:

- Last up to 2x longer than a standard masonry bit
- Optimum carbide grade maximizes durability
- Ideal for drilling for anchors, plastic fixings, and pipe-work clearance holes

For the complete range of EXTREME Masonry drill bits see page 105

1100 W - 2 Speed Mid-Handle Percussion Drill

DWD525KS



Improved drilling performance from powerful new motor gives improved performance in heavy duty applications
Two speed gearbox for increased versatility
Mechanical clutch increases user control and protection
Innovative mode selection collar allows intuitive control for optimal performance

Standard Equipment: multi-position side handle, depth stop, Heavy Duty Carrying Case.

Chuck Capacity	1.5-13 mm
Power Input	1100 Watts
Power Output	540 Watts
Max Torque	40/20 Nm
No Load Speed	0-1250 0-3500 rpm
Blows per Minute	0-56000 bpm
Max. Drilling Capacity [Wood]	40 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	2.8 kg
Length x Height	345 x 225 mm



1300 W - 2 Speed Percussion Drill

DWD530KS



Improved drilling performance from powerful new motor gives improved performance in heavy duty applications
Two speed gearbox for increased versatility
Electro-Mechanical clutch increases user control and protection
Innovative mode selection collar allows intuitive control for optimal performance

Standard Equipment: multi-position side handle, depth stop, Heavy Duty Carrying Case.

Chuck Capacity	1.5-13 mm
Power Input	1300 Watts
Power Output	680 Watts
Max Torque	40/20 Nm
No Load Speed	0-1100 0-2700 rpm
Blows per Minute	0-56000 bpm
Max. Drilling Capacity [Wood]	40 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	2.8 kg
Length x Height	370 x 215 mm



2 Speed Dry Diamond Drill with 16mm Keyed Chuck

D21570K



New motor gives improved performance in applications with dry core bits up to 127 mm in bricks or soft masonry
Two speed gearbox for increased versatility when drilling in wood, metal and concrete with standard drill bits
Heavy duty 16mm keyless steel chuck allows quick bit change whilst offering excellent bit retention
Innovative mode selection collar allows intuitive control for optimal performance

Standard Equipment: Multi-Position side handle, Depth Stop, Heavy Duty Carrying Case

Spindle Thread	1/2" X 20 U.N.F.
Power Input	1300 Watts
Power Output	680 Watts
No Load Speed	0-1100 0-2700 rpm
Max. Drilling Capacity [Masonry]	100 mm
Weight	2.4 kg
Length x Height	352 x 215 mm



10mm 0-2800rpm Rotary Drill

DWD014 / DWD014S*



Compact design enables comfortable one handed use and allows access to tight spaces
Low weight ensures the drill is easy to use and it reduces user fatigue
Variable speed dial switch ensures control to suit different hole sizes in different materials
Trigger sensitive variable speed switch allows a user to drill slowly for precision accuracy when starting to drill a hole

Standard Equipment: Chuck key

Chuck Capacity	1.0-10 mm
Power Input	550 Watts
Power Output	269 Watts
Max Torque	7.9 Nm
No Load Speed	0-2800 rpm
Max. Drilling Capacity [Wood]	25 mm
Max. Drilling Capacity [Steel]	10 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	1.34 kg
Length x Height	225 x 170 mm

*Available with keyless chuck as S version



10 mm Rotary Drill with Keyed Chuck

DWD 112 / DWD 112S*



Rubber grip gives maximum comfort to the user while drilling
Ideal for use in a woodworking or light metal fabrication workshop to drill small holes into wood or sheet metal
Size, balance and weight designed for one handed operation
Variable speed switch control to suit different materials

Chuck Capacity	1.0-10 mm
Power Input	701 Watts
Power Output	358 Watts
Max Torque	10.9 Nm
No Load Speed	0-2500 rpm
Max. Drilling Capacity [Wood]	25 mm
Max. Drilling Capacity [Steel]	10 mm
Spindle Thread	1/2" X 20 U.N.F.
Weight	1.8 kg
Length x Height	230 x 190 mm

*Available with keyless chuck as S version