





Main

Range	TeSys
Product name	TeSys F
Product or component type	Contacteur
Device short name	LC1F
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	<= 460 V DC <= 1000 V AC 50/60 Hz
[Ie] rated operational current	500 A (<= 55 °C) at <= 440 V AC AC-3 700 A (<= 40 °C) at <= 440 V AC AC-1
Motor power kW	335 kW at 660...690 V AC 50/60 Hz 147 kW at 220...240 V AC 50/60 Hz 355 kW at 500 V AC 50/60 Hz 335 kW at 1000 V AC 50/60 Hz 295 kW at 440 V AC 50/60 Hz 280 kW at 415 V AC 50/60 Hz 250 kW at 380...400 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	700 A at <= 40 °C
Irms rated making capacity	5000 A AC conforming to IEC 60947-4-1
Rated breaking capacity	4000 A conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	1200 A <= 40 °C 10 min 1500 A <= 40 °C 3 min 2400 A <= 40 °C 1 min 3200 A <= 40 °C 30 s 4200 A <= 40 °C 10 s
Associated fuse rating	800 A gG at <= 440 V 500 A aM at <= 440 V
Average impedance	0.18 mOhm at 50 Hz - Ith 700 A
[Ui] rated insulation voltage	1500 V conforming to VDE 0110 group C 1000 V conforming to IEC 60947-4-1
Power dissipation per pole	45 W AC-3 88 W AC-1
Mounting support	Plate
Standards	EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038
Product certifications	BV CCC CSA DNV GL RINA RMRoS UL LROS
Connections - terminals	Power circuit : bar 2 x (40 x 5 mm) Power circuit : lugs-ring terminals 2 cable(s) 240 mm ²
Tightening torque	Power circuit : 35 N.m

Environment

IP degree of protection	IP20 front face with shrouds (ordered separately) conforming to VDE 0106 IP20 front face with shrouds (ordered separately) conforming to IEC 60529
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 9 Gn for 11 ms Vibrations contactor open 2 Gn, 5...300 Hz
Height	238 mm
Width	233 mm
Depth	232 mm
Product weight	9.75 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual