



R4E355AN Series Motorized Impeller

Ø 355mm Backward Curved 3D Impeller

- These new backward curved centrifugal fans feature twofold-curved blades. These impellers have improved efficiency and reduced noise.
- Impeller completely made of aluminium.
- Maintenance-free ball bearings.
- Insulation class "F". Cable exit: variable. Direction of rotation is CW as seen from intake side.
- UL, CSA, VDE approvals on most models, please contact application engineering.
- Recommended inlet ring: 35561-2-4013.

Part Number	Curve	CFM @ D	VAC	Hertz	Power (W)	dBA	Max Amb. Temp. C	Capacitor (µF)	Speed (RPM)	Wgt. (lbs)
R4E355-AN09-10	1	2090	115	60	390	71	50	30	1670	15
R4E355-AN11-11	1	2090	230	60	410	71	50	7	1680	15
R4E355-AN07-09	1	2090	277	60	400	71	50	5	1670	15

