

Wiha T-handle torque tools.

T-handle torque tools with scale.



2893 TorqueVario®-STplus T-handle torque tool.
Torque can be set via numerical scale.
With slipping clutch.

Handle: Window scale displays torque value numerically. Torque infinitely adjustable with Torque-Setter setting tool (also supplied). Soft-grip T-handle for extreme comfort and optimal torque transmission. Audible and perceptible click when the pre-set torque has been attained.

Standards: Based on EN ISO 6789, BS EN 26789, ASME B107.14M.
Accuracy: ±6%, traceable to national standards.
Application: For applications where recommended torque settings are important. Use in combination with an interchangeable 6 mm blade for Wiha T-handle torque tools.
Extra: Delivered in practical plastic box, incl. factory calibration certificate.

Order-No.	Nm	⌀	•	•	•
29233 1	5-14	6	56	120	1



2893 S01 TorqueVario®-STplus T-handle torque tool set, 11 pcs.
With bit universal holder, 6 TORX®/ hex Standard bits and 2 adapter blades for nuts.

Handle: Model 5-14 Nm. Window scale displays torque value numerically. Torque infinitely adjustable with Torque-Setter setting tool (also supplied). Soft-grip T-handle for extreme comfort and optimal torque transmission.

Standards: Based on EN ISO 6789, BS EN 26789, ASME B107.14M.
Accuracy: ±6%, traceable to national standards.
Application: For applications where recommended torque settings are important.
Extra: Delivered in robust metal box, incl. factory calibration certificate.

Order-No.	Series	•
29234 8	2893 S01	1
	2893	TorqueVario®-STplus T-handle torque tool, Model 5-14 Nm
	289-900	Torque-Tplus Setter
	2899	Torque-Tplus adapter blade 1/4" 3/8"
	2899	Torque-Tplus bit quick release holder 1/4"
	7015 Z	T25x25 T30x25 T40x25
	7013 Z	4,0x25 5,0x25 6,0x25

Pre-set T-handle torque tools.



2891 TorqueFix®-Tplus T-handle torque tool.
With a fixed torque value pre-set by Wiha.
Automatic release.
With slipping clutch.

Handle: Soft-grip T-handle for extreme comfort and optimal torque transmission. Audible and perceptible click when the pre-set torque has been attained.

Standards: Based on EN ISO 6789, BS EN 26789, ASME B107.14M.
Accuracy: ±6%, traceable to national standards.
Application: For applications where recommended torque settings are important. Use in combination with an interchangeable 6 mm blade for Wiha T-handle torque tools.
Extra: Delivered in practical plastic box, incl. factory calibration certificate.

Order-No.	Nm	⌀	•	•	•
29228 7	6	6	56	120	1
29229 4	8	6	56	120	1
29230 0	10	6	56	120	1
29231 7	12	6	56	120	1
29236 2	12.5	6	56	120	1
29232 4	14	6	56	120	1

Torque-Tplus Setter and interchangeable blades.



289-900 Torque-Tplus Setter.
Setting tool for variable T-handle torque tools.
Included in every T-handle torque tool delivery.

Blade: Octagonal profile with drilled tip, through hardened, zinc-plated.
Handle: Made of impact resistant cellulose acetate.

Order-No.	•	•	•
28691 0	80	150	1



2899 Torque-Tplus TORX® interchangeable blade.
For T-handle torque tools.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time. Colour-coding: dark green.

Application: For applications where recommended torque settings are important.

Order-No.	•	•	•	•	max. Nm	max. in.lbs.	•
28734 4	T15	6	130	53	6	53	10
28735 1	T20	6	130	53	10	88	10
28736 8	T25	6	130	53	15	132	10
28737 5	T27	6	130	53	15	132	10
28738 2	T30	6	130	53	15	132	10
28739 9	T40	6	130	53	15	132	10



2899 Torque-Tplus TORX PLUS® interchangeable blade.
For T-handle torque tools.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time. Colour-coding: light green.

Application: For applications where recommended torque settings are important.

Order-No.	•	•	•	•	max. Nm	max. in.lbs.	•
28740 5	15IP	6	130	53	8	70	10
28741 2	20IP	6	130	53	13	115	10
28742 9	25IP	6	130	53	15	132	10
28743 6	27IP	6	130	53	15	132	10
28744 3	30IP	6	130	53	15	132	10
28745 0	40IP	6	130	53	15	132	10

Interchangeable blades.



2899 Torque-Tplus hex interchangeable blade.
For T-handle torque tools.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time. Colour-coding: red.

Application: For applications where recommended torque settings are important.

Order-No.	•	•	•	•	max. Nm	max. in.lbs.	•
28746 7	3	6	130	53	9	79	10
28747 4	4	6	130	53	15	132	10
28748 1	5	6	130	53	15	132	10
28749 8	6	6	130	53	15	132	10



2899 Torque-Tplus bit quick release holder.
For T-handle torque tools.
Suitable for C 6.3 and E 6.3 (1/4") bits.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Sleeve: Quick release bit holder for T-handle torque tools. Enables ultra fast bit changes.

Application: For controlled turning of screws with bits at a prescribed torque.

Order-No.	•	•	•	•	•	•
28758 0	1/4	6	125	11	105 mm visible length	10



2899 Torque-Tplus adapter blade.
For T-handle torque tools.
Suitable for 1/4" resp. 3/8" square sockets.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Head: Nickel-plated, spring-mounted ball.

Application: For controlled turning of screws with nuts at a prescribed torque.

Order-No.	•	•	•	•	•	•
28756 6	1/4	6	120	53	100 mm visible length	10
28757 3	3/8	6	120	53	100 mm visible length	10