



### Main

|                          |                   |
|--------------------------|-------------------|
| Relay application        | Remote control    |
| Range of product         | DuoLine           |
| Device short name        | TL'clic           |
| Poles description        | 2P                |
| Pole contact composition | 2 NO              |
| [In] rated current       | 16 A              |
| Network type             | AC                |
| Network frequency        | 50/60 Hz          |
| Control circuit voltage  | 230 V AC 50/60 Hz |
| Supply inrush power      | 19 VA             |
| 9 mm pitches             | 2                 |

### Complementary

|  |  |
|--|--|
| [Ue] rated operational voltage               | 250 V AC 50/60 Hz  |
| Control type                                 | Remote control<br>Toggle   |
| Control signal type                          | Impulse  |
| Switching frequency                          | 5 switching operation/minute   |
| Impulse duration                             | 50 ms  |
| Remote control type                          | Illuminated pushbutton 3 mA  |
| Local signalling                             | ON/OFF indication  |
| Mounting mode                                | Fixed  |
| Mounting support                             | 35 mm symmetrical DIN rail   |
| Comb busbar distribution block compatibility | Upside: Bar'clic   |
| Height                                       | 60 mm  |
| Width  | 18 mm  |
| Depth  | 84 mm  |
| Connections - terminals                      | Prefabricated connection<br>Tunnel type terminals 2 cable(s) 1.5 mm <sup>2</sup> rigid<br>Tunnel type terminals 2 cable(s) 1.5 mm <sup>2</sup> flexible with<br>Tunnel type terminals 2 cable(s) 1.5 mm <sup>2</sup> flexible without<br>Tunnel type terminals 1 cable(s) 4 mm <sup>2</sup> flexible without |
| Auxiliary connection terminal                | Control circuit: tunnel type terminals 2 cable(s) rigid 0.5...1.5 mm <sup>2</sup><br>Control circuit: tunnel type terminals 2 cable(s) flexible 0.5...1.5 mm <sup>2</sup> with cable end<br>Control circuit: tunnel type terminals 2 cable(s) flexible 0.5...1.5 mm <sup>2</sup> without cable end           |

### Environment

|                          |           |
|--------------------------|-----------|
| Product certifications   | NF        |
| RoHS EUR conformity date | 0633      |
| RoHS EUR status          | Compliant |