

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	APVD
			A	REVISED PER 0S14-0150-05.	04OCT2005	REH JGH

1. INTERFACE PER MIL-C-39012.
2. SEE INSTRUCTION SHEET 408-2987-9.



RECOMMENDED STRIP LENGTHS
SCALE NTS

A	58483-1	.105	HX4-1637	414013-3	1-413889-5	9-414364-2	RG 178,196	5414363-8
B	58483-1	.128	HX4-1637	414013-3	1-413889-3	9-414364-1	RG 174,188,316	5414363-5
C	58483-1	.151	HX4-1637	414013-3	1-413889-4	9-414364-0	RG 174,188,316(ALL DBL SHIELDED)	5414363-4
B	58483-1	.128	HX4-1637	414013-3	1-413889-3	9-414364-0	RG 174,188,316	5414363-3
POSITION LETTER	AMP DIE SET	HEX SIZE	DANIELS DIE SET	3 END CAP QTY=1	2 FERRULE QTY=1	1 PLUG ASSY QTY=1	CABLE	PART NO
AMP PRO-CRIMPER FOR BRAID CRIMP				M 22520/5-01 FOR BRAID CRIMP				
TOOLING INFORMATION				THIS DRAWING IS A CONTROLLED DOCUMENT.				
DIMENSIONS: mm [INCHES]				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± 0.130 [.005] 4 PLC ± - ANGLES ± 1°				
MATERIAL				FINISH				
-				-				
CUSTOMER DRAWING						DWN J. HAVENER 23MAR2005 CHK J. HAVENER 23MAR2005 APVD J. HAVENER 23MAR2005 PRODUCT SPEC APPLICATION SPEC WEIGHT -	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
						NAME	PLUG,RTANG CRIMP,HEX CRIMP,SMB	
						SIZE	CAGE CODE	DRAWING NO
						A3	00779	C-5414363
						RESTRICTED TO		
						-		
						SCALE	SHEET	REV
						8:1	1 of 1	A