

DETAILS

Product Number	F14487_FLORENCE-1R-MAXI-WG
Family	Florence
Type	Lens
Color	clear
Diameter	21,65 x 286 mm
Height	11.04 mm
Style	rectang
Optic Material	PMMA
Holder Material	
Fastening	
Status	ready
ROHS Compliant	Yes
Date Updated	22/05/2015



OPTICAL PROPERTIES


LED	Viewing Angle	Light Beam	Efficiency	cd/lm	Connector
Luxeon 3030 2D	Asymmetric deg	Asymmetric	91 %	1.000	-
XP-G	Asymmetric deg	Asymmetric	92 %	1.400	-
Fortimo LED Line 1ft 1100lm 8x0 1R xV2	Asymmetric deg	Asymmetric	94 %	0.940	-
Duris S5 (2 chip)	Asymmetric deg	Asymmetric	91 %	1.100	-
Oslon SSL 80	Asymmetric deg	Asymmetric	93 %	1.700	-
XP-E2	Asym deg	Asymmetric	94 %	1.470	-
XP-E	Asymmetric deg	Asymmetric	91 %	1.700	-
LUXEON Rebel ES	Asymmetric deg	Asymmetric	92 %	1.300	-
LUXEON T	sim: Asymmetric	Asymmetric	sim: 90 %	sim: 0.000	-
NCSxx19B	Asymmetric deg	Asymmetric	91 %	1.300	-
XB-H	sim: Asymmetric	Asymmetric	sim: 90 %	sim: 0.000	-
NF2x757A	sim: Asymmetric	Asymmetric	sim: 89 %	sim: 0.000	-
XQ-E	Asym deg	Asymmetric	94 %	1.580	-
XP-G2	Asymmetric deg	Asymmetric	93 %	1.500	-
LUXEON TX	sim: Asymmetric	Asymmetric	sim: 91 %	sim: 0.000	-
LUXEON R	sim: Asymmetric	Asymmetric	sim: 88 %	sim: 0.000	-
LUXEON Rebel	Asymmetric deg	Asymmetric	92 %	1.400	-
LUXEON A	Asymmetric deg	Asymmetric	92 %	1.400	-
LUXEON Z ES	Asym deg	Asymmetric	94 %	1.300	-
NVSxx19B/NVSxx19C	Asymmetric deg	Asymmetric	91 %	1.200	-

H G F E D C B A

4

4


285.6



Left view

3

3





Top view

2

2

Highly recommended to cover wall-side wire outlet with light fixture to avoid reflections from components.
Cover max level = lens top level to avoid blocking light from the wall.




INDEX	PART NO	DESCRIPTION	MATERIAL	COLOUR
1	C14487	FLORENCE-1R-MAXI-WG	PMMA	clear

Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures: class M
According to DIN ISO 2768-2
Form and position: class L

LEDiL LediL Oy
Salorankatu 10
FIN 24240 SALO
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE
C14487_FLORENCE-1R-MAXI-WG

This drawing is the property of LEDiL Oy. It may not be reproduced, copied or communicated without a written agreement with LEDiL Oy.


SIZE	PART NUMBER
A3	C14487

SCALE	1:1	WEIGHT		SHEET	1/1
-------	-----	--------	--	-------	-----

H G B A

Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_3030_2D) / LDC (Linear)


Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_3030_2D)
Lamps: 1 x Luxeon_3030_2D_x22_(L130-4080003000W21)
_1602.96lm@200mA_CCT=4000K_P=12.8W_I=0.2A




Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G)

Lamps: 1 x Cree_XP-G_x12_(XPGWHT-L1-CWPI-00BE7)_795.108lm@250mA_P=8.6W_I=0.25A




Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(Fortimo_LED_line_1ft_1100lm_840_1R_LV2)
Lamps: 1 x Philips_Fortimo_LED_line_1ft_1100lm_840_1R_LV2_1067.99lm@250mA_P=8.04281W_η=0.2498mA



Ledil F14487_FLORENCE-1R-MAXI-WG_(Duris_S5-2chip) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Duris_S5-2chip)


Lamps: 1 x Osram_Duris_S5-2chip_x22_1225.67lm@150mA_P=9.55W_I=150mA




Ledil F14487_FLORENCE-1R-MAXI-WG_(SSL80) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(SSL80)

Lamps: 1 x Osram_Oslon_SSL80_x12_(LCW_CQ7P.EC)_838.967lm@250mA_P=9.3W_I=0.25A




Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(XP-E2)_2
Lamps: 1 x (XP-E2_florence)_881.969lm@250mA_P=8.62385W_I=0.2498mA



Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-E) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-E)


Lamps: 1 x Cree_XP-E_x12_(XPEWHT-L1-3C0-Q5-0-06)_941.258lm@250mA_P=9W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel-ES) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel-ES)


Lamps: 1 x Luxeon_Rebel-ES_x12_(LXML-PWC2)_1141.53lm@250mA_P=8.65W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(NCSxx19B) / LDC (Linear)


Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(NCSxx19B)

Lamps: 1 x Nichia_NCSxx19B_x12_(NCSL219B)_941.258lm@250mA_P=8.9W_I=0.25A



Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(XQ-E)


Lamps: 1 x CREE_XQ-E_(XQEAWT-0-7B1-Q40-0H-00001)_872.003lm@250mA_P=8.58163W_I=249.8mA



Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G2) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G2)


Lamps: 1 x Cree_XP-G2_x12_(XPGBWT-01-4A0-R3-0-01)_1206.16lm@250mA_P=8.5W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel) / LDC (Linear)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel)


Lamps: 1 x Luxeon_Rebel_x12_(LXM8-PW30)_763.184lm@250mA_P=8.3W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_A) / LDC (Linear)


Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_A)

Lamps: 1 x Luxeon_A_x12_(LXH8-PW30)_834.791lm@250mA_P=8.3W_I=0.25A



Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(LUXEON_Z-ES)


Lamps: 1 x LUXEON_Z-ES_(LXZ2-3080-3)_882.543lm@250mA_CCT=3000K_P=8.27363W_I=249.8mA



Ledil F14487_FLORENCE-1R-MAXI-WG_(NVSxx19B) / LDC (Linear)


Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(NVSxx19B)

Lamps: 1 x Nichia_NVSxx19B_x12_(NVSL219B)_1045.07lm@250mA_P=8.6W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_3030_2D) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_3030_2D)
Lamps: 1 x Luxeon_3030_2D_x22_(L130-4080003000W21)
_1602.96lm@200mA_CCT=4000K_P=12.8W_I=0.2A




cd/klm
— C0 - C180 — C90 - C270

$\eta = 91\%$


Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G)

Lamps: 1 x Cree_XP-G_x12_(XPGWHT-L1-CWPI-00BE7)_795.108lm@250mA_P=8.6W_I=0.25A



Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(Fortimo_LED_line_1ft_1100lm_840_1R_LV2)
Lamps: 1 x Philips_Fortimo_LED_line_1ft_1100lm_840_1R_LV2_1067.99lm@250mA_P=8.04281W_I=0.2498mA



cd/klm


— C0 - C180 — C90 - C270

$\eta = 94\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(Duris_S5-2chip) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Duris_S5-2chip)

Lamps: 1 x Osram_Duris_S5-2chip_x22_1225.67lm@150mA_P=9.55W_I=150mA



cd/klm


— C0 - C180 — C90 - C270

$\eta = 91\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(SSL80) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(SSL80)

Lamps: 1 x Osram_Oslon_SSL80_x12_(LCW_CQ7P.EC)_838.967lm@250mA_P=9.3W_I=0.25A



cd/klm


— C0 - C180

— C90 - C270

$\eta = 93\%$

Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(XP-E2)_2

Lamps: 1 x (XP-E2_florence)_881.969lm@250mA_P=8.62385W_I=0.2498mA



cd/klm


— C0 - C180 — C90 - C270

$\eta = 95\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-E) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-E)

Lamps: 1 x Cree_XP-E_x12_(XPEWHT-L1-3C0-Q5-0-06)_941.258lm@250mA_P=9W_I=0.25A



cd/klm


— C0 - C180 — C90 - C270

$\eta = 91\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel-ES) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel-ES)


Lamps: 1 x Luxeon_Rebel-ES_x12_(LXML-PWC2)_1141.53lm@250mA_P=8.65W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(NCSxx19B) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(NCSxx19B)

Lamps: 1 x Nichia_NCSxx19B_x12_(NCSL219B)_941.258lm@250mA_P=8.9W_I=0.25A




cd/klm

— C0 - C180 — C90 - C270

$\eta = 91\%$

Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(XQ-E)

Lamps: 1 x CREE_XQ-E_(XQEAWT-0-7B1-Q40-0H-00001)_872.003lm@250mA_P=8.58163W_I=249.8mA



cd/klm


— C0 - C180 — C90 - C270

$\eta = 95\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G2) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(XP-G2)

Lamps: 1 x Cree_XP-G2_x12_(XPGBWT-01-4A0-R3-0-01)_1206.16lm@250mA_P=8.5W_η=0.25A



cd/klm


— C0 - C180 — C90 - C270

η = 93%

Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Rebel)


Lamps: 1 x Luxeon_Rebel_x12_(LXM8-PW30)_763.184lm@250mA_P=8.3W_I=0.25A



Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_A) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(Luxeon_A)

Lamps: 1 x Luxeon_A_x12_(LXH8-PW30)_834.791lm@250mA_P=8.3W_I=0.25A




cd/klm

— C0 - C180 — C90 - C270

$\eta = 92\%$

Luminaire: LEDiL Oy F14487_FLORENCE-1R-MAXI-WG_(LUXEON_Z-ES)

Lamps: 1 x LUXEON_Z-ES_(LXZ2-3080-3)_882.543lm@250mA_CCT=3000K_P=8.27363W_I=249.8mA



cd/klm


— C0 - C180 — C90 - C270

$\eta = 94\%$

Ledil F14487_FLORENCE-1R-MAXI-WG_(NVSxx19B) / LDC (Polar)

Luminaire: Ledil F14487_FLORENCE-1R-MAXI-WG_(NVSxx19B)

Lamps: 1 x Nichia_NVSxx19B_x12_(NVSL219B)_1045.07lm@250mA_P=8.6W_I=0.25A



cd/klm

— C0 - C180

— C90 - C270

$\eta = 91\%$

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.