



# Intel® Edison Module

Hardware Guide

---

*September 2014*

*Revision 002*



**Notice:** This document contains information on products in the design phase of development. The information here is subject to change without notice. Do not finalize a design with this information.

INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

A "Mission Critical Application" is any application in which failure of the Intel Product could result, directly or indirectly, in personal injury or death. SHOULD YOU PURCHASE OR USE INTEL'S PRODUCTS FOR ANY SUCH MISSION CRITICAL APPLICATION, YOU SHALL INDEMNIFY AND HOLD INTEL AND ITS SUBSIDIARIES, SUBCONTRACTORS AND AFFILIATES, AND THE DIRECTORS, OFFICERS, AND EMPLOYEES OF EACH, HARMLESS AGAINST ALL CLAIMS COSTS, DAMAGES, AND EXPENSES AND REASONABLE ATTORNEYS' FEES ARISING OUT OF, DIRECTLY OR INDIRECTLY, ANY CLAIM OF PRODUCT LIABILITY, PERSONAL INJURY, OR DEATH ARISING IN ANY WAY OUT OF SUCH MISSION CRITICAL APPLICATION, WHETHER OR NOT INTEL OR ITS SUBCONTRACTOR WAS NEGLIGENT IN THE DESIGN, MANUFACTURE, OR WARNING OF THE INTEL PRODUCT OR ANY OF ITS PARTS.

Intel may make changes to specifications and product descriptions at any time, without notice. Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "undefined." Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them. The information here is subject to change without notice. Do not finalize a design with this information.

Intel software products are copyrighted by and shall remain the property of Intel Corporation. Use, duplication, or disclosure is subject to restrictions stated in Intel's Software License Agreement, or in the case of software delivered to the government, in accordance with the software license agreement as defined in FAR 52.227-7013.

The products described in this document may contain design defects or errors known as errata which may cause the product to deviate from published specifications. Current characterized errata are available on request.

The code names presented in this document are only for use by Intel to identify products, technologies, or services in development that have not been made commercially available to the public, i.e., announced, launched, or shipped. They are not "commercial" names for products or services and are not intended to function as trademarks.

Contact your local Intel sales office or your distributor to obtain the latest specifications and before placing your product order.

Copies of documents which have an order number and are referenced in this document, or other Intel literature may be obtained by calling 1-800-548-4725 or by visiting Intel's website at <http://www.intel.com/design/literature.htm>.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See [http://www.intel.com/products/processor\\_number](http://www.intel.com/products/processor_number) for details.

Intel, the Intel logo, and Intel Atom are trademarks of Intel Corporation in the United States and other countries.

\* Other brands and names may be claimed as the property of others.

Copyright © 2014 Intel Corporation. All rights reserved.



# Contents

|          |                                                                      |           |
|----------|----------------------------------------------------------------------|-----------|
| <b>1</b> | <b>Introduction .....</b>                                            | <b>6</b>  |
| 1.1      | References .....                                                     | 6         |
| <b>2</b> | <b>High-Level Functional Description .....</b>                       | <b>7</b>  |
| 2.1      | Block diagram .....                                                  | 8         |
| 2.2      | Module photos .....                                                  | 8         |
| <b>3</b> | <b>Component and Subsystem Details.....</b>                          | <b>10</b> |
| 3.1      | Intel® Atom™ processor Z34XX.....                                    | 10        |
| 3.2      | Wi-Fi / BT module.....                                               | 10        |
| 3.3      | Managed NAND (eMMC) flash .....                                      | 10        |
| 3.4      | DDR SDRAM.....                                                       | 10        |
| 3.5      | Power management IC (PMIC).....                                      | 11        |
| 3.6      | USB 2.0 transceiver ULPI interface .....                             | 11        |
| 3.7      | Integrated chip antenna or u.FL connector for external antenna ..... | 11        |
| 3.8      | 70-pin interface connector.....                                      | 12        |
| <b>4</b> | <b>External Interfaces on 70-Pin Connector .....</b>                 | <b>15</b> |
| 4.1      | I <sup>2</sup> C Interfaces .....                                    | 15        |
| 4.2      | SD card interface .....                                              | 15        |
| 4.3      | UART interfaces .....                                                | 15        |
| 4.4      | SPI interface.....                                                   | 16        |
| 4.5      | I2S interface.....                                                   | 16        |
| 4.6      | PWM .....                                                            | 17        |
| 4.7      | GPIO .....                                                           | 17        |
| 4.8      | USB.....                                                             | 18        |
| 4.9      | Clocks .....                                                         | 18        |
| 4.10     | System reset.....                                                    | 18        |
| 4.11     | Special software recovery .....                                      | 19        |
| 4.12     | Power input and output.....                                          | 19        |
| 4.13     | V_VBAT_BKUP.....                                                     | 19        |
| <b>5</b> | <b>Powering Edison .....</b>                                         | <b>20</b> |
| 5.1      | Main power supply VSYS .....                                         | 20        |
| 5.2      | Lithium-polymer battery direct attach.....                           | 20        |
| 5.3      | Lithium-polymer battery with diode or FET isolation.....             | 21        |
| 5.4      | Connection to USB VBUS.....                                          | 21        |
| 5.5      | Cold boot sequence.....                                              | 22        |
| <b>6</b> | <b>Edison Mechanicals .....</b>                                      | <b>23</b> |
| <b>7</b> | <b>Layout.....</b>                                                   | <b>24</b> |
| 7.1      | Antenna keepout.....                                                 | 24        |
| 7.2      | Layout SD card, I2S, SPI, I2C.....                                   | 24        |
| 7.3      | Layout DXF.....                                                      | 25        |
| 7.4      | Layout PTC EMN files .....                                           | 25        |
| <b>8</b> | <b>Handling .....</b>                                                | <b>27</b> |
| <b>9</b> | <b>Debug UART Errata.....</b>                                        | <b>28</b> |



## Figures

|           |                                                                |    |
|-----------|----------------------------------------------------------------|----|
| Figure 1  | Edison block diagram.....                                      | 8  |
| Figure 2  | Edison top view.....                                           | 8  |
| Figure 3  | Edison bottom view.....                                        | 9  |
| Figure 4  | Example Edison external USB design.....                        | 18 |
| Figure 5  | Example Edison lithium-polymer battery direct attach.....      | 20 |
| Figure 6  | Example Edison lithium-polymer battery with FET isolation..... | 21 |
| Figure 7  | Edison cold boot sequence.....                                 | 22 |
| Figure 8  | Edison mechanical dimensions (top view through PCB).....       | 23 |
| Figure 9  | Area around antenna.....                                       | 24 |
| Figure 10 | Layout DXF.....                                                | 25 |
| Figure 11 | PTC EMN graphic.....                                           | 25 |
| Figure 12 | EDISON H383485-300.....                                        | 26 |
| Figure 13 | Inserting an Edison module.....                                | 27 |

## Tables

|         |                                                           |    |
|---------|-----------------------------------------------------------|----|
| Table 1 | Product-specific documents.....                           | 6  |
| Table 2 | Hardware features.....                                    | 7  |
| Table 3 | Edison 70-pin connector part numbers.....                 | 12 |
| Table 4 | Edison 70-pin connector board-to-board mating height..... | 12 |
| Table 5 | Edison connector pinout and signal list.....              | 13 |
| Table 6 | Edison I2S available formats.....                         | 16 |
| Table 7 | Edison PWM programming examples.....                      | 17 |
| Table 8 | Layout SD card.....                                       | 24 |



## Revision History

| Revision | Description           | Date               |
|----------|-----------------------|--------------------|
| ww32     | Initial release       | August 4, 2014     |
| ww34     | Minor edits.          | August 20, 2014    |
| 001      | First public release. | September 9, 2014  |
| 002      | Minor corrections.    | September 16, 2014 |

§



# 1 Introduction

---

This document describes the hardware interface of the Intel® Edison compute module. It provides an overview of how to create an expansion board that connects directly to Edison.

## 1.1 References

**Table 1** Product-specific documents

| Reference | Name                                              | Number/location |
|-----------|---------------------------------------------------|-----------------|
| 331188    | Intel® Edison Board Support Package User Guide    |                 |
| 331189    | Intel® Edison Module Hardware Guide               | (This document) |
| 331190    | Intel® Edison Breakout Board Hardware Guide       |                 |
| 331191    | Intel® Edison Kit for Arduino* Hardware Guide     |                 |
| 331192    | Intel® Edison Native Application Guide            |                 |
| 331193    | Intel® Edison Quick Start Guide                   |                 |
| [RN]      | Intel® Edison Board Support Package Release Notes |                 |
| [GSG]     | Intel® Edison Getting Started Guide               |                 |





## 2 High-Level Functional Description

The Intel® Edison compute module is designed to lower the barriers to entry for anyone prototyping and producing IoT and wearable computing products. Intel® Edison contains the core system processing and connectivity elements: processor, PMIC, RAM, eMMC, and Wi-Fi/BT. It is not a self-contained, standalone device. Intel® Edison is a module that interfaces with end-user systems via a 70-pin connector. The Intel® Edison compute module does not include any video input or output interfaces (MIPI CSI, MIPI DSI, HDMI, etc.). Internal image processing and graphics processing cores are disabled (ISP, PowerVR, VED, VEC, VSP, etc.). Intel® Edison relies on the end-user support of input power. (in other words, the Intel® Edison compute module does not necessarily control battery recharging). Table 2 shows the main system components.


**Table 2** Hardware features

| Component        | Description                                                                                                                                                                                                                                                                                                                                                           |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Processor        | Dual Core IA-32 @ 500 MHz, 32-bit Intel® Atom™ Processor Z34xx Series @ 100 MHz                                                                                                                                                                                                                                                                                       |
| RAM              | 1 GB LPDDR3 POP memory (2 channel 32 bits @ 800 MT/sec)                                                                                                                                                                                                                                                                                                               |
| Internal storage | 4 GB eMMC (v4.51 spec)                                                                                                                                                                                                                                                                                                                                                |
| Power            | TI SNB9024 power management IC                                                                                                                                                                                                                                                                                                                                        |
| Wireless         | Dual-band (2.4 and 5 GHz) IEEE 802.11a/b/g/n                                                                                                                                                                                                                                                                                                                          |
| Bluetooth*       | BT 4.0 + 2.1 EDR                                                                                                                                                                                                                                                                                                                                                      |
| Antenna          | Dual-band onboard chip antenna or u.FL for external antenna                                                                                                                                                                                                                                                                                                           |
| Connector        | 70-pin Hirose DF40 Series (1.5, 2.0, or 3.0 mm stack height)                                                                                                                                                                                                                                                                                                          |
| Size             | 35.5 × 25.0 × 3.9 mm maximum (to be verified)                                                                                                                                                                                                                                                                                                                         |
| Power input      | 3.15 to 4.5 V                                                                                                                                                                                                                                                                                                                                                         |
| I/O              | 40 general purpose GPIO which can be configured as: <ul style="list-style-type: none"><li>• SD card: 1 interface</li><li>• UART: 2 controllers (one full flow control, one Rx/Tx)</li><li>• I<sup>2</sup>C: 2 controllers</li><li>• SPI: 1 controller with 2 chip selects</li><li>• I2S: 1 controller</li><li>• GPIO: Additional 14 (with 4 capable of PWM)</li></ul> |
| USB 2.0          | 1 OTG controller                                                                                                                                                                                                                                                                                                                                                      |
| Clocks           | 19.2 MHz, 32 kHz                                                                                                                                                                                                                                                                                                                                                      |

## 2.1 Block diagram


Figure 1 shows the basic Edison block diagram.

Figure 1 Edison block diagram




## 2.2 Module photos

Figure 2 Edison top view



**Figure 3** Edison bottom view



§



## 3 Component and Subsystem Details

---

### 3.1 Intel® Atom™ processor Z34XX

Intel® Atom™ Processor Z34xx Series is the next generation 22 nm SoC product targeted for the smartphone market segment. The SoC contains dual IA-32 cores operating at 500 MHz. The architecture includes 2-wide instruction decode and Out Of Order Execution with 1 MB cache shared between the two CPU cores. It includes Intel SIMD Extensions 2, 3, 4 (SSE2, SSE3, SSE4.1/4.2).

### 3.2 Wi-Fi / BT module

The Murata integrated Wi-Fi BT module is built around a Broadcom BCM43340 Wi-Fi /BT device.

The Broadcom BCM43340 single chip quad device provides the highest level of integration for a mobile or handheld wireless system, with integrated dual band (2.4 / 5 GHz) IEEE 802.11a/b/g/n MAC/baseband/radio with Bluetooth 4.0.

- Dual-band 2.4 GHz and 5 GHz IEEE 802.11 a/b/g/n.
- Single-stream IEEE 802.11n support for 20 MHz and 40 MHz channels provides PHY layer rates up to 150 Mbps for typical upper layer throughput in excess of 90 Mbps.
- Supports standard SDIO v2.0 and gSPI (48 MHz) host interfaces.
- Complies with Bluetooth\* Core Specification Version 4.0 with provisions for supporting future specifications. Bluetooth Class 1 or Class 2 transmitter operation.
- Security:
  - WPA and WPA2 (personal) support for powerful encryption and authentication.
  - AES in WLAN hardware for faster data encryption and IEEE 802.11i compatibility –Reference WLAN subsystem provides Cisco\* Compatible Extensions (CCX, CCX 2.0, CCX 3.0, CCX 4.0, CCX 5.0).
  - Reference WLAN subsystem provides Wi-Fi protected setup (WPS).

### 3.3 Managed NAND (eMMC) flash

Edison uses 4 GB of managed NAND to store the file system and user data. Managed NAND flash contains a full MMC controller, wear-leveling firmware, and all the other features that are typically found in MMC cards, except it is available in a small BGA form-factor.

- Bus mode
  - Data bus width: 1 bit (default), 4 bits, 8 bits
  - Data transfer rate: up to 200 MBps (HS200)
  - MMC I/F clock frequency: 0~200 MHz
  - MMC I/F boot frequency: 0~52 MHz

### 3.4 DDR SDRAM

Edison supports 1 GB LPDDR3 memory at speeds up to 1033 MT/s.

- 8 banks
- Row addresses R0-R13
- Column addresses C0-C9
- Dual-channel 32 bits
- 400 MHz clock max (800 MT/s)



### 3.5 Power management IC (PMIC)

Edison uses the Texas Instruments\* SNB9024 Power Management Integrated Circuit (PMIC). The SNB9024 PMIC is for mobile application processors platforms with high feature integration in order to minimize system board area. It includes subsystems for voltage regulation, A/D conversion, GPIOs, and RTC. The SNB9024 device is controlled and programmed using an I<sup>2</sup>C interface. There is also a serial voltage ID interface between the SOC and PMIC for handling core voltage rail settings as well as system control signals.

- Four high-efficiency buck converters
  - - Two dual-phase 0.55 to 1.2 V @ 4.8 A with DVS
  - - One dual-phase 1.24 V @ 2.5 A
  - - One single-phase 1.8 V @ 1.1 A
- One 5 V 1.2 A boost converter
- One 3.3 V/3.4 V 1.4 A buck-boost converter
- Five low drop-out regulators
  - - Three programmable 1.05 to 2.85 V @ 100 to 300 mA
  - - One high precision 1 V @ 2 mA
  - - One DVS 0.75 to 0.95 V @ 220 mA
- Two load switches with slew rate control and external load switch control
- USB and AC/DC adapter power supply detection with external charger control (enable/disable and current limit)
- I<sup>2</sup>C Interface and dedicated SVI
- Interrupt controller for PMIC events
- Seven general purpose 1.8 V I/Os, with two of them supporting up to 3.3 V
- 32.768 kHz RTC for backup time
- Alarm timer interrupt
- Sleep clock outputs (32.768 kHz)

### 3.6 USB 2.0 transceiver ULPI interface

The TUSB1211 is a USB 2.0 transceiver chip, designed to interface with a USB controller via a ULPI interface. It supports all USB 2.0 data rates (High-Speed 480 Mbps, Full-Speed 12 Mbps and Low-Speed 1.5 Mbps) in both Host and Peripheral modes. TUSB1211 also supports the OTG (Ver1.3) optional addendum to the USB 2.0 specification, including Host Negotiation Protocol (HNP) and Session Request Protocol (SRP).

TUSB1211 also supports USB Battery Charging Specification v1.1 integrating a charger detection module for sensing and control on DP/DM lines, and ACA (Adaptive Charger Accessory) detection and control on ID line. ACA allows simultaneous connection of a USB Charger or Charging Downstream Port and an Accessory to a portable OTG device. Configuration bits allow an ACA-agnostic legacy link to correctly communicate with the connected accessory port through the ACA.

### 3.7 Integrated chip antenna or u.FL connector for external antenna

The Edison module has an integrated dual-band 2.4/5 GHz antenna built onboard. The onboard antenna is used primarily for small form factor plastic devices. For larger devices or a device which has a metal enclosure, another version of Edison is available with an industry standard u.FL connector for attachment to an external antenna. This will allow the end-user to locate the antenna for optimal performance.



### 3.8 70-pin interface connector

The Edison module connects to the end user device via a 70-pin connector. The connector on Edison is a Hirose 70-pin DF40 Series “header” connector sometimes referred to as a “plug” connector. The Hirose part number for the “header” connector on Edison is: DF40C-70DP-0.4V(51).

The mating Hirose connector on an expansion board is the “receptacle” connector. This mating “receptacle” connector is available in three different heights. The board-to-board mating stack height can be 1.5, 2.0, or 3.0 mm. Table 3 lists the Hirose part number for the “receptacle” connector and corresponding DigiKey and Mouser part numbers for an expansion board.

**Table 3 Edison 70-pin connector part numbers**

| Hirose P/N                | Mating stack height | DigiKey P/N                                               | Mouser P/N           |
|---------------------------|---------------------|-----------------------------------------------------------|----------------------|
| DF40C-70DS-0.4V(51)       | 1.5 mm              | n/a                                                       | 798-DF40C70DS04V51   |
| DF40C(2.0)-70DS-0.4V(51)  | 2.0 mm              | H11908CT-ND (low quantity)<br>H11908TR-ND (tape and reel) | 798-DF40C2070DS04V51 |
| DF40HC(3.0)-70DS-0.4V(51) | 3.0 mm              | n/a                                                       | n/a                  |

The Edison Arduino board utilizes the 2.0 mm board-to-board stack height connector.

The bottom side of Edison (side with 70-pin connector) has a component height (shield height) of 1.5 mm and will sit flush against the connecting PCB if a 1.5 mm connector is used. Table 3 lists the expansion board component height restrictions for components under Edison.

**Table 4 Edison 70-pin connector board-to-board mating height**

| Hirose P/N                | Board-to-board mating height | Available height under Edison |
|---------------------------|------------------------------|-------------------------------|
| DF40C-70DS-0.4V(51)       | 1.5 mm                       | n/a                           |
| DF40C(2.0)-70DS-0.4V(51)  | 2.0 mm                       | 0.5 mm                        |
| DF40HC(3.0)-70DS-0.4V(51) | 3.0 mm                       | 1.5 mm                        |

Edison is secured to an expansion board via two mounting holes each with a diameter of 2.0 mm. Any mounting standoffs will also need to match the mating connector height (1.5, 2.0, or 3.0 mm).

Table 5 lists the Edison 70-pin connector pinouts and signals.

**Table 5** Edison connector pinout and signal list

| Pin            | Signal name   | Alternate function | Description                                                                                          |
|----------------|---------------|--------------------|------------------------------------------------------------------------------------------------------|
| 2, 4, 6        | VSYS          |                    | System input power (3.3 to 4.5 V)                                                                    |
| 8, 10          | 3.3 V         |                    | System 3.3 V output                                                                                  |
| 12             | 1.8 V         |                    | System 1.8 V output (same as I/O voltage levels)                                                     |
| 14             | DCIN          |                    | Input, connect to VSYS when powering from a DC power adapter (no connect if powering from a battery) |
| 1,5,9,11,13,15 | GND           |                    | Ground                                                                                               |
| 7              | MSIC_SLP_CLK3 |                    | 32 kHz sleep clock output                                                                            |
| 3              | USB_ID        |                    | USB OTG ID pin                                                                                       |
| 16             | USB_DP        |                    | USB D+                                                                                               |
| 18             | USB_DN        |                    | USB D-                                                                                               |
| 20             | USB_VBUS      |                    | USB VBUS input (does not power system)                                                               |
| 17             | PWRBTN#       |                    | Power/sleep button input (active low)                                                                |
| 19             | FAULT         |                    | USB power fault input (from external USB current limit switch)                                       |
| 21             | PSW           |                    | USB power output enable (to external USB current limit switch)                                       |
| 23             | V_VBAT_BKUP   |                    | Real-time clock (RTC) backup battery input                                                           |
| 36             | RESET_OUT#    |                    | System reset output (active low)                                                                     |
| 24             | GP44          |                    | GPIO                                                                                                 |
| 25             | GP165         |                    | GPIO                                                                                                 |
| 26             | GP45          |                    | GPIO                                                                                                 |
| 28             | GP46          |                    | GPIO                                                                                                 |
| 30             | GP47          |                    | GPIO                                                                                                 |
| 32             | GP48          |                    | GPIO                                                                                                 |
| 34             | GP49          |                    | GPIO                                                                                                 |
| 42             | GP15          |                    | GPIO                                                                                                 |
| 48             | GP14          |                    | GPIO                                                                                                 |
| 35             | GP12_PWM0     | PWM_0              | GPIO, capable of PWM output                                                                          |
| 33             | GP13_PWM1     | PWM_1              | GPIO, capable of PWM output                                                                          |
| 37             | GP182_PWM2    | PWM_2              | GPIO, capable of PWM output                                                                          |
| 39             | GP183_PWM3    | PWM_3              | GPIO, capable of PWM output                                                                          |
| 41             | GP19          | I2C_1_SCL          | GPIO, I2C1 clock (open collector when configured for I <sup>2</sup> C)                               |
| 43             | GP20          | I2C_1_SDA          | GPIO, I2C1 data (open collector when configured for I <sup>2</sup> C)                                |
| 45             | GP27          | I2C_6_SCL          | GPIO, I2C6 clock (open collector when configured for I <sup>2</sup> C)                               |
| 47             | GP28          | I2C_6_SDA          | GPIO, I2C6 data (open collector when configured for I <sup>2</sup> C)                                |
| 50             | GP42          | I2S_2_RXD          | GPIO, I2S2 receive data (input)                                                                      |
| 52             | GP40          | I2S_2_CLK          | GPIO, I2S2 clock (output)                                                                            |



| Pin         | Signal name   | Alternate function | Description                             |
|-------------|---------------|--------------------|-----------------------------------------|
| 54          | GP41          | I2S_2_FS           | GPIO, I2S2 frame sync (output)          |
| 56          | GP43          | I2S_2_TXD          | GPIO, I2S2 transmit data (output)       |
| 22          | GP134         | UART_2_RX          | GPIO, UART2 receive (input)             |
| 27          | GP135         | UART_2_TX          | GPIO, UART2 transmit (output)           |
| 51          | GP111         | SPI_2_FS1          | GPIO, SPI2 chip select 1 (output)       |
| 53          | GP110         | SPI_2_FS0          | GPIO, SPI2 chip select 0 (output)       |
| 55          | GP109         | SPI_2_CLK          | GPIO, SPI2 clock output                 |
| 57          | GP115         | SPI_2_TXD          | GPIO, SPI2 transmit data (output)       |
| 59          | GP114         | SPI_2_RXD          | GPIO, SPI2 receive data (input)         |
| 46          | GP131         | UART_1_TX          | GPIO, UART1 transmit (output)           |
| 61          | GP130         | UART_1_RX          | GPIO, UART1 receive data (input)        |
| 63          | GP129         | UART_1_RTS         | GPIO, UART1 ready to send (output)      |
| 65          | GP128         | UART_1_CTS         | GPIO, UART1 clear to send (input)       |
| 44          | GP84          | SD_0_CLK_FB        | GPIO, SD clock feedback                 |
| 58          | GP78          | SD_0_CLK           | GPIO, SD clock output                   |
| 60          | GP77          | SD_0_CD#           | GPIO, SD card detect input (active low) |
| 62          | GP79          | SD_0_CMD           | GPIO, SD command                        |
| 66          | GP80          | SD_0_DAT0          | GPIO, SD data 0                         |
| 70          | GP81          | SD_0_DAT1          | GPIO, SD data 1                         |
| 64          | GP82          | SD_0_DAT2          | GPIO, SD data 2                         |
| 68          | GP83          | SD_0_DAT3          | GPIO, SD data                           |
| 67          | OSC_CLK_OUT_0 |                    | 19.2 MHz high speed clock output        |
| 31          | RCVR_MODE     |                    | Firmware recovery mode                  |
| 69          | FW_RCVR       |                    | Firmware recovery (active high on boot) |
| 29,38,40,49 | Unused.       |                    |                                         |





## 4 External Interfaces on 70-Pin Connector

---

All Edison I/O (with the exception of USB) uses 1.8 V signaling.

### 4.1 I<sup>2</sup>C Interfaces

Edison has two available I<sup>2</sup>C interfaces, I2C1 and I2C6. I2C1 on pins 41 and 43 is a general purpose I<sup>2</sup>C interface that connects directly to the IA cores. I2C6 on pins 45 and 47 can be configured as I2C6 which connects to the IA cores or as I2C8 which connects to a system controller fabric (controlled by MCU). For the initial release of Edison, only I2C1 and I2C6 are available. Both of these interfaces are open collector when configured as I<sup>2</sup>C. When configured as GPIO, they can be standard push pull outputs.

The I<sup>2</sup>C module can operate in the following modes:

- Standard mode (with data rates up to 100 kbps).
- Fast mode (with data rates up to 400 kbps).
- High-speed mode (with data rates up to 3.4 Mbps).
- The SoC is always I<sup>2</sup>C master, it does not support multimaster mode.
- The SoC can support clock stretching by slave devices.
- Both 7-bit and 10-bit addressing modes are supported.

When I2C6 is configured as I2C8, it can only run in standard or fast mode.

### 4.2 SD card interface

An SD 3.0 compliant interface is available on pins 44, 58, 60, 62, 64, 66, 68, and 70.

SD memory key features

- Host clock up to 50 MHz
- Supports card detection (insertion/removal) with dedicated card detection signal only.
- Meets SD Host Controller Standard Specification version 3.0.
- Only supports SD memory
- Requires external level shifter for support of 2.85 V devices

### 4.3 UART interfaces

There are two UARTs available, UART1 with flow control and UART2 without flow control. The UART1 interface is available on pins 46, 63, 61, and 54. UART2 is on pins 22 and 27. The UARTs are:

- 16550 compliant
- 64-byte buffer size
- Baud rate from 300 bps to 3.686 Mbps.

The UART2 alternate function is as the Linux debug serial port.



## 4.4 SPI interface

An SPI interface is available on pins 51, 53, 55, 57, and 59. The interface has two available chip selects.

- In a single-frame transfer, the SoC supports all four possible combinations for the serial clock phase and polarity.
- In multiple frame transfer, the SoC supports SPH=1 and SPO= 0 or 1.
- The SoC may toggle the slave select signal between each data frame for SPH=0.
- 25 MHz Master mode, 16.67 MHz slave mode.

## 4.5 I2S interface

An I2S interface is available on pins 50, 52, 54, and 56. All of the I2S modes below have not been verified and are subject to change. Table 6 lists the available formats available on the I2S port.

**Table 6 Edison I2S available formats**

| Mode                  | Priority       | Frame rate                     | Bits/sample | Number of slots                             | Frame-to-data offset | Frame polarity  | Frame width              | Frame rate inaccuracy | Notes                                                                           |
|-----------------------|----------------|--------------------------------|-------------|---------------------------------------------|----------------------|-----------------|--------------------------|-----------------------|---------------------------------------------------------------------------------|
| I2S master            | 1              | 192K, 96K, 48K, 16K, 8K        | 16, 24      | 2                                           | 1                    | 0-left, 1-right | 50/50                    | 0%                    | Standard I2S protocol. 50% duty cycle on frame.                                 |
| PCM slave - SFS       | 1              | 192K, 96K, 48K, 44.1K, 16K, 8K | 16, 24      | 192 kHz: 2<br>96 kHz: 4<br>All else: 1 to 6 | 0                    | High            |                          |                       |                                                                                 |
| PCM slave - LFS       | 1              | 192K, 96K, 48K, 44.1K, 16K, 8K | 16, 24      | 192 kHz: 2<br>96 kHz: 4<br>All else: 1 to 6 | 0                    | High            |                          |                       |                                                                                 |
| PCM master - SFS      | 1              | 192K, 96K, 48K, 16K, 8K        | 16, 24      | 192 kHz: 2<br>All else: 1 to 4              | 0                    | High            | 1 bit clockwise          | 0%                    | Rising edge frame sensitive. Design supports more frame-to-data offset options. |
| PCM master - LFS      | 1              | 192K, 96K, 48K, 16K, 8K        | 16, 24      | 192 kHz: 2<br>All else: 1 to 4              | 0                    | High            | 1-bit to $n$ -bit clocks | 0%                    | $n$ is the width of one slot. Design supports width > 1 slot.                   |
| Left justified master | 2              | 192K, 96K, 48K                 | 16, 24      | 2                                           | 0                    | 0-left, 1-right | 50/50                    | 0%                    | Design supports flipping polarity on the frame signal.                          |
| I2S slave             | 3              | 192K, 96K, 48K, 44.1K          | 16, 24      | 2                                           | 0                    | 0-left, 1-right | 50/50                    | 0%                    |                                                                                 |
| Left justified slave  | 3              | 192K, 96K, 48K                 | 16, 24      | 2                                           | 0                    | 0-left, 1-right | 50/50                    | 0%                    |                                                                                 |
| Right justified       | Not supported. |                                |             |                                             |                      |                 |                          |                       |                                                                                 |



## 4.6 PWM

There are four available GPIO that can be configured as PWM outputs. These are found on pins 33, 35, 37, and 39. The PWM resolution is 8 bits.

The main PWM variables that control PWM output are:

- The PWM output frequency and duty cycle can be estimated by the equations:
  - Target frequency  $\approx 19.2 \text{ MHz} * \text{Base\_unit value} / 256$
  - Target PWM duty cycle  $\approx \text{PWM\_on\_time\_divisor} / 256$

Table 7 shows some examples of PWM programming.

**Table 7 Edison PWM programming examples**

| Integer part of PWM_base_unit (bits 29:22) | Fractional part of PWM_base_unit (bits 21:8) | Decimal base unit value | Base unit type | PWM frequency (Hz) | PWM period ( $\mu\text{s}$ ) | Bits of resolution | PWM steps |
|--------------------------------------------|----------------------------------------------|-------------------------|----------------|--------------------|------------------------------|--------------------|-----------|
| 0000_0000b                                 | 00_0100_0000_0000b                           | 0.0625                  | fractional     | 4,688              | 213                          | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0010_0000_0000b                           | 0.03125                 | fractional     | 2,344              | 427                          | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0001_0000_0000b                           | 0.015625                | fractional     | 1,172              | 853                          | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_1000_0000b                           | 0.0078125               | fractional     | 586                | 1,707                        | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0100_0000b                           | 0.00390625              | fractional     | 293                | 3,413                        | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0010_0000b                           | 0.00195325              | fractional     | 146                | 6827                         | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0001_0000b                           | 0.0009765625            | fractional     | 73.2               | 13,653                       | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0000_1000b                           | 0.00048828125           | fractional     | 36.6               | 27,307                       | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0000_0100b                           | 0.000244140625          | fractional     | 18.3               | 54,613                       | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0000_0010b                           | 0.0001220703125         | fractional     | 9.2                | 109,227                      | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0000_0001b                           | 0.00006103515625        | fractional     | 4.6                | 218,453                      | 8                  | 0.39%     |
| 0000_0000b                                 | 00_0000_0010_0001b                           | 0.00201416015625        | fractional     | 151                | 6619                         | 8                  | 0.39%     |

## 4.7 GPIO

A number of general purpose I/Os are available on the external interface. These are found on pins: 24, 25, 26, 28, 30, 32, 34, 42, and 48. Some of these serve alternate functions of interrupts for external sensor support. All the interfaces listed in Section 4 (I2C, I2S, UART, etc.) if not used, can be turned into general purpose I/Os.

When the pin mode is chosen as GPIO, it can be programmed as an output or input. When programmed as an input, a GPIO can serve as an interrupt or wake source. Inputs have programmable pullups or pulldowns. Pullup value can be 2, 20, or 50 kohm. I<sup>2</sup>C pins also have an additional 910 ohm value. When in general purpose mode, input GPIO signals enter a glitch filter by default, before reaching the edge detection registers.

To ensure that a pulse is detected by the edge detection register, the pulse should be five clock cycles long.

- 100 ns for a 50 MHz clock when SoC is in S0 state.
- 260 ns for 19.2 MHz clock when SoC is in S0i1 or S0i2 State.
- 155.5  $\mu\text{s}$  for 32 kHz clock (RTC) when SoC is in S0i3 State.

Most GPIO-capable pins are configured as GPIO inputs during the assertion of all resets, and they remain inputs until configured otherwise. As outputs, the GPIOs can be individually cleared or set. They can be preprogrammed to either state when entering standby. Output drive is  $\pm 3 \text{ mA}$ .


## 4.8 USB

The Edison module has a single USB 2.0 interface. This interface is the primary method for downloading code. The interface is found on pins: 3, 16, 18, and 20.

**Note:** The USB\_VBUS signal should be applied to pin 20. This signal is only used to alert the Edison module that it has been connected to a host port.

The Edison module does not use power applied to pin 20 to power the device. Edison is designed to support OTG, using the ID signal on pin 3. The OTG power function is offboard. Two signals PSW (pin 21), and FAULT (pin 19) from the ULPI controller are used to control the external power switch and monitor the overcurrent condition on VBUS. Figure 4 shows the configuration of the **external hardware**.

**Figure 4** Example Edison external USB design



The PSW signal is active high and controls an external VBUS power switch or charge pump.

The FAULT signal is active low. **FAULT should be connected to GND if USB host mode is not used.**

## 4.9 Clocks

Edison has two clock outputs. A 32 KHz sleep clock connected to pin 7 and a high frequency 19.2 MHz clock connected to pin 67. The sleep clock has +/-5mA drive capability, and may be programmed to provide an output when the SoC is in a sleep state. The high frequency 19.2 MHz clock has a drive strength of TBD mA. Buffering of the clocks may be necessary, depending on external trace lengths.

## 4.10 System reset

Edison has two system reset signals PWRBTN# (pin 17) and RESET\_OUT# (pin 36). The PWRBTN# pin is an active low input which can cause the Edison module to transition into and out of sleep, or cause a power off, depending on the configuration of the software. RESET\_OUT# is open-drain, and driven low by default out of system reset. This signal can be used by external hardware to indicate system reset. The Edison I/Os are undefined until RESET\_OUT# transitions high.



## 4.11 Special software recovery

Edison has two signals used during boot, to cause the SoC to force firmware and OS image download and is useful to provide a recovery mechanism in the event of a corrupted flash image. These signals are FW\_RCVR on pin 69, and RCVR\_MODE on pin 31. The FW\_RCVR signal must be held low during boot until RESET\_OUT# goes high.

## 4.12 Power input and output

There are five power rails on the Edison module, VSYS, 3.3V, 1.8V, USB\_VBUS, and V\_VBAT\_BKUP. VSYS is the only input power rail to the Edison module and the voltage range is 3.15V to 4.5V. USB\_VBUS is a standard USB VBUS input from 4.75V to 5.25V. This rail is not used to power the device. It is only used by the USB ULPI PHY to determine a host device has attached to the Edison device. The 3.3V and 1.8V are power outputs from the Edison module that source a maximum of 250mA (TBV).

DCIN is a signal which indicates whether Edison is being powered from a battery or from an external power source. DCIN also sets the voltage level required on VSYS in order to boot. When DCIN is floating or tied to ground the voltage on VSYS MUST rise from 2.5 to 3.5 V in 100 milliseconds, otherwise the boot is aborted. When the boot is aborted, power must be cycled below 2.5V. If DCIN is connected to VSYS, Edison will start to boot when VSYS is above 2.5 V for 100 milliseconds.

**Note:** The absolute minimum voltage to assure Wi-Fi and Bluetooth functionality is 3.15 V.

## 4.13 V\_VBAT\_BKUP

The PMIC has a dedicated charging subsystem for the backup supply, allowing the use of either rechargeable coin cell batteries or super-capacitors. The external cell should be connected to pin 23, V\_VBAT\_BKUP. The PMIC can be programmed with charge voltage of 2.5, 3.0, 3.15 or 3.3V. The charge current is programmable to 10, 50, 100, or 500uA. The default settings are 2.5V and 10uA. The capability to change these values is TBD.



## 5 Powering Edison

Edison may be embedded in a number of devices either battery powered, or AC wall powered. Therefore, Edison was designed not to support a specific power delivery method or specific battery chemistry and capacity range. This portion of the design is left to the end user. With the interfaces available smart battery coulomb counters and smart rechargers could be placed onto one of the available I2C busses. Porting of the software to the specific bus would be the responsibility of the end user.

### 5.1 Main power supply VSYS


Edison uses VSYS (pins 2, 4, and 6) as the only power input path. Internal to Edison this signal is also connected to the VBAT path. Application of power to VSYS is interpreted as a battery insertion and will cause Edison to boot. The VSYS power range is 3.15V min to 4.5V max (see Section 4.12). This allows VSYS to run off a standard lithium ion battery. There are a number of possible power configurations for Edison, based on the size and cost sensitivity of the end user product.

### 5.2 Lithium-polymer battery direct attach

The simplest battery power connection to Edison is to directly attach a battery to VSYS, as shown in Figure 5. We do not recommend this configuration, however, as the charging system cannot distinguish between charge current and total system current.

**Note:** If Edison is prevented from booting by holding the power button signal PWRBTN# (pin 17) low, then the power input can be assumed to be the battery charging current.


**Figure 5** Example Edison lithium-polymer battery direct attach



## 5.3 Lithium-polymer battery with diode or FET isolation

In this configuration, Edison will see a diode drop during normal operation. This configuration allows the system to boot even with a dead battery. This configuration requires an additional pin to the external world to control the charging. Replacing the diode with a PFET, and pulling the gate low will remove the diode drop power loss. The external charger would require a gate control pin for an external PFET. This function is found on rechargers like BQ24073.

**Figure 6** Example Edison lithium-polymer battery with FET isolation



## 5.4 Connection to USB VBUS


It is **NOT** possible to run Edison directly off a USB power supply. The maximum input voltage to VSYS should be less than 4.5V. The USB power supply specification (4.75V – 5.25V) exceeds the safe operational range of Edison. USB power must be down converted with an LDO or small buck switching converter or a recharger like BQ24074.

## 5.5 Cold boot sequence

Figure 6 shows the signal sequence from a cold boot.

**Note:** The reset# signal in Figure 6 is accessible on the 70-pin connectors as RESET\_OUT# on pin 36.


**Figure 7** Edison cold boot sequence



## 6 Edison Mechanicals

Figure 8 shows the dimensions (in millimeters) of the Edison module.

**Figure 8** Edison mechanical dimensions (top view through PCB)



The location for pin 1 of the 70-pin connector is the lower right corner of the connector. The location of pin 2 is across the connector at the lower left corner. Consequently, the location of pin 69 is the upper right corner of the connector and the location of pin 70 is the upper left corner of the connector. The center point of the connector is specified in the drawing.

The diameters of the two mounting holes are 2.0 mm. Screw heads should be less than 3.0 mm. The mounting holes were designed for a T1.6 mm screw.

**Note:** The onboard chip antenna in the lower right corner of Edison is denoted in the drawing as “ANTENNA KOZ”. User-designed expansion PCBs should not place components or metallic objects close to the antenna keepout zone.


Most components on both sides of Edison will be covered with a shield. The height of the shields on both sides of the board, as measured from the surface of the PCB, is approximately 1.5 mm. The PCB thickness is specified as 0.8 mm  $\pm$  0.1 mm. Therefore, the total maximum thickness of Edison is 3.9 mm. These values are verified with DVT modules.

## 7 Layout

### 7.1 Antenna keepout

The area under and around the antenna should be kept free of all components, routes, and ground plane. The Intel® Edison board DXF in white with antenna keepout shown in the Arduino\* trace layers. See Figure 9.

**Figure 9** Area around antenna



### 7.2 Layout SD card, I2S, SPI, I2C

**Table 8** Layout SD card

| Signal parameter                                        | Metric (mm)                        | Standard (mils) |
|---------------------------------------------------------|------------------------------------|-----------------|
| Total length L1                                         | 0.254 to 101.6 mm                  | 10 to 4000 mils |
| DATA/CMD/CTRL to CLK maximum pin-to-pin length mismatch | ±2.54 mm                           | ±100 mils       |
| Minimum main route spacing ratio                        | 60 × 60 μm. 1:1 trace width/space. |                 |
| CLK to DATA/CMD/CTRL matching                           | ±200 mils                          |                 |
| Characteristic single ended impedance                   | 42 to 45 ohm (±10%)                |                 |
| Load capacitance                                        | 2 to 5 pF                          |                 |

**Note:**


- 1) For SPI, total length is 6000 mils.
- 2) For I<sup>2</sup>C, total length is 8000 mils.

## 7.3 Layout DXF

The following embedded file is a DXF of the Edison module as shown in the picture below.

**Note:** KOZ is keep out zone.

**Figure 10** Layout DXF



## 7.4 Layout PTC EMN files

**Figure 11** PTC EMN graphic





Figure 12 EDISON H383485-300




§

## 8 Handling

When assembling an Intel® Edison module to an Arduino board, handle the Intel® Edison module by the PCB edges. Avoid holding or exerting pressure to the shields. To mate the Intel® Edison board to the Arduino\* board, apply pressure directly above the connector and to the left corner, as shown in Figure 13.

**Figure 13** Inserting an Edison module



§



## 9 Debug UART Errata

---

The Intel® Edison board has a known error on all UARTs. When Edison goes into low power sleep, the UART internal FIFO and interface is powered down. Therefore, a two-wire UART (Rx/Tx) will lose the first received character whenever Edison is in sleep mode. In order to avoid this condition, when sleep mode is enabled, a four-wire UART (Rx, Tx, CTS, and RTS) is required.

### §