

HITACHI

KAOHSIUNG HITACHI
ELECTRONICS CO.,LTD
P.O. BOX 26-27
2,13TH EAST ST. K.E.P.Z.
KAOHSIUNG TAIWAN R.O.C.
TEL:(07) 821-5811 (7 LINE)
FAX:(07) 821-5815

FOR MESSRS : _____

DATE : Nov.25,2011

CUSTOMER'S ACCEPTANCE SPECIFICATIONS


TX14D12VM1CPC

C O N T E N T S

No.	ITEM	SHEET No.	PAGE
1	COVER	7B64PS 2701-TX14D12VM1CPC-5	1-1/1
2	RECORD OF REVISION	7B64PS 2702-TX14D12VM1CPC-5	2-1/2~2/2
3	GENERAL DATA	7B64PS 2703-TX14D12VM1CPC-5	3-1/1
4	ABSOLUTE MAXIMUM RATINGS	7B64PS 2704-TX14D12VM1CPC-5	4-1/2~2/2
5	ELECTRICAL CHARACTERISTICS	7B64PS 2705-TX14D12VM1CPC-5	5-1/3~3/3
6	OPTICAL CHARACTERISTICS	7B64PS 2706-TX14D12VM1CPC-5	6-1/3~3/3
7	BLOCK DIAGRAM	7B64PS 2707-TX14D12VM1CPC-5	7-1/1
8	INTERFACE TIMING CHART	7B64PS 2708-TX14D12VM1CPC-5	8-1/6~6/6
9	DIMENSIONAL OUTLINE	7B63PS 2709-TX14D12VM1CPC-5	9-1/1
10	APPEARANCE STANDARD	7B64PS 2710-TX14D12VM1CPC-5	10-1/5~5/5
11	PRECAUTION IN DESIGN	7B64PS 2711-TX14D12VM1CPC-5	11-1/3~3/3
12	DESIGNATION OF LOT MARK	7B64PS 2712-TX14D12VM1CPC-5	12-1/1
13	PRECAUTION FOR USE	7B64PS 2713-TX14D12VM1CPC-5	13-1/1

*When product will be discontinued, customer will be informed by HITACHI with twelve months prior to discontinuation.

ACCEPTED BY; _____

PROPOSED BY; 

KAOHSIUNG HITACHI ELECTRONICS CO.,LTD.	Sh. No.	7B64PS 2701-TX14D12VM1CPC-5	PAGE	1-1/1
---	------------	-----------------------------	------	-------

RECORD OF REVISION

DATE	SHEET No.	SUMMARY																		
May.13,'08	7B64PS 2705-TX14D12VM1CPC-2 PAGE 5-1/3	5.2.3 MECHANICAL CHARACTERISTICS Changed : <table><tr><th>ITEM</th><th>SPECIFICATION</th><th>NOTE</th></tr><tr><td>Pen Input Pressure</td><td>20gf ~ 80gf</td><td>R0.8, Polyacetal Pen</td></tr><tr><td>Finger</td><td>20gf ~ 80gf</td><td>R8.0, Silicon Rubber</td></tr></table> ↓ <table><tr><th>ITEM</th><th>SPECIFICATION</th><th>NOTE</th></tr><tr><td>Pen Input Pressure</td><td>1.2N max.</td><td>R0.8, Polyacetal Pen</td></tr><tr><td>Finger</td><td>1.2N max.</td><td>R8, Silicon Rubber</td></tr></table>	ITEM	SPECIFICATION	NOTE	Pen Input Pressure	20gf ~ 80gf	R0.8, Polyacetal Pen	Finger	20gf ~ 80gf	R8.0, Silicon Rubber	ITEM	SPECIFICATION	NOTE	Pen Input Pressure	1.2N max.	R0.8, Polyacetal Pen	Finger	1.2N max.	R8, Silicon Rubber
	ITEM	SPECIFICATION	NOTE																	
	Pen Input Pressure	20gf ~ 80gf	R0.8, Polyacetal Pen																	
	Finger	20gf ~ 80gf	R8.0, Silicon Rubber																	
	ITEM	SPECIFICATION	NOTE																	
Pen Input Pressure	1.2N max.	R0.8, Polyacetal Pen																		
Finger	1.2N max.	R8, Silicon Rubber																		
7B64PS 2708-TX14D12VM1CPC-2 PAGE 8-6/6	8.5 INTERNAL PIN CONNECTION Changed : CN1 JAE : FA5B040HF1R3000(Sn plating) → FA5B040HP1R3000(Au plating)																			
7B64PS 2709-TX14D12VM1CPC-2 PAGE 9-1/1	9. DIMENSIONAL OUTLINE The lot label size and position is changed.																			
7B64PS 2712-TX14D12VM1CPC-2 PAGE 12-1/1	12.1 LOT MARK Changed : 5 digits for production number ↓ 6 digits for production number 12.4 LOCATION OF LOT MARK Changed : Lot No. & Production Control No. (90) HITACHI TX14D12VM1CPC 4113T-00001 REV. MADE IN TAIWAN 高電圧注意 CAUTION HIGH VOLTAGE 123456 17 (25) ↓ (26) TX14D12VM1CPC 8041T HITACHI REV: (5D) MADE IN TAIWAN 123456 (14) Added : 12.5 REVISION(Rev.) CONTROL<table><tr><th>Rev No.</th><th>ITEM</th></tr><tr><td>A</td><td>CN1 JAE : FA5B040HF1R3000</td></tr><tr><td>B</td><td>CN1 JAE : FA5B040HP1R3000</td></tr></table>	Rev No.	ITEM	A	CN1 JAE : FA5B040HF1R3000	B	CN1 JAE : FA5B040HP1R3000													
Rev No.	ITEM																			
A	CN1 JAE : FA5B040HF1R3000																			
B	CN1 JAE : FA5B040HP1R3000																			
KAOHSIUNG HITACHI ELECTRONICS CO.,LTD.		DATE Nov.25,'11																		
Sh. No.		7B64PS 2702-TX14D12VM1CPC-5																		
PAGE		2-1/2																		

RECORD OF REVISION

DATE	SHEET No.	SUMMARY					
Sep.05,'08	7B64PS 2704-TX14D12VM1CPC-3 PAGE 4-2/2	4.2 ENVIRONMENTAL ABSOLUTE MAXIMUM RATINGS					
		Changed :					
		ITEM		OPERATING		STORAGE	
				MIN.	MAX.	MIN.	MAX.
		Temperature		(-20)	(70)	(-30)	(80)
		↓					
		ITEM		OPERATING		STORAGE	
				MIN.	MAX.	MIN.	MAX.
		Temperature		-20	70	-30	80
Sep.05,'08	7B64PS 2706-TX14D12VM1CPC-3 PAGE 6-1/3	6.1 OPTICAL CHARACTERISTICS OF LCD					
		Changed : Response Time : TYP. (45) → (30)					
	7B64PS 2706-TX14D12VM1CPC-3 PAGE 6-3/3	6.2 OPTICAL CHARACTERISTICS OF LCD (BACKLIGHT ON)					
		Changed : Brightness : MIN. 160 → 200					
		TYP. 280 → 320					
Nov.12,'10	7B64PS 2710-TX14D12VM1CPC-4 PAGE 10-5/5	10.3 APPEARANCE SPECIFICATION					
		Changed : Blistering Puffiness 0.4mm max. → 0.6mm max.					
Nov.25,'11	7B64PS 2706-TX14D12VM1CPC-5 PAGE 6-1/3	6. OPTICAL CHARACTERISTICS					
		Revised:					
		Item		Symbol	Min.	Typ.	Max.
		Color Chromaticity	Green	X	0.34	0.39	0.44
				↓			
		Item		Symbol	Min.	Typ.	Max.
		Color Chromaticity	Green	X	0.27	0.32	0.37

3.GENERAL DATA

The specifications are applied to the following TFT-LCD Module with Back-light unit.

(1) Part Name	TX14D12VM1CPC
(2) Module Dimensions	131.0(W)mm x 102.2(H)mm x 12.4(D)mm typ.
(3) LCD Active Area	115.2(W)mm x 86.4(H)mm
(4) Dot Pitch	0.12(W)mm x 3(R,G,B)(W) x 0.36(H)mm
(5) Resolution	320x3(R,G,B))(W)x240(H) dots
(6) Color Pixel Arrangement	R,G,B Vertical stripe
(7) LCD Type	Transmissive Color TFT LCD (Normally White)
(8) Display Type	Active Matrix
(9) Number of Colors	262k Colors (R,G,B 6bit digital each)
(10) Backlight	Light Emitting Diode (LED)x21
(11) Weight	200g typ.
(12) Interface	40pin (C-MOS)
(13) Power Supply Voltage	3.3V only (Include Timing Controller and Power Unit)
(14) Viewing Direction	6 O'clock (without image inversion and least brightness change) 12 O'clock (contrast peak located at)
(15) Touch Panel	Resistance type The surface is antiglare type

4. ABSOLUTE MAXIMUM RATINGS

4.1 ELECTRICAL ABSOLUTE MAXIMUM RATINGS

VSS=0V

ITEM	SYMBOL	MIN.	MAX.	UNIT	COMMENT
Power Supply for Logic	VDD	-0.3	4.0	V	
Input Voltage	VI	-0.3	VDD+0.3		(Note 1)
Input Current	Ii	0	1	A	
Static Electricity	VESD0	-	±100	V	(Note 2,3)
	VESD1	-	±8	kV	(Note 2,4)

Note 1 : DTMG,DCLK,RD0~RD5,GD0~GD5,BD0~BD5.

Note 2 : 200pF-250Ω 25℃ - 70%RH

Note 3 : Interface Pin Connector.

Note 4 : The surface of metal bezel and LCD panel .

4.2 ENVIRONMENTAL ABSOLUTE MAXIMUM RATINGS

I T E M	OPERATING		STORAGE		COMMENT
	MIN.	MAX.	MIN.	MAX.	
Temperature	-20	70	-30	80	(Note 2,3,6,7,8,10)
Humidity	(Note 1)		(Note 1)		Without condensation
Vibration	-	4.9m/s ² (0.5G)	-	19.6m/s ² (2G) (Note 5)	(Note 4)
Shock	-	29.4m/s ² (3G)	-	490m/s ² (50G) (Note 5)	XYZ directions (Note 9)
Corrosive Gas	Not Acceptable		Not Acceptable		
Operating Life (Note 12)	40,000 h (Note 11)		-		At 25°C , I _{LED} =84mA

Note 1 : Ta ≤ 40°C :85%RH max.

Ta > 40°C :Absolute humidity must be lower than the humidity of 85%RH at 40°C .

Note 2 : For storage condition Ta at -30°C < 48h , at 80°C < 100h.

For operating condition Ta at -20°C < 100h , at 70°C < 100h.

Note 3 : Background color changes slightly depending on ambient temperature.

This phenomenon is reversible.

Note 4 : 5Hz~100Hz(Except resonance frequency)

Note 5 : This LCM will resume normal operation after finishing the test.

Note 6 : The response time will be slower at low temperature.

Note 7 : Only operation is guaranteed at operating temperature. Contrast, response time, another display quality are evaluated at +25°C.

Note 8 : If LED is driven by high current. The life time of LED will be note11 reduced.

Also high temperature and humidity.

Note 9 : Pulse Width : 10ms

Note 10 : This is panel surface temperature , not ambient temperature.

Note 11 : When brightness reached 50% of initial brightness.

Note 12 :Life time is estimated data.

5. ELECTRICAL CHARACTERISTICS

5.1 ELECTRICAL CHARACTERISTICS OF LCD

Ta=25°C, VSS=0V

ITEM	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Power Supply Voltage	VDD	-	3.0	3.3	3.6	V
Input Voltage for Logic (Note 1)	VI	"H" level	2.0	-	VDD	V
		"L" level	VSS	-	0.8	
Power Supply Current (Note 2)	IDD	VDD-VSS=3.3V	-	65	-	mA
Vsync Frequency	fV	-	-	60	68	Hz
Hsync Frequency	fH for VGA display mode	-	25.3	29.5	36.1	kHz
	fH for QVGA display mode		13.1	15.2	17.7	
DCLK Frequency	fCLK for VGA display mode	-	17.2	20.9	26.7	MHz
	fCLK for QVGA display mode		4.85	5.85	7.0	

Note 1 : DTMG, DCLK, RD0~RD5, GD0~GD5, BD0~BD5.

Note 2 : fV=60Hz, Ta=25°C, Pattern used as display pattern : All Black.

Note 3 : Need to make sure of flickering and rippling of display when setting the frame frequency in your set.

5.2 ELECTRICAL CHARACTERISTICS OF TOUCH PANEL

5.2.1 OPERATING CONDITION

ITEM	SPECIFICATION	NOTE
Operating Voltage	5VDC	7VDC max.
Operating Current	20mA max.	

5.2.2 ELECTRICAL CHARACTERISTICS

ITEM		SPECIFICATION	NOTE
Resistance Between Terminal	XT-XB	210~880Ω	
	YR-YL	230~650Ω	
Insulation Resistance	X-Y	20MΩ min.	At 25V DC
Linearity	X	±1.5% max.	(Note 1)
	Y	±1.5% max.	
Chattering		10ms max.	

5.2.3 MECHANICAL CHARACTERISTICS

ITEM	SPECIFICATION	NOTE
Pen Input Pressure	1.2N max.	R0.8, Polyacetal Pen
Finger	1.2N max.	R8, Silicon Rubber
Surface Hardness	2H min.	JIS K 5400


5.2.4 OPTICAL CHARACTERISTICS

ITEM	SPECIFICATION	NOTE
Transmittance	80% min.	

Note 1 : Operating Voltage 5V DC.

Note 2 : Test Condition.

(a) X axis linearity testing method , 100g , VYR-VYL=5V , VOUT=VXT.




(b) Y axis linearity testing method , VXT-VXB=5V , VOUT=VYR.

Note 3 : Calculation

(a) Y axis linearity

Linearity= $\frac{\Delta E \text{ max.}}{EA - EH} \times 100(\%)$




5.3 ELECTRICAL CHARACTERISTICS OF LED BACKLIGHT

Ta=25℃ (Backlight on)

ITEM	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT	REMARKS
LED Input Voltage (Note 1)	VLED	-	11.5	12	12.5	V	BL Unit
LED Forward Current (Note 1)	ILED	-	-	84	91	mA	BL Unit
LED Reverse Current	I _R	V _R = 4V	-	-	50	μA	LED / Part

Note 1 : LED circuit



6. OPTICAL CHARACTERISTICS

6.1 OPTICAL CHARACTERISTICS OF LCD


Ta=25°C (Backlight on)

ITEM		SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT	NOTE
Viewing Area		θx	$\phi=0^{\circ}, K \geq 5.0$	60	70	-	deg	1~5
		$\theta x'$	$\phi=180^{\circ}, K \geq 5.0$	60	70	-	deg	1~5
		θy	$\phi=90^{\circ}, K \geq 5.0$	70	80	-	deg	1~5
		$\theta y'$	$\phi=270^{\circ}, K \geq 5.0$	60	70	-	deg	1~5
Contrast Ratio		K	$\phi=0^{\circ}, \theta=0^{\circ}$	120	350	-	-	5
Response Time (rise+fall)		tr+tf	$\phi=0^{\circ}, \theta=0^{\circ}$	-	30	-	ms	6
Color Tone (Primary Color)	Red	x	$\phi=0^{\circ}, \theta=0^{\circ}$	0.57	0.62	0.67	-	
		y		0.31	0.36	0.41	-	
	Green	x		0.27	0.32	0.37	-	
		y		0.52	0.57	0.62	-	
	Blue	x		0.10	0.15	0.20	-	
		y		0.03	0.08	0.13	-	
	White	x		0.31	0.36	0.41	-	
		y		0.30	0.35	0.40	-	


Note 1 : Driving Condition
 Display Pattern : White Raster
 I_{LED} Current : 84mA

(Measurement condition : HITACHI standard)
 (Note 3~6) : See next page.


Note 2 : Measurement Condition
 (Transmittance)




Note 3 : Definition of θ and ϕ
(Normal)
Viewing direction



Note 4 : Definition of Viewing angle ϕ_1 and ϕ_2





Contrast ratio "K" vs Viewing angle " ϕ "



Note 5 : Definition of contrast "K"

$$K = \frac{\text{White Brightness}}{\text{Black Brightness}}$$

Note 6 : Definition optical response time




6.2 OPTICAL CHARACTERISTICS OF LCD (BACKLIGHT ON)

ITEM	MIN.	TYP.	MAX.	UNIT	NOTE
Brightness	200	320	-	cd/m ²	I _{LED} =84mA (Note 1)
Brightness Uniformity	-	-	±25	%	Under mentioned (Note 1,2,3)

(Measurement condition : HITACHI standard)

LED:0h operation, Ta=25°C
Display data should be set to all “ON”.




- Note 1 : Measurement after 10 minutes from LED operating.
Active area center.
- Note 2 : Brightness control : 100%.
- Note 3 : Measurement of the following 9 places on the display.



Note 4 : Definition of the brightness tolerance.

$$\left(\frac{\text{Max. brightness or Min. brightness} - \text{Average brightness}}{\text{Average brightness}} \right) \times 100\%$$


7. BLOCK DIAGRAM



8.INTERFACE TIMING

8.1 Timing Chart

(Data is latched negative edge trigger of DCLK)



Note 1 : DTMG is definition of the above timing for Hsync and Vsync.

Note 2 : No matter when Hsync and Vsync is inputted ,this LCM can be drove only DTMG Signal. DTMG should be set to low level when it is not input valid data.

8.2.1 INTERFACE TIMING FOR QVGA DISPLAY MODE

ITEM		SYMBOL	MIN.	TYP.	MAX.	UNIT	REMARKS
DCLK	Cycle time	t _{CLK}	60	171	206	ns	
	Low level Width	t _{WCL}	12	-	-		
	High level Width	t _{WCH}	12	-	-		
	Rise time	t _{rCLK}	-	-	20		
	Fall time	t _{fCLK}	-	-	20		
	Duty	D	0.45	0.5	0.55	-	D= t _{CLKL} / t _{CLK}
Hsync	Set up time	t _{SH}	5	-	-	ns	for DCLK
	Hold time	t _{HH}	10	-	-		
	Cycle	t _{HP}	358	385	453	t _{CLK}	
	Valid width	t _{WH}	4	5	-		
	Rise/Fall time	t _{Hr} ,t _{Hf}	-	-	30	ns	
Vsync	Set up	t _{SV}	0	-	-	t _{CLK}	for Hsync
	Hold	t _{HV}	2	-	-		
	Cycle	t _{VP}	247	253	535	t _{HP}	
	Valid width	t _{WV}	2	2	-		
	Rise/Fall time	t _{Vr} ,t _{Vf}	-	-	50	ns	
DTMG	Set up time	t _{SI}	5	-	-	ns	for DCLK
	Hold time	t _{HI}	10	-	-		
	Rise/Fall time	t _{Ir} ,t _{If}	-	-	30	ns	
	Horizontal back porch	t _{HBP}	24	35	99	t _{CLK}	
	Horizontal front porch	t _{HFP}	8	30	62		
	Vertical back porch	t _{VBP}	7	9	197	t _{HP}	
	Vertical front porch	t _{VFP}	2	4	97		
Data	Set up time	t _{SD}	5	-	-	ns	for DCLK
	Hold time	t _{HD}	10	-	-		
	Rise/Fall time	t _{Dr} ,t _{Df}	-	-	20	ns	


Note : Vsync Cycle should be set to odd.

8.2.2 INTERFACE TIMING FOR VGA DISPLAY MODE

ITEM		SYMBOL	MIN.	TYP.	MAX.	UNIT	REMARKS
DCLK	Cycle time	t_{CLK}	37.4	47.8	58.1	ns	
	Low level Width	t_{WCL}	15	-	-		
	High level Width	t_{WCH}	15	-	-		
	Rise time	t_{rCLK}	-	-	25		
	Fall time	t_{fCLK}	-	-	25		
	Duty	D	0.45	0.5	0.55	-	$D = t_{CLKL} / t_{CLK}$
Hsync	Set up time	t_{SH}	5	-	-	ns	for DCLK
	Hold time	t_{HH}	10	-	-		
	Cycle	t_{HP}	679	709	739	t_{CLK}	
	Valid width	t_{WH}	4	5	5		
	Rise/Fall time	t_{Hr}, t_{Hf}	-	-	30	ns	
Vsync	Set up	t_{SV}	0	-	-	t_{CLK}	for Hsync
	Hold	t_{HV}	2	-	-		
	Cycle	t_{VP}	485	491	533	t_{HP}	
	Valid width	t_{WV}	2	2	2		
	Rise/Fall time	t_{Vr}, t_{Vf}	-	-	50	ns	
DTMG	Set up time	t_{SI}	5	-	-	ns	for DCLK
	Hold time	t_{HI}	10	-	-		
	Rise/Fall time	t_{Ir}, t_{If}	-	-	30	t_{CLK}	
	Horizontal back porch	t_{HBP}	24	37	50		
	Horizontal front porch	t_{HFP}	15	32	49	t_{HP}	
	Vertical back porch	t_{VBP}	4	7	28		
	Vertical front porch	t_{VFP}	1	4	25		
Data	Set up time	t_{SD}	5	-	-	ns	for DCLK
	Hold time	t_{HD}	10	-	-		
	Rise/Fall time	t_{Dr}, t_{Df}	-	-	25	ns	

Note : Vsync Cycle should be set to odd.

8.3 POWER ON/OFF SEQUENCE



POWER ON

$$\begin{aligned} t_1 &\leq 15\text{ms} \\ 0\text{ms} < t_2 &\leq 45\text{ms} \\ 0.1\text{s} &\leq t_3 \end{aligned}$$

POWER OFF

$$\begin{aligned} 5\text{ms} &\leq t_4 \\ 0\text{ms} &\leq t_5 \leq 45\text{ms} \\ 0\text{ms} &\leq t_6 \leq 20\text{ms} \\ 0.4\text{s} &\leq t_7 \end{aligned}$$

Note 1 : $0\text{V} \leq \text{VI}(t) \leq \text{VDD}(t)$

VI(t) and VDD(t) is a surfeit of condition for power on/off.

Note 2 : Input Voltage(Signal) should not be set high impedance when power on.

8.4 RELATIONSHIP BETWEEN DISPLAYED COLOR AND INPUT DATA

	COLOR & GRAY SCALE	DATA SIGNAL																	
		R5	R4	R3	R2	R1	R0	G5	G4	G3	G2	G1	G0	B5	B4	B3	B2	B1	B0
Basic Color	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red(0)	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	Green(0)	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	Blue(0)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
	Cyan	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	Magenta	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
Red	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red(62)	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
	Red(61)	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	Red(1)	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red(0)	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
Green	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Green(62)	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
	Green(61)	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	Green(1)	0	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0
	Green(0)	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
Blue	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue(62)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
	Blue(61)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:	:
	Blue(1)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	0
	Blue(0)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1

8.5 INTERNAL PIN CONNECTION

CN1 JAE : FA5B040HP1R3000(Au plating) (Suitable FPC : t0.3±0.03mm , 0.5±0.03mm pitch)


PIN No.	SIGNAL	FUNCTION
1	VDD	Power Supply for Logic
2	VDD	
3	VDD	
4	VDD	
5	NC	No Connection
6	DTMG	Timing Signal for Data
7	VSS	GND
8	DCLK	Dot Clock
9	VSS	GND
10	V/Q	Selection Signal for VGA or QVGA ("H" = VGA, "L" or "NC" = QVGA)
11	VSS	GND
12	B5	Blue Data
13	B4	
14	B3	
15	VSS	GND
16	B2	Blue Data
17	B1	
18	B0	
19	VSS	GND
20	G5	Green Data
21	G4	
22	G3	
23	VSS	GND
24	G2	Green Data
25	G1	
26	G0	
27	VSS	GND
28	R5	Red Data
29	R4	
30	R3	
31	VSS	GND
32	R2	Red Data
33	R1	
34	R0	
35	TEST	(Note 1)
36	VSS	GND
37	XT	Analog Signal From Digitizer TOP
38	YL	Analog Signal From Digitizer LEFT
39	XB	Analog Signal From Digitizer BOTTOM
40	YR	Analog Signal From Digitizer RIGHT

Note 1 : Keep open electrically , HITACHI test only.

CN2 JST Housing : BHR-03VS-1

PIN No.	SIGNAL	LEVEL	FUNCTION
1	V _{LED} ⁺	-	Power Supply for LED
2	NC	-	No connection
3	GND	-	GND for LED(OV)

9. DIMENSIONAL OUTLINE



Scale : NTS
Unit : mm


10. APPEARANCE STANDARD

10.1 APPEARANCE INSPECTION CONDITION


Visual inspection should be done under the following condition.

- (1) The inspection should be done in a dark room.
(about 1000(lx),500(lx)min. and non-directive)
- (2) The distance between eyes of an inspector and the LCD module is 30cm.
- (3) The viewing zone is shown the figure.

The θ is defined as $\theta \leq 45^\circ$ for LCM power off
 $\theta \leq 5^\circ$ for LCM power on



10.2 DEFINITION OF ZONE



10.3 APPEARANCE SPECIFICATION

(1)LCD Appearance

*) If the problem related to this section occurs about this item, the responsible persons of both party (Customer and HITACHI) will discuss the matter in detail.

No.	ITEM	CRITERIA				APPLIED ZONE
L C D	Scratches	Length L(mm)	Width W(mm)	Maximum number acceptable	Minimum space	A,B
		Ignored	$W \leq 0.02$	Ignored	-	
		$L \leq 40$	$0.02 < W \leq 0.04$	10	-	
		$L \leq 20$	$W \leq 0.04$	10	-	
	Dent	Distinguished one is acceptable (To be judged by HITACHI standard)				A
	Wrinkles in Polarizer	Same as above				A
	Bubbles	Average diameter D(mm)		Maximum number acceptable		A
		$D \leq 0.3$		Ignored		
		$0.3 < D \leq 0.5$		12		
		$0.5 < D$		3		
	Stains Foreign Materials Dark Spot	Filamentous (Line shape)				A,B
		Length L(mm)	Width W(mm)	Maximum number acceptable		
		$L \leq 2.0$	$W \leq 0.03$	Ignored		
		$L \leq 3.0$	$0.03 < W \leq 0.05$	10		
		$L \leq 2.5$	$0.05 < W \leq 0.1$	1		
		Round(Dot shape)				A,B
		Average diameter D(mm)	Maximum number acceptable	Minimum Space		
		$D < 0.2$	Ignored	-		
		$0.2 \leq D < 0.3$	10	10 mm		
		$0.3 \leq D < 0.4$	5	30 mm		
		$0.4 \leq D$	none	-		
		The total number	Filamentous + Round=10			
		Those wiped out easily are acceptable				
		Color Tone	To be judged by HITACHI STANDARD			
	Color Uniformity	Same as above				A
	Dot Defect			Maximum number acceptable		A
		Sparkle mode	1 dot	4		
2 dots (Note.(3)-(f))			1			
Total			5			
Black mode		1 dot	5			
		2 dots (Note.(3)-(f))	2			
		Total	5			
Total		10				

(2) LED BACKLIGHT APPEARANCE

No.	ITEM	CRITERIA			APPLIED ZONE
L E D B A C K L I G H T	Dark Spots	Average diameter D(mm)		Maximum number acceptable	A
	White Spots	$D \leq 0.4$		ignored	
	Foreign Materials (Spot)	$0.4 < D$		none	
	Foreign Materials (Line)	Width W(mm)	Length L(mm)	Maximum number acceptable	A
		$W \leq 0.2$	$L \leq 2.5$	1	
			$2.5 < L$	None	
		$0.2 < W$	-	none	
	Scratches	Width W(mm)	Length L(mm)	Maximum number acceptable	A
		$W \leq 0.1$	-	ignored	
		$0.1 < W \leq 0.2$	$L \leq 11.0$	1	
			$11.0 < L$	None	
		$0.2 < W$	-	none	

(3) Touch panel appearance

Visual inspection should be done under the following condition.

*) The inspection should be done in a dark room.




(about 1000(lx),500(lx)min. and non-directive)

*) The distance between eyes of an inspector and the LCD module is 30 cm.


*) The viewing angle $\leq 60^\circ$.

No.	ITEM	CRITERIA			APPLIED ZONE
T O U C H P A N E L	Scratches	Width W(mm)	Length L(mm)	Maximum number acceptable	A,B
		$W > 0.1$	$L \geq 10$	None	
		$0.10 \geq W > 0.05$	$L < 10$	4 pcs max.	
		$0.05 \geq W$	$L < 10$	Ignored	
	Foreign Materials	Filamentous (Line shape)			A,B
		Width W(mm)	Length L(mm)	Maximum number acceptable	
		$W > 0.10$	-	Dust (circular)	
		$0.10 \geq W > 0.05$	$3 < L$	None	
		$0.05 \geq W$	$L \leq 3$	Ignored	
		Round(Dot shape)			A,B
		Average diameter D(mm)		Maximum number acceptable	
		$D > 0.35$		None	
		$0.35 \geq D > 0.25$		6 psc max.	
		$D \leq 0.25$		Ignored	
	Newton Ring (Touch Panel)	Need to discuss with customer			A,B
	Touch Panel Uncleanliness	No conspicuous dirt			A
	Rubbing Scratch	To be judged by HITACHI standard			-


(4) Glass indentation

Glass Indentation								
ITEM	SPECIFICATIONS							
Common Indentation		<table><tr><td>X</td><td>Y</td><td>Z</td></tr><tr><td>≤ 5.0</td><td>≤ 3.0</td><td>≤ T</td></tr></table>	X	Y	Z	≤ 5.0	≤ 3.0	≤ T
	X	Y	Z					
≤ 5.0	≤ 3.0	≤ T						
Corner Broken		<table><tr><td>X</td><td>Y</td><td>Z</td></tr><tr><td>≤ 3.0</td><td>≤ 3.0</td><td>≤ T</td></tr></table>	X	Y	Z	≤ 3.0	≤ 3.0	≤ T
	X	Y	Z					
≤ 3.0	≤ 3.0	≤ T						
Proceeding Crack		None						


Blistering Puffiness



Note 1 : Definition of average diameter (D)



Note 2 : Definition of length (L) and width (W)



Note 3 : Definition of dot defect

(a) Dot Defect : Defect Area $> 1/2$ dot

(b) Sparkle mode : Brightness of dot is more than 30% at Black raster.

(c) Black mode : Brightness of dot is less than 70% at R.G.B raster.

(d) 1 dot : Defect dot is isolated , not attached to other defect dot.

(e) N dot : N defect dots are consecutive (fig.1).

(N means the number of defect dots.)

(fig .1)

R	G	B	R	G	B	R	G	B

2 dots defect included defect dot "X" is defined as follows.

Adjacent dots to defect dot "X" :


(f) Counting definition of adjacent dots (1 set) : same as 1 dot defect.

(g) Those wiped out easily are acceptable.

11. PRECAUTION IN DESIGN

11.1 MOUNTING PRECAUTION

(1) When assembling the Touch Panel on you case, please refer to the figure below.



(2) The clearance between the Touch Panel and case shall be designed so that the case edge never presses the input screen when it is deformed by heat or other causes.

(3) The case shall be designed not to touch the tail portion (FPC for Touch Panel).

(4) The boundary space between the effective area and the insulated area is unstable. Touching this area may effect the operation of the Touch Panel.
The case must be designed so that it does not touch the boundary space.

11.2 PRECAUTIONS AGAINST ELECTROSTATIC DISCHARGE

As this module contains C-MOS LSIs, it is not strong against electrostatic discharge. Make certain that the operator's body is connected to the ground through a list band , etc. And don't touch I/F pins directly.

11.3 HANDLING PRECAUTIONS

(1) Since the Touch Panel on the top, and the frame on the bottom tend to be easily damaged, they should be with full care so as not to get them touched, pushed or rubbed by a piece on glass, tweezers and anything else which are harder a pencil lead 2H.

(2) As the adhesives used for adhering upper/lower polarizer's and frame are made of organic substances which will be deteriorated by a chemical reaction with such chemicals as acetone, toluene, ethanol and isopropyl alcohol. The following are recommended for use :

normal hexane

Please contact with us when it is necessary for you to use chemicals other than the above.

- (3) Lightly wipe to clean the dirty surface with absorbent cotton or other soft material like chamois, soaked in the recommended chemicals without scrubbing it hardly. Always wipe the surface horizontally or vertically. Never give a wipe in a circle. To prevent the display surface from damage and keep the appearance in good state, it is sufficient, in general, to wipe it with absorbent cotton.
- (4) Immediately wipe off saliva or water drop attached on the display area because it may cause deformation or faded color.
- (5) Foggy dew deposited on the surface may cause a damage, stain or dirt to the polarizer.
When you need to take out the LCD module from some place at low temperature for test, etc.
It is required to be warmed them up to temperature higher than room temperature before taking them out.
- (6) Touching the display area or I/F pins with bare hands or contaminating them are prohibited, because the stain on the display area and poor insulation between terminals are often caused by being touched with bare hands.
(Some cosmetics are detrimental to polarizer's.)
- (7) In general, the glass is fragile so that, especially on its periphery, tends to be cracked or chipped in handling. Please not give the LCD module sharp shocks by falling, etc.
- (8) Maximum pressure to the surface must be less than 1.96×10^4 Pa.
And if the pressure area is less than 1cm^2 , maximum pressure must be less than 1.96N.
- (9) Since the metal width is narrow on these locations (see page 9-1/1), please careful with handling.
- (10) Top sheets shall be cleaned gently using a soft cloth such as those used for glasses.
Hard wiping accumulated dust will leave scars on the surface even using a cloth.

11.4 OPERATION PRECAUTION

- (1) Using a LCM module beyond its maximum ratings may result in its permanent destruction.
LCM module's should usually be used under recommended operating conditions shown in chapter 4. Exceeding any of these conditions may adversely affect its reliability.
- (2) Response time will be extremely delayed at lower temperature than the specified operating temperature range and on the other hand LCD's shows dark blue at higher temperature.
However those phenomena do not main defects of the LCD module. Those phenomena will disappear in the specified operating temperature range.

- (3) If the display area is pushed hard during operation, some display patterns will be abnormally display.
- (4) A slight dew depositing on terminals may cause electrochemical reaction which leads to terminal open circuit. Please operate the LCD module under the relative condition of 40°C 85%RH.
- (5) Resistance range : Your controller shall be set up to allow the resistance range of Touch Panel specified in our CAS.
- (6) Pointed position of Touch Panel may shift owing to a change in resistance of Touch Panel depending on the operation condition . To compensate this shift, the set shall be given a calibration function.
- (7) Input shall be made with a stylus pen (poly acetal , R0.8). Chances are very high that use of a metal piece including a ball point pen or sharp edge will impair accuracy.
- (8) The Touch Panel is an auxiliary input device. The system shall be designed to have other input device.

11.5 STORAGE

In case of storing LCD module for a long period of time (for instance, for years) for the purpose of replacement use, the following precautions necessary.

- (1) Store the LCD modules in a dark place; do not expose them to sunlight or ultraviolet rays.
- (2) Keep the temperature between 10°C and 35°C at normal humidity.
- (3) Store the LCD modules in the container which is used for shipping from us.
- (4) No articles shall be left on the surface over an extended period of time.


11.6 SAFETY

Wear finger cots or gloves whenever handling or assembling a Touch Panel its glass edges are sharp.

12. DESIGNATION OF LOT MARK

12.1 LOT MARK

Lot mark is consisted of 5 digits for production lot and 6 digits for production control.



Year	Figure in lot mark
2011	1
2012	2
2013	3
2014	4
2015	5

Month	Figure in lot mark	Month	Figure in lot mark
Jan.	01	Jul.	07
Feb.	02	Aug.	08
Mar.	03	Sep.	09
Apr.	04	Oct.	10
May	05	Nov.	11
Jun.	06	Dec.	12

Week (day in calendar)	Figure in lot mark
1~ 7	1
8~14	2
15~21	3
22~28	4
29~31	5

12.2 SERIAL No.

Serial No. is consisted of 6 digits number (000001~999999).

12.3 REVISION (Rev.) CONTROL


Rev. column is controlled by manufacturing A-Z except I and O is to be written on this column.

12.4 LOCATION OF LOT MARK

Label is bring attached on the back side of module.

12.5 REVISION(Rev.) CONTROL

Rev No.	ITEM
A	CN1 JAE : FA5B040HF1R3000
B	CN1 JAE : FA5B040HP1R3000



13. PRECAUTION FOR USE

- (1) A limit sample should be provided by the both parties on an occasion when the both parties agree to its necessity.

Judgment by a limit sample shall take effect after the limit sample has been established and confirmed by the both parties.

- (2) On the following occasions, the handling of the problem should be decided through discussion and agreement between responsible persons of the both parties.

(1) When a question is arisen in the specifications.

(2) When a new problem is arisen which is not specified in this specifications.

(3) When an inspection specifications change or operating condition change by customer is reported to HITACHI, and some problem is arisen in the specification due to the change.

(4) When a new problem is arisen at the customer's operating set for sample evaluation.

- (3) Regarding the treatment for maintenance and repairing, both parties will discuss it in six months later after latest delivery of this product.

The precaution that should be observed when handling LCM have been explained above.

If any points are unclear or if you have any requests , please contact with HITACHI.