

### LOW EMI CURRENT SENSE HIGH SIDE SWITCH


#### Features

- Load current feedback
- Over current shutdown
- Active clamp
- ESD protection
- Input referenced to Vcc
- Over temperature shutdown
- Switching time optimized for low EMI
- Reverse battery protection

#### Description

The AUIR3317(S) is a fully protected 4 terminals high side switch. The input signal is referenced to Vcc. When the input voltage  $V_{cc} - V_{in}$  is higher than the specified threshold, the output power Mosfet is turned on. When the  $V_{cc} - V_{in}$  is lower than the specified  $V_{il}$  threshold, the output Mosfet is turned off. A current proportional to the power Mosfet current is sourced to the Ifb pin. Either over current and over temperature latches off the switch. The device is reset by pulling the input pin high. Other integrated protections (ESD, reverse battery, active clamp) make the switch very rugged in automotive environment.

#### Typical Connection



#### Product Summary

|               |           |
|---------------|-----------|
| Rds(on)       | 7 mΩ max. |
| Vcc op.       | 6 to 26V  |
| Current Ratio | 8800      |
| Over-current  | 120A      |
| Vclamp        | 40V       |

#### Package



TO-220  
AUIR3317



D2Pak  
Pin 4 and 5 fused  
AUIR3317S

## Qualification Information<sup>†</sup>

|                                   |                      |                                                                                                                                                                               |                                          |
|-----------------------------------|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------|
| <b>Qualification Level</b>        |                      | Automotive<br>(per AEC-Q100 <sup>††</sup> )                                                                                                                                   |                                          |
|                                   |                      | Comments: This family of ICs has passed an Automotive qualification. IR's Industrial and Consumer qualification level is granted by extension of the higher Automotive level. |                                          |
| <b>Moisture Sensitivity Level</b> |                      | D2PAK-5L                                                                                                                                                                      | MSL1, 260°C<br>(per IPC/JEDEC J-STD-020) |
|                                   |                      | TO220-5L                                                                                                                                                                      | Not applicable                           |
| <b>ESD</b>                        | Machine Model        | Class M4 (450V)<br>(per AEC-Q100-003)                                                                                                                                         |                                          |
|                                   | Human Body Model     | Class H3A (4,500 V)<br>(per AEC-Q100-002)                                                                                                                                     |                                          |
|                                   | Charged Device Model | Class C4 (1000 V)<br>(per AEC-Q100-011)                                                                                                                                       |                                          |
| <b>IC Latch-Up Test</b>           |                      | Class II, Level A<br>(per AEC-Q100-004)                                                                                                                                       |                                          |
| <b>RoHS Compliant</b>             |                      | Yes                                                                                                                                                                           |                                          |

<sup>†</sup> Qualification standards can be found at International Rectifier's web site <http://www.irf.com/>

<sup>††</sup> Exceptions to AEC-Q100 requirements are noted in the qualification report.

## Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are referenced to Vcc lead. (Tj=-40°..150°C, Vcc=6..26V Tambient=25°C unless otherwise specified).

| Symbol        | Parameter                                                          | Min. | Max. | Units |
|---------------|--------------------------------------------------------------------|------|------|-------|
| Vcc-Vin       | Maximum Vcc voltage                                                | -16  | 37   | V     |
| Vcc-Vin cont. | Maximum continuous Vcc voltage                                     | -16  | 26   |       |
| Vcc-Vfb       | Maximum lfb voltage                                                | -16  | 33   |       |
| Vcc-Vout      | Maximum output voltage                                             | -0.3 | 37   |       |
| Ids cont.     | Maximum body diode continuous current Rth=60°C/W (1) Tambient=25°C | —    | 2.8  | A     |
| Ids pulsed    | Maximum body diode pulsed current (1)                              | —    | 100  |       |
| Pd            | Maximum power dissipation Rth=60°C/W Tambient=25°C                 | —    | 2    | W     |
| Tj max.       | Max. storage & operating temperature junction temperature          | -40  | 150  | °C    |
| Min Rfb       | Minimum on the resistor on lfb pin                                 | 0.3  | —    | kΩ    |
| lfb max.      | Max. lfb current                                                   | -50  | 50   | mA    |

(1) Limited by junction temperature. Pulsed is also limited by wiring

## Thermal Characteristics

| Symbol | Parameter                                                                | Typ. | Max. | Units |
|--------|--------------------------------------------------------------------------|------|------|-------|
| Rth1   | Thermal resistance junction to ambient D <sup>2</sup> -Pak Std footprint | 60   | —    | °C/W  |
| Rth2   | Thermal resistance junction to case D <sup>2</sup> -Pak                  | 0.7  | —    |       |
| Rth2   | Thermal resistance junction to case TO220                                | 0.7  | —    |       |

## Recommended Operating Conditions

These values are given for a quick design. For operation outside these conditions, please consult the application notes.

| Symbol     | Parameter                           | Min. | Max.    | Units |
|------------|-------------------------------------|------|---------|-------|
| Iout       | Continuous output current           | —    | 23<br>7 | A     |
|            | Tambient=85°C, Rth=5°C/W, Tj=125°C  |      |         |       |
|            | Tambient=85°C, Rth=60°C/W, Tj=125°C |      |         |       |
| Pulse min. | Minimum turn-on pulse width         | 1    | —       | ms    |
| Fmax.      | Maximum operating frequency         | —    | 200     | Hz    |

## Protection Characteristics

 $T_j = -40^{\circ}\text{C} \dots 150^{\circ}\text{C}$ ,  $V_{cc} = 6 \dots 26\text{V}$ 

| Symbol       | Parameter                                                         | Min. | Typ. | Max. | Units              | Test Conditions                                             |
|--------------|-------------------------------------------------------------------|------|------|------|--------------------|-------------------------------------------------------------|
| Tsd          | Over temperature threshold                                        | —    | 165  | —    | $^{\circ}\text{C}$ | See fig. 5                                                  |
| OV           | Over voltage protection (not latched)                             | 26   | 29   | 33   | V                  |                                                             |
| Isdf         | Fixed over current shutdown                                       | 90   | 120  | 150  | A                  | $V_{cc} - V_{ifb} > 4\text{V}(3)$                           |
| treset       | Time to reset protection                                          | —    | 50   | 500  | $\mu\text{s}$      | See fig. 5                                                  |
| Min. pulse   | Min. pulse width (no WAIT state)                                  | —    | 900  | 2000 |                    | $T_j = 25^{\circ}\text{C}$                                  |
| WAIT         | WAIT function timer                                               | 0.4  | 1    | 2    | ms                 | See fig. 4 and 5                                            |
| Rds(on) rev. | Reverse battery On state resistance<br>$T_j = 25^{\circ}\text{C}$ | 4    | 6.7  | 10   | $\text{m}\Omega$   | $V_{cc} - V_{in} = -14\text{V}$ ,<br>$I_{out} = 30\text{A}$ |
|              | $T_j = 125^{\circ}\text{C}$                                       | —    | 10   | 15   |                    |                                                             |

(3) With  $V_{cc} - V_{ifb} < 4\text{V}$ , the Isdf is lower than specified in the datasheet

## Static Electrical Characteristics

 $T_j = -40^{\circ}\text{C} \dots 150^{\circ}\text{C}$ ,  $V_{cc} = 6 \dots 26\text{V}$  (unless otherwise specified)

| Symbol   | Parameter                                              | Min. | Typ. | Max. | Units            | Test Conditions                                                                                                       |
|----------|--------------------------------------------------------|------|------|------|------------------|-----------------------------------------------------------------------------------------------------------------------|
| Vcc op.  | Operating Voltage range                                | 6    | —    | 26   | V                |                                                                                                                       |
| Icc off  | Supply leakage current                                 | —    | 1.5  | 5    | $\mu\text{A}$    | $V_{in} = V_{cc}$ , $V_{cc} - V_{out} = 14\text{V}$ ,<br>$V_{cc} - V_{ifb} = 14\text{V}$ , $T_j = 25^{\circ}\text{C}$ |
| Iin, on  | On state IN positive current                           | 1.5  | 3    | 6    | mA               | $V_{cc} - V_{in} = 14\text{V}$ , $T_j = 25^{\circ}\text{C}$                                                           |
| Vih      | High level Input threshold voltage (4)                 | —    | 5.4  | 6.3  | V                |                                                                                                                       |
| Vil      | Low level Input threshold voltage (4)                  | 4    | 4.9  | 5.8  |                  |                                                                                                                       |
| Vhyst    | Input hysteresis Vih-Vil                               | 0.2  | 0.4  | 1.5  |                  |                                                                                                                       |
| Iout     | Drain to source leakage current                        | —    | 1.2  | 5    | $\mu\text{A}$    | $V_{in} = V_{cc}$ , $V_{cc} - V_{ifb} = 0\text{V}$ ,<br>$V_{cc} - V_{out} = 14\text{V}$ , $T_j = 25^{\circ}\text{C}$  |
| Rds(on)  | On state resistance (5) $T_j = 25^{\circ}\text{C}$     | 4    | 5.5  | 7    | $\text{m}\Omega$ | $I_{out} = 30\text{A}$ , $V_{cc} - V_{in} = 14\text{V}$                                                               |
|          | On state resistance (5) $T_j = 25^{\circ}\text{C}$     | 4    | 6    | 10   |                  | $I_{out} = 17\text{A}$ , $V_{cc} - V_{in} = 6\text{V}$                                                                |
|          | On state resistance (5)(6) $T_j = 150^{\circ}\text{C}$ | 7    | 10.5 | 13.5 |                  | $I_{out} = 30\text{A}$ , $V_{cc} - V_{in} = 14\text{V}$                                                               |
| V clamp1 | Vcc to Vout clamp voltage 1                            | 36   | 39   | —    | V                | $I_{out} = 50\text{mA}$                                                                                               |
| V clamp2 | Vcc to Vout clamp voltage 2                            | —    | 40   | 43   |                  | $I_{out} = 30\text{A}$ , $T_j = 25^{\circ}\text{C}$                                                                   |

(4) Input thresholds are measured directly between the input pin and the tab. Any parasitic resistance in common between the load current path and the input signal path can significantly affect the thresholds.

(5) Rdson is measured between the tab and the Out pin, 5mm away from the package.

(6) Guaranteed by design

## Switching Electrical Characteristics

 $V_{cc} = 14\text{V}$ , Resistive load =  $0.5\Omega$ ,  $T_j = 25^{\circ}\text{C}$ 

| Symbol | Parameter                     | Min. | Typ. | Max. | Units | Test Conditions |
|--------|-------------------------------|------|------|------|-------|-----------------|
| tdon   | Turn on delay time to 10% Vcc | 30   | 120  | 300  | μs    | See figure 2    |
| tr1    | Rise time to Vcc-Vout=5V      | 20   | 50   | 125  |       |                 |
| tr2    | Rise time to Vcc-Vout=0.1Vcc  | 30   | 80   | 200  |       |                 |
| Eon    | Turn on energy                | —    | 14   | —    | mJ    |                 |
| tdoff  | Turn off delay time           | 30   | 140  | 350  | μs    |                 |
| tf     | Fall time to Vout=10% of Vcc  | 35   | 100  | 250  |       |                 |
| Eoff   | Turn off energy               | —    | 7    | —    | mJ    |                 |


## Current Sense Characteristics

$T_j = -40^{\circ}\text{C} \dots 150^{\circ}\text{C}$ ,  $V_{cc} = 6 \dots 26\text{V}$  (unless otherwise specified)

| Symbol   | Parameter                                            | Min.  | Typ.  | Max.  | Units | Test Conditions                              |
|----------|------------------------------------------------------|-------|-------|-------|-------|----------------------------------------------|
| Ratio    | I Load/I <sub>fb</sub> current ratio                 | 8,200 | 8,800 | 9,950 | —     | R <sub>fb</sub> =500Ω, I <sub>out</sub> =60A |
| Ratio_TC | I Load/I <sub>fb</sub> variation aver temperature(6) | -5    | —     | +5    | %     | T <sub>j</sub> =-40°C to 150°C               |
| Offset   | Load current diagnostic offset                       | -0.2  | 0     | +0.25 | A     | I <sub>out</sub> =2A                         |
| trst     | I <sub>fb</sub> response time (low signal)           | —     | 1     | —     | μs    | 90% of the I <sub>out</sub> step             |

## Functional Block Diagram

All values are typical



## Lead Assignments





Figure 1 – Voltages and current definitions







Figure 2 – Switching time definitions



**Figure 3 – Active clamp waveforms**




**Figure 4 – Min. pulse and Wait function**




**Figure 5 – Protection Timing Diagrams**


All curves are typical characteristics. Operation in hatched areas is not recommended.  $T_j=25^{\circ}\text{C}$ ,  $R_{\text{fth}}=500\text{ohm}$ ,  $V_{\text{cc}}=14\text{V}$  (unless otherwise specified).




**Figure 6 – Icc (mA) Vs Vcc-Vin (V)**



**Figure 7 – Icc off (µA) Vs Tj (°C)**



**Figure 8 - Normalized Rds(on) (%) Vs Tj (°C)**



**Figure 9 – Vih and Vil (V) Vs Tj (°C)**




Figure 10 – Error (+/- A) Vs I load (A)




Figure 11 – Ids (A) Vs Rifb (Ω)




Figure 12 – Max. iout (A) Vs Tamb. (°C)




Figure 13 – Max. iout (A) Vs inductance (μH)




Figure 14 –  $I_{ds}$  (A) Vs over temperature protection response time (s)






Figure 15 – Transient thermal impedance (°C/W) Vs time (s)


**Case Outline - TO220 - 5 Leads**








| C O M P O N E N T | D I M E N S I O N S   |         |             |         | N O T E S |
|-------------------|-----------------------|---------|-------------|---------|-----------|
|                   | M I L L I M E T E R S |         | I N C H E S |         |           |
|                   | M I N .               | M A X . | M I N .     | M A X . |           |
| A                 | 3.56                  | 4.83    | .140        | .190    |           |
| A1                | 0.51                  | 1.40    | .020        | .055    |           |
| A2                | 2.03                  | 2.92    | .080        | .115    |           |
| b                 | 0.64                  | 0.89    | .025        | .035    | 5         |
| b1                | 0.64                  | 0.84    | .025        | .033    |           |
| c                 | 0.36                  | 0.61    | .014        | .024    |           |
| c1                | 0.36                  | 0.56    | .014        | .022    | 5         |
| D                 | 14.22                 | 16.51   | .560        | .650    | 4         |
| D1                | 8.38                  | 9.02    | .330        | .355    |           |
| D2                | 11.68                 | 12.88   | .460        | .507    | 7         |
| E                 | 9.65                  | 10.67   | .380        | .420    | 4, 7      |
| E1                | 6.86                  | 8.89    | .270        | .350    | 7         |
| E2                |                       | 0.76    | —           | .030    | 8         |
| e                 | 1.70 BSC              |         | .067 BSC    |         |           |
| H1                | 5.84                  | 6.86    | .230        | .270    | 7, 8      |
| L                 | 12.70                 | 14.73   | .500        | .580    |           |
| φP                | 3.53                  | 3.73    | .139        | .147    |           |
| Q                 | 2.54                  | 3.05    | .100        | .120    |           |


**NOTES:**

- 1.- DIMENSIONING AND TOLERANCING AS PER ASME Y14.5 M- 1994.
- 2.- DIMENSIONS ARE SHOWN IN INCHES [MILLIMETERS].
- 3.- LEAD DIMENSION AND FINISH UNCONTROLLED IN L1.
- 4.- DIMENSION D, D1 & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5.- DIMENSION b1 & c1 APPLY TO BASE METAL ONLY.
- 6.- CONTROLLING DIMENSION : INCHES.
- 7.- THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS E,H1,D2 & E1.
- 8.- DIMENSION E2 X H1 DEFINE A ZONE WHERE STAMPING AND SINGULATION IRREGULARITIES ARE ALLOWED.
- 9.- OUTLINE CONFORMS TO JEDEC TO-220, EXCEPT A2 (max.) AND D2 (min.) WHERE DIMENSIONS ARE DERIVED FROM THE ACTUAL PACKAGE OUTLINE.
- 10.- LEADS AND DRAIN ARE PLATED WITH 100% Sn






FOOT PRINT  
SCALE 2:1




| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 |       |
| A1     |             | 0.254 |          | .010 |       |
| b      | 0.66        | 0.91  | .026     | .036 | 4     |
| b1     | 0.66        | 0.81  | .026     | .032 |       |
| c      | 0.38        | 0.74  | .015     | .029 |       |
| c1     | 0.38        | 0.58  | .015     | .023 | 4     |
| d      | 1.14        | 1.65  | .045     | .065 |       |
| D      | 8.51        | 9.65  | .335     | .380 | 3     |
| D1     | 6.86        |       | .270     |      |       |
| E      | 9.65        | 10.67 | .380     | .420 | 3     |
| E1     | 6.22        |       | .245     |      |       |
| e      | 1.70 BSC    |       | .067 BSC |      |       |
| H      | 14.73       | 15.49 | .580     | .609 |       |
| L      | 1.14        | 1.39  | .045     | .055 |       |
| L1     |             | 1.65  |          | .065 |       |
| L2     | 1.27        | 1.78  | .050     | .070 |       |
| L3     | 0.25 BSC    |       | .010 BSC |      |       |
| L4     | 4.78        | 5.28  | .188     | .208 |       |
| m      | 17.78       |       | .700     |      |       |
| m1     | 8.89        |       | .350     |      |       |
| n      | 11.43       |       | .450     |      |       |
| o      | 1.93        |       | .076     |      |       |
| p      | 3.81        |       | .150     |      |       |
| P      | 0.51        | 0.71  | .020     | .028 |       |

6. LEADS AND DRAIN ARE FILLED WITH 100%  $S_0$

## Tape & Reel - D2PAK – 5 leads



**Part Marking Information**



**Ordering Information**

| Base Part Number | Package Type   | Standard Pack       |          | Complete Part Number |
|------------------|----------------|---------------------|----------|----------------------|
|                  |                | Form                | Quantity |                      |
| AUIR3317         | TO220 – 5Leads | Tube                | 50       | AUIR3317             |
|                  | D2Pak – 5Leads | Tube                | 50       | AUIR3317S            |
|                  |                | Tape and reel left  | 800      | AUIR3317STRL         |
|                  |                | Tape and reel right | 800      | AUIR3317STRR         |

### **IMPORTANT NOTICE**

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

Only products certified as military grade by the Defense Logistics Agency (DLA) of the US Department of Defense, are designed and manufactured to meet DLA military specifications required by certain military, aerospace or other applications. Buyers acknowledge and agree that any use of IR products not certified by DLA as military-grade, in applications requiring military grade products, is solely at the Buyer's own risk and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

For technical support, please contact IR's Technical Assistance Center  
<http://www.irf.com/technical-info/>

**WORLD HEADQUARTERS:**

101 N. Sepulveda Blvd., El Segundo, California 90245  
Tel: (310) 252-7105

## Revision History

| Revision | Date       | Notes/Changes                     |
|----------|------------|-----------------------------------|
| A        |            | First release                     |
| B        | 10/06/2010 | AU release                        |
| C        | 25/08/2011 | Add test condition to Isdf page 4 |
|          |            |                                   |
|          |            |                                   |
|          |            |                                   |
|          |            |                                   |
|          |            |                                   |
|          |            |                                   |