+3 V/+5 V/±5 V CMOS 4- and 8-Channel Analog Multiplexers

ADG658/ADG659

FEATURES

±2 V to ±6 V dual supply
2 V to 12 V single supply
Automotive temperature range −40°C to +125°C
<0.1 nA leakage currents
45 Ω on resistance over full signal range
Rail-to-rail switching operation
Single 8-to-1 multiplexer ADG658
Differential 4-to-1 multiplexer ADG659
16-lead LFCSP/TSSOP/QSOP packages
Typical power consumption <0.1 µW
TTL/CMOS compatible inputs
Package upgrades to 74HC4051/74HC4052 and MAX4051/MAX4052/MAX4581/MAX4582

APPLICATIONS

Automotive applications
Automatic test equipment
Data acquisition systems
Battery-powered systems
Communication systems
Audio and video signal routing
Relay replacement
Sample-and-hold systems
Industrial control systems

FUNCTIONAL BLOCK DIAGRAM



Figure 1.

GENERAL DESCRIPTION

The ADG658 and ADG659 are low voltage, CMOS analog multiplexers comprised of eight single channels and four differential channels, respectively. The ADG658 switches one of eight inputs (S1–S8) to a common output, D, as determined by the 3-bit binary address lines A0, A1, and A2. The ADG659 switches one of four differential inputs to a common differential output, as determined by the 2-bit binary address lines A0 and A1. An $\overline{EN}$ input on both devices is used to enable or disable the device. When disabled, all channels are switched off.

These parts are designed on an enhanced process that provides lower power dissipation yet gives high switching speeds. These parts can operate equally well as either multiplexers or demultiplexers and have an input range that extends to the supplies. All channels exhibit break-before-make switching action, preventing momentary shorting when switching channels. All digital inputs have 0.8 V to 2.4 V logic thresholds, ensuring TTL/CMOS logic compatibility when using single +5 V or dual ±5 V supplies.

The ADG658 and ADG659 are available in 16-lead TSSOP/QSOP packages and 16-lead 4 mm × 4 mm LFCSP packages.

PRODUCT HIGHLIGHTS

1. Single- and dual-supply operation. The ADG658 and ADG659 offer high performance and are fully specified and guaranteed with ±5 V, +5 V, and +3 V supply rails.
2. Automotive temperature range −40°C to +125°C.
3. Low power consumption, typically <0.1 µW.
4. 16-lead 4 mm × 4 mm LFCSP packages, 16-lead TSSOP package and 16-lead QSOP package.

Rev. B
Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 **www.analog.com**
Fax: 781.461.3113 **©2004–2009 Analog Devices, Inc. All rights reserved.**

TABLE OF CONTENTS

Features 1
Applications 1
Functional Block Diagram 1
General Description 1
Product Highlights 1
Revision History 2
Specifications 3
Dual Supply 3
5 V Single Supply 5
2.7 V to 3.6 V Single Supply 7
Absolute Maximum Ratings 9
ESD Caution 9
Pin Configurations and Function Descriptions 11
Typical Performance Characteristics 13
Test Circuits 16
Outline Dimensions 19
Ordering Guide 20

REVISION HISTORY

2/09—Rev. A to Rev. B

Changes to Ordering Guide 20

7/04—Rev. 0 to Rev. A

Updated Format ..... Universal
Added QSOP Package Outline 20
Changes to Ordering Guide 20

3/03—Rev. 0: Initial Version

SPECIFICATIONS

DUAL SUPPLY

V_{DD} = +5 V ± 10%, V_{SS} = −5 V ± 10%, GND = 0 V, unless otherwise noted.

Table 1.

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to+125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			V_{SS} to V_{DD}	V	V_{DD} = +4.5 V, V_{SS} = −4.5 V
On Resistance (R_{ON})	45			Ω typ	V_S = ±4.5 V, I_S = 1 mA; see Figure 21
	75	90	100	Ω max	
On Resistance Match between	1.3			Ω typ	
Channels (ΔR_{ON})	3	3.2	3.5	Ω max	V_S = 3.5 V, I_S = 1 mA
On Resistance Flatness ($R_{FLAT(ON)}$)	10			Ω typ	V_{DD} = +5 V, V_{SS} = −5 V;
	16	17	18	Ω max	V_S = ±3 V, I_S = 1 mA
LEAKAGE CURRENTS					V_{DD} = +5.5 V, V_{SS} = −5.5 V
Source OFF Leakage I_S (OFF)	±0.005			nA typ	V_D = ±4.5 V, V_S = ∓ 4.5 V; see Figure 22
	±0.2		±5	nA max	
Drain OFF Leakage I_D (OFF)	±0.005			nA typ	V_D = ±4.5 V, V_S = ∓ 4.5 V; see Figure 23
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
Channel ON Leakage I_D, I_S (ON)	±0.005			nA typ	V_D = V_S = ±4.5 V; see Figure 24
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.4	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current					
I_{INL} or I_{INH}	0.005			μA typ	V_{IN} = V_{INL} or V_{INH}
			±1	μA max	
C_{IN}, Digital Input Capacitance	2			pF typ	
DYNAMIC CHARACTERISTICS[1]					
$t_{TRANSITION}$	80			ns typ	R_L = 300 Ω, C_L = 35 pF
	115	140	165	ns max	V_S = 3 V; see Figure 25
t_{ON} ($\overline{EN}$)	80			ns typ	R_L = 300 Ω, C_L = 35 pF
	115	140	165	ns max	V_S = 3 V; see Figure 27
t_{OFF} ($\overline{EN}$)	30			ns typ	R_L = 300 Ω, C_L = 35 pF
	45	50	55	ns max	V_S = 3 V; see Figure 27
Break-Before-Make Time Delay, t_{BBM}	50			ns typ	R_L = 300 Ω, C_L = 35 pF
			10	ns min	V_{S1} = V_{S2} = 3 V; see Figure 26
Charge Injection	2			pC typ	V_S = 0 V, R_S = 0 Ω,
	4			pC max	C_L = 1 nF; see Figure 28
Off Isolation	−90			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 29
Total Harmonic Distortion, THD + N	0.025			% typ	R_L = 600 Ω, 2 V p-p, f = 20 Hz to 20 kHz
Channel-to-Channel Crosstalk (ADG659)	−90			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 31
−3 dB Bandwidth					
ADG658	210			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 30
ADG659	400			MHz typ	

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to+125°C	Unit	Test Conditions/Comments
C_S (OFF)	4			pF typ	f = 1 MHz
C_D (OFF)					
ADG658	23			pF typ	f = 1 MHz
ADG659	12			pF typ	f = 1 MHz
C_D, C_S (ON)					
ADG658	28			pF typ	f = 1 MHz
ADG659	16			pF typ	f = 1 MHz
POWER REQUIREMENTS					V_{DD} = +5.5 V, V_{SS} = −5.5 V
I_{DD}	0.01			µA typ	Digital Inputs = 0 V or 5.5 V
			1	µA max	
I_{SS}	0.01			µA typ	Digital Inputs = 0 V or 5.5 V
			1	µA max	

[1] Guaranteed by design; not subject to production test.

5 V SINGLE SUPPLY

V_{DD} = 5 V ± 10%, V_{SS} = 0 V, GND = 0 V, unless otherwise noted.

Table 2.

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			0 to V_{DD}	V	V_{DD} = 4.5 V, V_{SS} = 0 V
On Resistance (R_{ON})	85			Ω typ	V_S = 0 V to 4.5 V, I_S = 1 mA; see Figure 21
	150	160	200	Ω max	
On Resistance Match between	4.5			Ω typ	V_S = 3.5 V, I_S = 1 mA
Channels (ΔR_{ON})	8	9	10	Ω max	
On Resistance Flatness ($R_{FLAT(ON)}$)	13	14	16	Ω typ	V_{DD} = 5 V, V_{SS} = 0 V, V_S = 1.5 V to 4 V, I_S = 1 mA
LEAKAGE CURRENTS					V_{DD} = 5.5 V
Source OFF Leakage I_S (OFF)	±0.005			nA typ	V_S = 1 V/4.5 V, V_D = 4.5 V/1 V; see Figure 22
	±0.2		±5	nA max	
Drain OFF Leakage I_D (OFF)	±0.005			nA typ	V_S = 1 V/4.5 V, V_D = 4.5 V/1 V; see Figure 23
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
Channel ON Leakage I_D, I_S (ON)	±0.005			nA typ	V_S = V_D = 1 V or 4.5 V, see Figure 24
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.4	V min	
Input Low Voltage, V_{INL}			0.8	V max	
Input Current					
I_{INL} or I_{INH}	0.005			μA typ	V_{IN} = V_{INL} or V_{INH}
			±1	μA max	
C_{IN}, Digital Input Capacitance	2			pF typ	
DYNAMIC CHARACTERISTICS[1]					
$t_{TRANSITION}$	120			ns typ	R_L = 300 Ω, C_L = 35 pF
	200	270	300	ns max	V_S = 3 V; see Figure 25
t_{ON} ($\overline{EN}$)	120			ns typ	R_L = 300 Ω, C_L = 35 pF
	190	245	280	ns max	V_S = 3 V; see Figure 27
t_{OFF} ($\overline{EN}$)	35			ns typ	R_L = 300 Ω, C_L = 35 pF
	50	60	70	ns max	V_S = 3 V; see Figure 27
Break-Before-Make Time Delay, t_{BBM}	100			ns typ	R_L = 300 Ω, C_L = 35 pF
			10	ns min	V_{S1} = V_{S2} = 3 V; see Figure 26
Charge Injection	0.5			pC typ	V_S = 2.5 V, R_S = 0 Ω, C_L = 1 nF; see Figure 28
	1			pC max	
Off Isolation	−90			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 29
Channel-to-Channel Crosstalk (ADG659)	−90			dB typ	R_L = 50 Ω, C_L = 5 pF; f = 1 MHz; see Figure 31
−3 dB Bandwidth					
ADG658	180			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 30
ADG659	330			MHz typ	
C_S (OFF)	5			pF typ	f = 1 MHz
C_D (OFF)					
ADG658	29			pF typ	f = 1 MHz
ADG659	15			pF typ	f = 1 MHz

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to +125°C	Unit	Test Conditions/Comments
C_D, C_S (ON)					
ADG658	30			pF typ	f = 1 MHz
ADG659	16			pF typ	f = 1 MHz
POWER REQUIREMENTS					V_{DD} = 5.5 V
I_{DD}	0.01			µA typ	Digital Inputs = 0 V or 5.5 V
			1	µA max	

[1] Guaranteed by design; not subject to production test.

2.7 V TO 3.6 V SINGLE SUPPLY

V_{DD} = 2.7 to 3.6 V, V_{SS} = 0 V, GND = 0 V, unless otherwise noted.

Table 3.

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to +125°C	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range			0 to V_{DD}	V	V_{DD} = 2.7 V, V_{SS} = 0 V
On Resistance (R_{ON})	185			Ω typ	V_S = 0 V to 2.7 V, I_S = 0.1 mA; see Figure 21
	300	350	400	Ω max	
On Resistance Match between	2			Ω typ	V_S = 1.5 V, I_S = 0.1 mA
Channels (ΔR_{ON})	4.5	6	7	Ω max	
LEAKAGE CURRENTS					V_{DD} = 3.3 V
Source OFF Leakage I_S (OFF)	±0.005			nA typ	V_S = 1 V/3 V, V_D = 3 V/1 V; see Figure 22
	±0.2		±5	nA max	
Drain OFF Leakage I_D (OFF)	±0.005			nA typ	V_S = 1 V/3 V, V_D = 3 V/1 V; see Figure 23
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
Channel ON Leakage I_D, I_S (ON)	±0.005			nA typ	V_S = V_D = 1 V or 3 V, see Figure 24
ADG658	±0.2		±5	nA max	
ADG659	±0.1		±2.5	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{INH}			2.0	V min	
Input Low Voltage, V_{INL}			0.5	V max	
Input Current					
I_{INL} or I_{INH}	0.005			μA typ	V_{IN} = V_{INL} or V_{INH}
			±1	μA max	
C_{IN}, Digital Input Capacitance	2			pF typ	
DYNAMIC CHARACTERISTICS[1]					
$t_{TRANSITION}$	200			ns typ	R_L = 300 Ω, C_L = 35 pF
	370	440	490	ns max	V_S = 1.5 V; see Figure 25
t_{ON} ($\overline{EN}$)	230			ns typ	R_L = 300 Ω, C_L = 35 pF
	370	440	490	ns max	V_S = 1.5 V; see Figure 27
t_{OFF} ($\overline{EN}$)	50			ns typ	R_L = 300 Ω, C_L = 35 pF
	80	90	110	ns max	V_S = 1.5 V; see Figure 27
Break-Before-Make Time Delay, t_{BBM}	200			ns typ	R_L = 300 Ω, C_L = 35 pF
			10	ns min	V_{S1} = V_{S2} = 1.5 V; see Figure 26
Charge Injection	1			pC typ	V_S = 1.5 V, R_S = 0 Ω, C_L = 1 nF; see Figure 28
	2			pC max	
Off Isolation	−90			dB typ	R_L = 50 Ω, C_L = 5 pF, f = 1 MHz; see Figure 29
Channel-to-Channel Crosstalk (ADG659)	−90			dB typ	R_L = 50 Ω, C_L = 5 pF; f = 1 MHz; see Figure 31
−3 dB Bandwidth					
ADG658	160			MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 30
ADG659	300			MHz typ	
C_S (OFF)	5			pF typ	f = 1 MHz
C_D (OFF)					
ADG658	29			pF typ	f = 1 MHz
ADG659	15			pF typ	f = 1 MHz

Parameter	+25°C	B Version −40°C to +85°C	Y Version −40°C to +125°C	Unit	Test Conditions/Comments
C_D, C_S (ON)					
ADG658	30			pF typ	f = 1 MHz
ADG659	16			pF typ	f = 1 MHz
POWER REQUIREMENTS					V_{DD} = 3.6 V
I_{DD}	0.01			μA typ	Digital Inputs = 0 V or 3.6 V
			1	μA max	

[1] Guaranteed by design; not subject to production test.

ABSOLUTE MAXIMUM RATINGS

T_A = 25°C, unless otherwise noted.

Table 4.

Parameter	Rating
V_{DD} to V_{SS}	13 V
V_{DD} to GND	−0.3 V to +13 V
V_{SS} to GND	+0.3 V to −6.5 V
Analog Inputs[1]	V_{SS} − 0.3 V to V_{DD} + 0.3 V
Digital Inputs[1]	GND − 0.3 V to V_{DD} + 0.3 V or 10 mA, whichever occurs first
Peak Current, S or D	40 mA
(Pulsed at 1 ms, 10% duty cycle max)	
Continuous Current, S or D	20 mA
Operating Temperature Range	
Automotive (Y Version)	−40°C to +125°C
Industrial (B Version)	−40°C to +85°C
Storage Temperature Range	−65°C to +150°C
Junction Temperature	150°C
θ_{JA} Thermal Impedance	
16-Lead QSOP	104°C/W
16-Lead TSSOP	150.4°C/W
16-Lead LFCSP (4-Layer Board)	70°C/W
Lead Temperature, Soldering	
Vapor Phase (60 sec)	215°C
Infrared (15 sec)	220°C
ESD	5.5 kV

[1] Over voltages at A_x, $\overline{EN}$, S, or D are clamped by internal diodes. Current should be limited to the maximum ratings.

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ESD CAUTION

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Table 5. ADG658 Truth Table

A2	A1	A0	$\overline{EN}$	Switch Condition
X[1]	X[1]	X[1]	1	None
0	0	0	0	1
0	0	1	0	2
0	1	0	0	3
0	1	1	0	4
1	0	0	0	5
1	0	1	0	6
1	1	0	0	7
1	1	1	0	8

[1] X = Don't Care

Table 6. ADG659 Truth Table

A1	A0	$\overline{EN}$	On Switch Pair
X[1]	X[1]	1	None
0	0	0	1
0	1	0	2
1	0	0	3
1	1	0	4

[1] X = Don't Care

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS



Figure 2. 16-Lead TSSOP/QSOP Pin Configuration



Figure 3. 16-Lead, 4 mm × 4 mm LFCSP Pin Configuration

Table 7. Pin Function Descriptions

Parameter	Description
V_{DD}	Most Positive Power Supply Potential.
V_{SS}	Most Negative Power Supply Potential.
I_{DD}	Positive Supply Current.
I_{SS}	Negative Supply Current.
GND	Ground (0 V) Reference.
S	Source Terminal. May be an input or output.
D	Drain Terminal. May be an input or output.
A_X	Logic Control Input.
$\overline{EN}$	Active Low Digital Input. When high, device is disabled and all switches are OFF. When low, A_X logic inputs determine ON switch.
V_D (V_S)	Analog Voltage on Terminals D, S.
R_{ON}	Ohmic Resistance between D and S.
ΔR_{ON}	On Resistance Match between Any Two Channels, i.e., R_{ON}max − R_{ON}min.
$R_{FLAT(ON)}$	Flatness is defined as the difference between the maximum and minimum value of ON Resistance as measured over the specified analog signal range.
I_S (OFF)	Source Leakage Current with the Switch OFF.
I_D (OFF)	Drain Leakage Current with the Switch OFF.
I_D, I_S (ON)	Channel Leakage Current with the Switch ON.
V_{INL}	Maximum Input Voltage for Logic 0.
V_{INH}	Minimum Input Voltage for Logic 1.
I_{INL} (I_{INH})	Input Current of the Digital Input.
C_S (OFF)	OFF Switch Source Capacitance. Measured with reference to ground.
C_D (OFF)	OFF Switch Drain Capacitance. Measured with reference to ground.
C_D, C_S (ON)	ON Switch Capacitance. Measured with reference to ground.
C_{IN}	Digital Input Capacitance.

Parameter	Description
t_{ON}	Delay between Applying the Digital Control Input and the Output Switching ON. See Test Circuit 7.
t_{OFF}	Delay between Applying the Digital Control Input and the Output Switching OFF.
t_{BBM}	ON Time. Measured between 80% points of both switches when switching from one address state to another.
Charge Injection	Measure of the Glitch Impulse Transferred from the Digital Input to the Analog Output during Switching.
Off Isolation	Measure of Unwanted Signal Coupling through an OFF Switch.
Crosstalk	Measure of Unwanted Signal Coupled through from One Channel to Another as a Result of Parasitic Capacitance.
Bandwidth	The Frequency at which the Output is Attenuated by 3 dB.
On Response	The Frequency Response of the ON Switch.
Insertion Loss	The Loss Due to the ON Resistance of the Switch.

TYPICAL PERFORMANCE CHARACTERISTICS



Figure 4. On Resistance vs. V_D (V_S) for Dual Supply



Figure 7. On Resistance vs. V_D (V_S) for Different Temperatures (Single Supply)



Figure 5. On Resistance vs. V_D (V_S) for Single Supply



Figure 8. On Resistance vs. V_D (V_S) for Different Temperatures (Single Supply)



Figure 6. On Resistance vs. V_D (V_S) for Different Temperatures (Dual Supply)



Figure 9. Leakage Current vs. Temperature (Dual Supply)



Figure 10. Leakage Current vs. Temperature (Single Supply)



Figure 13. t_{ON}/t_{OFF} Times vs. Temperature (Single Supply)



Figure 11. Charge Injection vs. Source Voltage



Figure 14. ON Response vs. Frequency (ADG658)



Figure 12. t_{ON}/t_{OFF} Times vs. Temperature (Dual Supply)



Figure 15. ON Response vs. Frequency (ADG659)



Figure 16. OFF Isolation vs. Frequency



Figure 17. Crosstalk vs. Frequency



Figure 18. THD + Noise



Figure 19. V_{DD} Current vs. Logic Level



Figure 20. Logic Threshold Voltage vs. Supply Voltage

TEST CIRCUITS



Figure 21. ON Resistance



Figure 23. I_D (OFF)



Figure 22. I_S (OFF)



Figure 24. I_D (ON)





Figure 25. Switching Time of Multiplexer, $t_{TRANSITION}$



Figure 26. Break-Before-Make Delay, t_{BBM}



Figure 27. Enable Delay, t_{ON} ($\overline{EN}$), t_{OFF} ($\overline{EN}$)



Figure 28. Charge Injection



Figure 29. Off Isolation



Figure 30. Bandwidth



Figure 31. Channel-to-Channel Crosstalk

OUTLINE DIMENSIONS



COMPLIANT TO JEDEC STANDARDS MO-153AB

Figure 32. 16-Lead Thin Shrink Small Outline Package [TSSOP]
(RU-16)
Dimensions shown in millimeters



COMPLIANT TO JEDEC STANDARDS MO-220-VGGC

Figure 33. 16-Lead Lead Frame Chip Scale Package [LFCSP]
(CP-16-4)
Dimensions shown in millimeters



Figure 34. 16-Lead Shrink Small Outline Package [QSOP]
(RQ-16)
Dimensions shown in millimeters

ORDERING GUIDE

Model	Temperature Range	Package Description	Package Option
ADG658YRU	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG658YRU-REEL7	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG658YRUZ[1]	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG658YRUZ-REEL7[1]	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG658YCP	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG658YCP-REEL7	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG658YCPZ[1]	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG658YRQ	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG658YRQ-REEL	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG658YRQZ[1]	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG658YRQZ-REEL7[1]	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG659YRU	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG659YRU-REEL7	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG659YRUZ[1]	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG659YRUZ-REEL7[1]	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG659WYRUZ-REEL7[1, 2]	−40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	RU-16
ADG659YCP	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG659YCPZ[1]	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG659YCPZ-REEL7[1]	−40°C to +85°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	CP-16
ADG659YRQ	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG659YRQ-REEL	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG659YRQ-REEL7	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16
ADG659YRQZ[1]	−40°C to +125°C	16-Lead Shrink Small Outline Package [QSOP]	RQ-16

[1] Z = RoHS Compliant Part.
[2] Qualified for automotive.

©2004–2009 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners.
D03273-0-2/09(B)